


REVISIONS						
P	LTR	DESCRIPTION			DATE	DWN
AF5	REVISED	PER	ECO-16-004800		12SEP2016	NK
AG	REVISED	PER	ECO-17-004657		05APR2017	RS

D




C

B


A



RECOMMENDED P.C. BOARD LAYOUT



- 1
- CONNECTOR WILL ACCEPT POSTED TYPE III+ PIN CONTACTS.
- 2
- CONTACT BODY: SELECT GOLD OVER NICKEL.
CONTACT POST: TIN-LEAD PER MIL-T-10727 OVER COPPER PER MIL-C-14550A.
- 3
- RECOMMENDED PC BOARD HOLE SIZE FOR CONTACT POST: 1.02±0.08[.040±.003] DIA.
- 4
- 5
- CONTACT BODY: SELECT GOLD OVER NICKEL.
CONTACT POST: TIN OVER NICKEL.
- 6
- POSITIONS LOADED WITH CONTACTS: 1-4, 10-17, 19-22, 24, 25, 29, 30, 32, 33.
- 7
- POSITIONS LOADED WITH CONTACTS: 1-20, 22-28, 30-37.
- 8
- OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI.
- 9
- CONTACT BODY: TIN OVER NICKEL.
CONTACT POST: TIN OVER NICKEL.
- 10
- CONTACT BODY: SELECT GOLD OVER NICKEL.
CONTACT POST: TIN/LEAD OVER NICKEL.
- 11
- CONTACT BODY: TIN/LEAD OVER NICKEL.
CONTACT POST: TIN/LEAD OVER NICKEL.



OBSOLETE	5	NO	YES	YES	—	.170	2-206934-9
OBSOLETE	5	NO	YES	NO	—	.413	2-206934-8
PRELIMINARY	5	NO	YES	NO	—	.257	2-206934-7
OBSOLETE	9	NO	YES	YES	—	.119	2-206934-6
OBSOLETE	5	NO	NO	NO	.150±.003	.240	2-206934-5
OBSOLETE	10	NO	NO	NO	.150±.003	.220	2-206934-3
OBSOLETE	5	NO	NO	YES	.150±.003	.119	2-206934-2
OBSOLETE	5	NO	NO	NO	.150±.003	.119	2-206934-1
OBSOLETE	5	NO	YES	YES	—	.618	2-206934-0
OBSOLETE	5	NO	NO	NO	.150±.003	.618	1-206934-9
OBSOLETE	5	NO	NO	NO	.150±.003	.429	1-206934-8
OBSOLETE	5	NO	YES	YES	—	.119	1-206934-7
OBSOLETE	10	NO	NO	YES	.150±.003	.429	1-206934-5
OBSOLETE	10	NO	YES	NO	—	.220	1-206934-3
OBSOLETE	11	NO	NO	NO	.150±.003	.429	1-206934-2
OBSOLETE	5	NO	NO	NO	.150±.003	.220	1-206934-1
OBSOLETE	10	YES	NO	YES	—	.119	1-206934-0
OBSOLETE	10	YES	YES	YES	—	.119	206934-9
OBSOLETE	10	NO	NO	NO	.150±.003	.618	206934-7
OBSOLETE	10	NO	NO	NO	.150±.003	.429	206934-6
OBSOLETE	10	NO	NO	NO	.150±.003	.119	206934-5
OBSOLETE	10	NO	YES	NO	—	.220	206934-4
OBSOLETE	10	NO	NO	NO	.158±.001	.618	206934-3
OBSOLETE	10	NO	NO	NO	.158±.001	.429	206934-2
OBSOLETE	10	NO	NO	NO	.150±.003	.220	206934-1
CONTACT FINISH	M3 INSERTS	4-40 INSERTS	PERIPHERAL SEAL	B	A	PART NUMBER	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J.GALLUCCI 5-30-91	TE Connectivity		
DIMENSIONS: mm		CHK W.G.LENKER 4-14-92	NAME K REAVER 4-14-92 RECEPTACLE ASSEMBLY, POSTED, STD SEX, SERIES 1, 23-37, CPC		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC 108-10024			
0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ±.005 4 PLC ± ANGLES ±		APPLICATION SPEC			
MATERIAL SEE CALLOUT		SIZE A1			
FINISH		CAGE CODE 00779			
CONTACT: 		DRAWING NO 206934			
CUSTOMER DRAWING		RESTRICTED TO —			
SCALE 2:1		SHEET 1 OF 1			
REV AG					