


The universal sawblade programme for Jigsaws

105 101 =
T188A


Shank suitable
for Bosch,
AEG, ELU,
FESTO, Hitachi,
Holz-Her,
Makita, Metabo



Type	T 101 B	T 101 BF	T 101 BR	T 101 D	T 301 CD	T 101 DP	T 111 C	T 119 B	T 101 AO	T 119 BO
Toothed length in mm	75	75	75	75	85	75	75	50	50	50
Tooth pitch in mm	2,5	2,5	2,5	4	3	4	3	2	1,35	2
Version	Ground HCS	Ground Bi-Metal	Ground HCS	Ground HCS	Ground HCS	Ground HCS	Side-set HCS	Wavy set HCS	Ground HCS, pointed teeth	Wavy set HCS
Cutting depth	<30 mm	3-10 mm Alu <30 mm	<30 mm	<60 mm	<60 mm	<60 mm	<60 mm	<30 mm	<25 mm	<20 mm
Pack of 5 Part No.	2 608 630 036	2 608 634 568	2 608 630 014	2 608 630 032	2 608 637 580	2 608 637 527	2 608 630 033	2 608 630 032	2 608 630 031	2 608 630 310
Pack of 3 Part No.	2 608 630 587			2 608 630 598	2 608 637 581	2 608 637 528	2 608 630 006	2 608 630 878	2 608 630 586	

HCS - High speed Carbon Steel, HSS - High speed Steel, HAS - High Alloy Steel, HM - Carbide tipped

Shank suitable
for Bosch,
AEG, ELU,
FESTO, Hitachi,
Holz-Her,
Makita, Metabo




Type	T 118 A/ T 318 A*	T 118 AF	T 118 AHM	T 118 B/ T 318 B*	T 118 BF	T 118 EF	T 118 EHM	T 118 G	T 113 A	T 141 HM T 340 HM
Toothed length in mm	50 100*	50	50	50 100*	50	50	50	50	75	60 95*
Tooth pitch in mm	1,2	1,2	1,06	2	2	1,5	1,41	0,7	-	4,3 4,5
Version	Wavy set HSS	Wavy set Bi-Metal	Tungsten carbide	Wavy set HSS	Wavy set Bi-Metal	Wavy Set Bi-Metal	Tungsten Carbide	Wavy Set HSS	Ground knife-edge, HCS	Carbide-tipped
Cutting depth	1,5-4 mm	1,5-4 mm	1,5-4 mm	3-6 mm	3-10 mm	2-5 mm	2-5 mm	<2 mm	-	<20 mm
Pack of 5 Part No.	2 608 631 013 2 608 631 319*	2 608 634 508		2 608 631 014 2 608 631 404*	2 608 634 503	2 608 634 504		2 608 631 012		2 608 630 882
Pack of 3 Part No.	2 608 631 887	2 608 634 684	2 608 630 883	2 608 631 673			2 608 630 885	2 608 631 674	2 608 635 177	2 608 630 883* 1 piece

Your guide to the right Jigsaw blade

Here's how to find the right sawblade quickly. Select your workpiece material from the vertical columns, then check the type of job down the left hand side. The optimal Bosch sawblade number for your purpose is where the vertical column and horizontal line intersect.

		Hardwood Softwood Chipboard	Chipboard	Plastic coated chipboard	Plywood	Laminated board	Wood containing nails	Steel, mild steel	Sheet metal	Stainless steel
Range of application										
Straight cuts		T 101 B T 101 D T 101 DP	T 101 D T 141 HM T 101 DP	T 101 BR	T 101 B T 119 B	T 101 D	T 101 BF	T 118 A T 318 A T 118 EHM	T 118 A T 118 AF	T 118 EHM T 118 AHM
Curved cuts Good curve negotiation		T 244 D T 101 AO T 119 BO	T 244 D T 101 AO T 119 BO	T 101 AO	T 101 AO T 119 BO	T 244 D	T 144 DF	T 118 AF	T 118 AF	
Thick materials		T 101 D T 144 D T 301 CD	T 101 D T 301 CD T 101 DP	T 101 D T 101 DP	T 119 B T 101 B	T 101 AO T 301 CD	T 144 DF	T 318 B T 118 B T 127 D		
Thin materials		T 101 B T 119 B	T 101 B	T 101 AO	T 101 AO	T 101 B	T 118 BF	T 118 A T 118 EHM T 118 AHM	T 118 G	T 118 EHM T 118 AHM
Fine cut		T 101 B T 101 BR T 101 AO T 301 CD	T 101 B T 301 CD	T 101 BR T 101 AO	T 101 AO T 101 BR	T 101 B	T 101 BF			
Coarse cut		T 111 C T 144 D	T 144 D T 111 C T 244 D	T 101 D	T 119 B	T 144 D	T 144 DF	T 127 D		
Rasps: flat half-round 3-cornered		T 132	T 132							
Parallel cut		T 101 DP	T 101 DP	T 101 DP	T 101 DP	T 101 DP				
Exact parallel cut										
Fast cutting		T 144 D T 301 CD T 101 D	T 144 D T 144 DF T 101 D	T 301 CD		T 144 D T 301 CD T 144 DF	T 144 DF		T 118 BF	
Bi-Metal		T 101 BF T 144 DF	T 101 BF T 144 DF	T 101 BF	T 118 EF	T 101 BF T 144 DF	T 101 BF T 144 DF T 118 BF	T 118 BF T 118 AF	T 118 AF T 118 EF T 118 BF	
Special application										
		T 101/301 only	T 101/301 only	T 101/301 only	T 101/301 only	T 101/301 only		Cutting oil emulsion	Cutting oil emulsion	Cutting oil emulsion



T 101 A	T 118 B T 318 A T 101 A	T 318 A T 318 B	T 101 B	T 101 A	T 141 HM T 130 T 127 D	T 130 T 150	T 113 A
T 227 D	T 227 D T 118 AF		T 119 B T 119 BO	T 119 BO	T 227 D	T 130	T 101 AO
T 127 D T 318 B T 118 B	T 318 B	T 318 B	T 101 D T 301 CD	T 101 A	T 340 HM	T 130	T 113 A
	T 118 G T 118 A	T 318 A	T 101 B		T 130	T 150	T 113 A
T 101 A	T 101 A	T 318 A		T 101 A	T 101 BF	T 150	T 113 A
T 127 D	T 111 C		T 111 C T 127 D T 101 DP	T 119 B	T 141 HM T 340 HM	T 130	T 119 B
	T 127 D				T 141 HM		
T 127 DF T 108 BF	T 118 BF T 118 EF		T 127 DF	T 119 BF	T 127 DF T 101 BF		

