

### Cleaning:

- > Clean this light fitting only with a soft dry cloth
- > Do not use any chemical or abrasive cleaners.

### Lamp replacement:

- > Switch off the electricity at the mains.
- > Unscrew lamp.
- > Screw in new lamp and restore electricity supply..

### Replacement lamp type:

Wattage: 15W Maximum  
Supply Voltage: 250V  
Size: E14

### Eventually, you may want to replace this light fitting:

When your light fitting comes to the end of its life or you choose to update or upgrade it by replacing it, please do not dispose of it with your normal household waste, please recycle where facilities exist. When you need to dispose of this fitting, check with your retailer or local authority for suitable options. New regulations will encourage the recycling of Waste from Electrical and Electronic Equipment ( European "WEEE Directive" effective August 2005 ).



### If you experience problems:

If your light is defective or develops a fault, please return it to the place where you bought it. You can call our Helpline for advice. The Helpline will gladly give advice on any aspect of any Eterna Lighting product but may not be able to give specific instructions regarding individual installations.

**If in doubt, consult a qualified electrician.**

### Help line:

Tel: 01933 673 144      Fax: 01933 678 083      Email: [sales@eterna-lighting.co.uk](mailto:sales@eterna-lighting.co.uk)  
For answers to frequently asked questions ( FAQs ) and other information visit our web-site  
[www.eterna-lighting.co.uk](http://www.eterna-lighting.co.uk)



# IMPORTANT !

## Safety and Installation instructions

### Pygmy Cabinet Light with Auto-switch

**Model(s)**  
D087, P1100 range

### Pack contents:

|                                    |   |
|------------------------------------|---|
| Single pygmy cabinet light fitting | 1 |
| 15 Watt pygmy lamp                 | 1 |
| Fixing pack                        | 1 |

**PLEASE READ THESE INSTRUCTIONS BEFORE  
INSTALLING YOUR NEW FITTING**

- -

**PLEASE RETAIN FOR FUTURE REFERENCE**

### Read this first:

- > **If in any doubt, consult a qualified electrician.**
- > Suitable for indoor use only.
- > Suitable for fixing on a normally flammable surface.
- > Before making fixing hole(s), check that there are no obstructions hidden beneath the mounting surface such as pipes or cables.
- > If the location of your new fitting requires the provision of a new electrical supply, the supply must conform with the requirements of the latest edition of the IEE wiring regulations.
- > Make connections to the electrical supply in accordance with the following code:
  - Live - Brown or Red
  - Neutral - Blue or Black
- > This product is designed for permanent connection to fixed wiring: this should be either a suitable lighting circuit ( protected with a 5 or 6 Amp MCB or fuse ) or a fused spur ( with a 3 Amp fuse ) via a fused connection unit. We recommend that the supply incorporates a switch for ease of operation.
- > This fitting is double insulated, do not connect any part to earth.
- > Ensure that the minimum distance from the light to any flammable surface is at least 40mm.
- > **If in any doubt, consult a qualified electrician.**

### Installation:

- 1) Turn off the electrical supply and remove the appropriate circuit fuse.
- 2) Choose the location of your pygmy light so that the movement of the switch is within the ranges shown in the diagram opposite.
- 3) Ensure that there is at least 40mm between the fitting and any overhanging or horizontal surface. See diagram opposite.
- 4) Secure the fitting in place using screws appropriate to the mounting surface.
- 5) Using cable clips for 2 x 0.75mm<sup>2</sup> flat twin flex, secure the cable to the mounting surface choosing a route which prevents the cable from fouling the movement of whatever you have planned to actuate the switch.
- 6) Using an Eterna ® Link lead ( not supplied ), make your connection to the mains supply. See above for wiring colour code.
- 7) Fit the 15 Watt pygmy lamp supplied.
- 8) Restore the power and switch on.

Safety markings:

