

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0676840101](#)
Status: **Obsolete**
Description: 0.80mm (.031") Pitch SODIMM Socket, Right Angle, Surface Mount, 5.20mm (.205") Mounted Height, 144 Circuits, 3.3V Power Supply, Semi- hard Tray Packaging, Lead-free

Documents:
[Drawing \(PDF\)](#)

General	
Product Family	Memory Module Sockets
Series	67684
Comments	3.3V Power Supply
Component Type	Socket
JEDEC Outline	N/A
Product Name	S.O. DIMM

Physical	
Circuits (Loaded)	144
Durability (mating cycles max)	30
Entry Angle	90° Angle (Side Entry)
Keying to Mating Part	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.20mm (.047")
Packaging Type	Tray
Pitch - Mating Interface	0.80mm (.031")
Temperature Range - Operating	-55°C to +85°C

Electrical	
Current - Maximum per Contact	0.3A
Voltage - Maximum	100V
Voltage Key	3.3V

Material Info

Reference - Drawing Numbers	
Sales Drawing	SD-67684-001

EU RoHS
Not RoHS Compliant
REACH SVHC
Not Reviewed
Low-Halogen Status
Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[67684Series](#)

Mates With
JEDEC Standard DRAM and SDRAM modules