

MICRO SWITCHES

ORDERING INFORMATION

SWITCH TYPE	PART SUFFIX	OF Max. (gf)		OP (mm)	PT Max. (mm)	OT Min. (mm)	MD Max. (mm)
VA2- □□□ 0-00D0-Z		Q	330	14.7±0.5	1.72	0.8	0.4
		H	230				
		S	170				
		L	110				
VA2- □□□ 1-01D0-Z		Q	330	15.3±0.5	2.8	0.6	0.5
		H	230				
		S	170				
		L	110				
VA2- □□□ 1-02D0-Z		Q	180	15.3±1.5	5.9	1.6	1.0
		H	125				
		S	86				
		L	50				
VA2- □□□ 1-03D0-Z		Q	120	15.3±2.5	9.3	-	2.1
		H	70				
		S	49				
		L	30				
VA2- □□□ 1-04D0-Z		Q	205	18.7±1.5	5.5	1.4	1.1
		H	140				
		S	110				
		L	65				
VA2- □□□ 1-05D0-Z		Q	330	20.7±0.8	2.7	0.6	0.45
		H	230				
		S	170				
		L	110				
VA2- □□□ 1-06D0-Z		Q	180	20.7±1.5	4.2	1.6	1.25
		H	125				
		S	100				
		L	65				