

FEATURES

Double tuning fork type contact guarantees high reliability.
2.54MM pitch Low-Profile mini type Match to 0.64mm sq. posts.


*Znsulator Tolerance:±0.20
Coostacts Tolerance:±0.05

MATERIAL

.Insulator.....21SPC NY66 (94V-2)
.Contact.....Gold Plated
.Terminal.....C-2680

SPECIFICATIONS

.Current Rating:3 amperes MAX
.Concact Resistance: 30m ΩMAX
.Insuiation Resistance: 1000 megohms MAX
.Dielectric Withstanding Voltage: AC 650 volts RMS at sea leve



RoHS
Compliant

HSM 玄茂科技股份有限公司
HSUAN MAO TECHNOLOGY CO., LTD.


APPD.
核准

DWG.
製圖

DATE

HELEN

2011/8/25



SCALE
比例

UNIT
單位

PAGE
張數

TOLERANCE
容許公差

0.00 ±
ANG. ±

SIZE
紙張尺寸

REV.
版次

PART NAME 品名

2.54mm MINI JUMPER 2P H:13.5mm WITH
HANDLE OPEN COVER GOLD PLATING ROHS

PART NO.

料號 C2700-02DAGX00R