


Socket Connector

Series


384



Rated current	10,0 A
Rated voltage	250 VRMS / VDC
	750 VRMS / VDC (variation 3)
Withstand voltage	875 VRMS for 1 minute
	1750 VRMS for 1 minute (variation 3)
Material contact	Copper alloy
Material insulator	Thermoplast UL94V-0
Operating temperature	-20°C to +85°C
Max. processing temper.	230°C for 5 seconds
All dimensions in mm.	


termination
max. pincount
030

Variation




Contact type

H



G



1

2

3

code		no. of contacts		first mate / last break		available in variation			
N	E	n	-			1	2		
	020	b1 + a0					3		
no. of contacts		see figure left		see figure left		see figure left		available in variation	
n	A	B	C	D	E				
008	47,00	29,00	38,00	38,00	30,00	1			
012	59,00	41,00	50,00	50,00	42,00	1			
016	71,00	53,00	62,00	62,00	54,00	1			
020	83,00	65,00	74,00	74,00	66,00	1		3	
030	83,00	65,00	74,00	74,00	66,00	2			

Contact type:
 Variation 1 = H,G
 Variation 2 = H,G
 Variation 3 = H

Plating:
 B = Ag 4 μ
 K = Au 0,8 μ

First mate/last break:
 (please see table)

Variation (1,2,3)

No. of contacts

Contact type (H,G)
 Plating contact (B,K)
 First mate/last break



Order code:

384 - 2 - 2222 - 2222 - ZS

Mating series	383	376
see page	15-2	15-4

Product group
15