

datasheet for PMS SKS
 article number: 932794001



product description:	order number: 932 794-001
description:	Test equipment set standard. Contents: 1 x Measuring lead MLN 50/1 black, 1 x Measuring lead MLN 50/1 red, 2 x Measuring lead MLN 100/1 black, 2 x Measuring lead MLN 100/1 red, 1 x Measuring lead MLN 200/1 black, 1 x Measuring lead MLN 200/1 red, 1 x Clamp- type test probe KLEPS 30 black, 1 x Clamp- type test probe KLEPS 30 red, 1 x Crocodile clip AK 2 S black, 1 x Crocodile clip AK 2 S red, 1 x PRUEF 2 black, 1 x PRUEF 2 red
typ:	PMS SKS
system:	4 mm system
order number:	932 794-001
clamping range:	4 mm - 9,5 mm
technical data	
measurement category	CAT II
norm	
type of contact:	pin (spring-loaded), socket
cable type:	LEH-XY
cable specification:	highly flexible lead
wire stranding:	259 x 0,07
rated voltage:	DC 60 V
rated current:	16 A
cable length:	50 cm, 100 cm, 200 cm
conductor size:	1 mm ²
cable material:	PVC
cable color:	Each article in black and red.
material	
contact material:	contact pin: brass, contact spring: copper berylli
contact surface material:	nickel-plated
contact holder material:	PA
connecting nut material:	Zn Al/Ni
environmental conditions:	
temperature range:	-15 °C to +70 °C
flammable class:	
housing:	94 V-2