


1.27mm Pin Header

- single row straight -

1.27mm x 2.54mm Pin Header


- dual row straight -



SPECIFICATIONS

Current rating	1 A
Insulator resistance	5000 MΩ min.
Contact resistance	20 mΩ max.
Dielectric withstanding voltage	500 V AC
Operating temperature	- 40° to +105°C
Contact material	Phosphor bronze
Insulator material	Nylon, UL 94 V-0

PCB Hole Layout



How to order

S xx - xxx - **S** xxx/xx - 01 /1

Single plastic	Nbr of contacts	Terminal code & dimensions			Plating
L1 = single row L2 = dual row	single row = 002 to 032 dual row = 004 to 100	Code	A	B	01 = tin / gold Other platings on request
		079 / 01	2.80 mm	2.60 mm	
		111 / 01	6.00 mm	2.60 mm	
		Other dimensions on request			
Double plastic " Boardstacker "	Nbr of contacts	Terminal code & dimensions			Plating
P1 = single row P2 = dual row	single row = 002 to 032 dual row = 004 to 100	Code	A	B	01 = tin / gold Other platings on request
		116 / 01	2.80 mm	2.60 mm	
		152 / 01	6.00 mm	3.00 mm	
		Other dimensions on request			