


Panel Mount Mini-DIN Receptacle

161-381/3, 161-381/4, 161-381/5,
161-381/6, 161-381/8

KOBICONN

Panel Mount Mini-DIN Receptacle

161-381/3, 161-381/4, 161-381/5, 161-381/6, 161-381/8



Dimensions: mm (In.)

LET	Part Name	Material	Finish
1	Housing	P.B.T.	-
2	Shield	Brass	Sn
3	Contact	Phosphor Bronze	Ag
4	Nut	Steel	Uni-Chrome

SPECIFICATIONS	
Insulation Resistance:	50M Ω Min. @250 VDC
Contact Resistance:	30m Max.
Dielectric Strength:	250 VAC for one minute
Insertion Force:	4.5 Kgf Max.
Extraction Force:	0.9 - 3 Kgf

Date Last Revised: 5-24-05

Available from Mouser Electronics
1-800-346-6873
www.mouser.com

KC- 300234

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Kobiconn:

[161-381/6](#) [161-381/4](#) [161-381/5](#) [161-381-8](#) [161-381/3](#)