

SPECIFICATIONS

Mechanical

Plug Mating Force: 3.00kg (6.61Lb) max.
Plug Unmating Force: 0.40~3.00kg (0.88~6.61Lb)
Contact Retention Force: 0.50kg (1.10Lb) min.
Durability: 1500 Cycles

Electrical


Current Rating: 1.00A
Contact Resistance: 50m Ω max(Initial)
 100 m Ω max(After life test)
Dielectric Withstanding Voltage: 500V AC/1min min.
Insulation Resistance: 100M Ω min.

Physical


Housing: Thermoplastic, UL 94V-0 rated
Contact: Copper alloy
Plating: See "ORDERING INFORMATION"
Operating Temperature: -25 °C to +85 °C
Recommended Thickness of PCB: 1.60[.063]

Audio Jack Connector

JA Series
Triple HD Jack, R/A, T/H
Type Φ 3.5mm [.138"]
13 Pos.



DRAWING



ORDERING INFORMATION

PRODUCT NO.: JA 3 3 3 3 1 - HA1P-4 F

Audio Jack Series _____

Body Type _____
3=Triple Jack

Sleeve Style _____
3=All Plastic Cylindrical

Plug Type _____
3=Three Band

Plug Diameter _____
3=3.50mm

Lead Free Code _____
4F=Lead Free

Extension Code _____

Contact Area Plating _____
1=Gold Flash