







REV.	DATE	DESCRIPTION
A	04/31/03	UPDATE DRAWING FORMAT



RECOMMENDED
CABLE STRIPPING DIM'S



					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007" .315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020" DO NOT SCALE DRAWING	APPROVALS		DATE		Amphenol Connex					
8						DRAWN	G.R.S.	04/31/03							
7						CHECKED									
6										PART DESCRIPTION SMA DIRECT SOLDER PLUG (FOR .047” SEMI–RIGID CABLE)					
5						ISSUED									
4	SOLDER BARREL	BRASS	GOLD	1						PART NO. 132249					
3	CONTACT PIN	BRASS	GOLD	1		SHEET	1 OF 1								
2	INSULATOR	TEFLON	NATURAL	1					DWG. NO. 132249.DWG						
1	BODY	BRASS	GOLD	1											
	DESCRIPTION	MATERIAL	FINISH	QTY		C:/132/132249.DWG			REV.	A	SIZE	A	SCALE	NA	