


Current refinements (click  to remove)

Search Tips

 Region  USA  Product Family  HSTTK Kynar*Heat Shrink 4ft. Pieces  Text Search: 'HSTTK19-48-Q'

Your search criteria matched only one product, shown below.



- For dry locations
 - Semi-rigid, highly heat resistant
 - Offers excellent chemical and abrasion resistance
 - Use in high temperature or solvent rich environment
-
- Semi-rigid highly heat resistant
 - Excellent chemical and abrasion resistance
 - Meets AMS-DTL-23053/8
 - Meets UL224 VW-1 flame retardant

Part Number:	HSTTK1948-Q
RoHS Compliancy Status:	Compliant
Part Description:	Semi-rigid heat resistant Kynar* Heat Shrink offers excellent chemical resistance in solvent rich environments.
Material:	Kynar*
Color:	Clear
CSA Certified:	Yes
Military Specification:	AMS-DTL-23053/8
UL Recognized:	E122770
Length (ft.):	4
Length (m):	1.2
Flammability Rating:	UL224 VW-1
Max. Recovered I.D. (In.):	.093
Max. Recovered I.D. (mm):	2.4
Min. Expanded I.D. (In.):	.187
Min. Expanded I.D. (mm):	4.8
Nominal Diameter (In.):	.187
Nominal Diameter (mm):	4.8
Nominal Recovered Wall Thickness (In.):	.010
Nominal Recovered Wall Thickness (mm):	0.3
Shrink Ratio:	2:1
Temperature Range:	-67°F to 347°F (-55°C to 175°C)
Min. Order UOM:	PC
Min. Order Qty.:	25
BOM Qty. (# of Pkgs.)	0
Add to My Catalog	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'My Catalog' features.