

T-Series




The T-Series Mini Tippette snap-in rocker switches are single pole with ratings up to 20 amps. A variety of circuits, actuators and terminations are available.

Specifications

- Certifications*: UL, CSA, VDE
- Dielectric Strength: 1,000 V (minimum)
- Insulation Resistance: 100 Megohms (minimum)
- Base Material: Nylon
- Actuator Material: Nylon
- Bezel Material: Nylon

* Due to ongoing technological advances, consult factory for certification specifics.

Dimensional Specifications: in. [mm]



SERIES	RATING ¹	TERMINATION/FUNCTION	ACTUATOR COLOR ³
T SINGLE POLE	10 5A 250VAC 10A 125VAC 1/2HP 125-250VAC	0 1 3 5 A B D F L M R T	B BLACK W WHITE
CIRCUIT	11 5A 250VAC 10A 125VAC 5A (TUNGSTEN) 125VAC L	0 1 3 5 A B D F 0 1 3 5	BASE COLOR³
A ON-NONE-OFF	20 10A 250VAC 15A 125VAC 3/4HP 125-250VAC	0 1 3 5 A B D F 0 1 3 5	B BLACK W WHITE
B ON-NONE-ON	22 10A 250VAC 15A 125VAC 20A 125-250VAC H 3/4HP 125-250VAC	0 1 3 5 A B D F 0 1 3 5	
C ON-OFF-ON	25 10A 250VAC 16A 125VAC 1/2HP 125-250VAC	0 1 3 5 A B D F 0 1 3 5	

ACTUATOR STYLE²

P PADDLE
PL PLUNGER
PS PADDLE - SHORT
T ROCKER
TL MOMENTARY ROCKER

NOTES:

Shading indicates standard configurations. Stainless steel bezels are available. Add suffix "Bezel" to the end of the catalog number. (ex.) TA201-TB-B/BEZEL

Imprinting is available. Please specify when ordering. (ex. TA201-TB-B/ON-OFF)

Panel Cut-Out Recommendations: For sheet metal panels, switch must enter panel in same direction as the punch. (Burr on bottom.) Test cut hole in actual material.

¹ Rating Code 22 is 20A 125VAC inductive when momentary function is specified. Rating Code 22 only available with circuits A & B. Rating Code 25 only available with PL-Plunger actuator.

² PL-Plunger actuator available only in T Series with circuit A, termination/function B or F, and terminals at T1 and 2.

³ Custom colors are available. Consult factory.