

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [170351-0002](#)
Status: **Active**
Description: EXTreme Guardian™ Crimp Receptacle Housing, 2 Circuit, 11.00mm Pitch, 8-10 AWG

Documents:
[3D Model](#) [Product Specification PS-46819-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

TUV R72130381
UL E29179

General

Product Family Crimp Housings
Series [170351](#)
Application Wire-to-Board, Wire-to-Wire
Product Name EXTreme Guardian™
UPC 884982274723

Physical

Circuits (maximum) 2
Color - Resin Black
Flammability 94V-0
Gender Male
Glow-Wire Compliant No
Keying to Mating Part None
Material - Resin Polyester
Net Weight 7.910/g
Number of Rows 1
Packaging Type Bag
Panel Mount No
Pitch - Mating Interface 11.00mm
Temperature Range - Operating -40°C to +105°C


Electrical

Current - Maximum per Contact 80A

Material Info

Reference - Drawing Numbers

Product Specification PS-46819-001
Sales Drawing SD-170351-0002



EU RoHS

**ELV and RoHS
Compliant**

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Low-Halogen

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of
Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
non-product compliance questions.

Search Parts in this Series

[170351](#)Series

Mates With

68790 EXTreme Guardian™ Cable
Assembly

Use With

[46819](#) High Power Terminal

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION