




SIGN	DATE	DESCRIPTION	APPROVER
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

- NOTES:
1. Rating:300V 20A(UL) ;
 2. Insulation Withstanding Voltage:AC2000V/MIN
 3. Insulation Resistance: $\geq 500M\Omega$ or more at DC500V
 4. Temperature Range: $-33^{\circ}C/+105^{\circ}C$
 5. Screw Torque Vlaue:4.5 lbf-in(UL)
 6. Suitable Electric Wire: 12-20AWG
 8. Housing: Nylon PA66
 9. Screw M3, Stell, Zinc Plated
 10. Standard Color: Natural

RoHS Compliant



TITLE		ES1000 Series - 10.0mm Euro Strip, Wire guard, flat base			
PART NO.	ES1000/XXDSFB	DWG NO.		ES1000/XXDSFB.DWG	
APPROVED	KSZ 2007.08.01	CHECKED	KSZ 2007.08.01	DESIGNED	KSZ 2007.08.01
DRAWN	KSZ 2007.08.01	5020		Tolerance	
SHEET: 01/01		UNIT: mm		SCALE: NONE	
		REV: A		X ±015	
				.XX ±0.075	
				.XXX ±0.05	

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF ON-SHORE TECHNOLOGY, INC. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF ON-SHORE TECHNOLOGY, INC.