








Material:

- Insulator: Hi-Temp Plastic UL 94V-0
- Contact: Phosphor Bronze T=0.20MM
- Shell: Brass T=0.30MM

Electrical:

- Contact Current Rating: 0.5 Amperes
- Dielectric Withstanding Voltage: 300V AC R.M.S.
- Insulation Resistance: 100MΩ Min.
- Contact Resistance: 30MΩ Max.
- Operating Temperature: -20°C ~ +85°C

⊕ = Assmann logo

RoHS
Compliant

ITEM NO.

A-HDMI282-19M-B-F-02-05-R

TITLE

HDMI Connector - Solder Type, Male,
19 Pin, Black Insulator, Contact Plating 30μ"

ASSMANN
Electronics, Inc.

1840 W. Drake Drive, Suite 101 • Tempe, AZ 85283
Toll Free: 1-877-277-6266 • Email: info@usa-assmann.com

THIS DRAWING IS UNPUBLISHED
©Copyright 2009 by Assmann Electronic Components
All International Rights Reserved