




&lt; List of part numbers with package codes &gt;

RCE5C1H330J0DBH03A

## Shape



L size or outer diameter D (mm)	3.6 mm max.
W size	3.5 mm max.
T size	2.5 mm max.
Lead spacing F	2.5 +0.4/-0.2mm
Lead diameter d	0.5 ±0.05mm

## Notes

Meet LF(Lead Free)[※LF : Lead content is less than 1000 ppm.], HF(Halogen Free)

## References

Packaging	Specifications	Minimum quantity
A	Ammo pack taping type	2000

## Specifications

1 of 1 Capacitance	22nF ±5%
<b>Attention</b> Rated voltage	50Vdc
1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, its specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.	
Temperature characteristics (complied standard)	COG(EIA)
2. This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.	±5%
<b>muRata</b> Murata Manufacturing Co., Ltd.	URL : <a href="https://www.murata.com/">https://www.murata.com/</a> 25 to 125 °C: 0+30ppm/°C -55 to 25 °C: 0+30/-72ppm/°C
Temperature coefficient	Last updated: 2018/02/09

Temperature range of temperature characteristics

-55 to 125°C

Operating temperature range

-55 to 125°C