


PRODUCT DATA SHEET

Part Number : **1921XX5W**

Type	Size	IP Rating	Description
LED	M14	67	Round bezel panel indicator

Dimensions(mm):



Part #	Colour	Voltage	Current(mA)	Intensity(mcd typ)
1921X25W	Cool white	12Vdc	20	500
1921X35W	Cool white	24Vdc	20	500

Notes:

1. Bezel codes : X=0(satin),1(black),or 2(matt) chrome
2. Storage temperature -25 °C to +80°C
3. Application temperature -20 °C to +60°C
4. Terminals: Brass +ve, Tinned brass -ve
5. Terminals not qualified for soldering
6. The plastic(polycarbonate) has limited chemical resistance
7. Sealed to IP67 when used with the supplied gasket
8. RoHS & REACH SVHC compliant

Issue # 1 : 13 Feb 12