

MATERIALS AND FINISHES

BODY ZINC ALLOY
PLATED NICKEL

CENTER CONTACT PHOSPHOR BRONZE
PLATED GOLD

INSULATOR POLYPROPYLENE (94 V-2)

HOUSING VALOX 420-SEO
COLOR BLACK

SOLDER TAIL COPPER OVER STEEL WIRE
PLATED TIN


FRONT CLIP PHOSPHOR BRONZE
PLATED NICKEL

CHIP CAPACITOR MULTILAYER CERAMIC


BOARD CLIP PHOSPHOR BRONZE
(C52100, GRADE H10)
PLATED TIN

LOCKWASHER PHOSPHOR BRONZE
PLATED NICKEL


JAM NUT BRASS
PLATED NICKEL



SCHEMATIC
9400 ±20% PF, 1.5 KV W V_{dc}



NUT
1/2-28 UNEF-2B



LOCKWASHER
15.90 REF
.626
.50 REF

RECOMMENDED MOUNTING HOLE
RECOMMENDED MOUNTING TORQUE:
0.56 N-m(5.00 IN-LBS)
PANEL THICKNESS: 5.5 (.217) MAX

73171-3090	73100-0223, ONE PER BAG
73100-0223	TRAY
PART NO.	PACKAGING


CHG: PANEL THICKNESS .217 WAS 2.17
EC NO: URF2008-0469
DRWN: JWIENER 2008/03/18
CHKD: SSHAH 2008/03/18
APPR: JWIENER 2008/03/18

QUALITY SYMBOLS
▽=0
▽=0

GENERAL TOLERANCES (UNLESS SPECIFIED)	
mm	INCH
4 PLACES ±---	±---
3 PLACES ±---	±---
2 PLACES ±---	±---
1 PLACE ±---	±---
ANGULAR ± 2 °	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	



DIMENSION STYLE	
MM/IN	
DRAWN BY	DATE
IRIS WANG	1995/03/07
CHECKED BY	DATE
APPROVED BY	DATE
FIELDS	1995/10/23
MATERIAL NO.	
SEE TABLE	
SIZE	
C	

SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION
METRIC		
TITLE		
BNC JACK, R/A RECEPTACLE		
50 OHMS FILTER		
BNC-J/PCB/RA/BK		
MOLEX INCORPORATED		
DOCUMENT NO.	SD-73100-0223	SHEET NO.
		1 OF 1
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		



BNC JACK
INTERFACE PER
ES-73599-0000

1/2-28 UNEF-2A



RECOMMENDED PCB HOLE
CONFIGURATION

