

32.768kHz SMD REFLOWABLE, CYLINDRICAL TYPE TUNING FORK CRYSTAL

AB206J



RoHS
Compliant



8.3 x 2.7mm

FEATURES:

- Formed leads for low cost SMD type
- Excellent shock resistance
- IR reflow capable

APPLICATIONS:

- Real time clock
- Measuring instruments
- Blue-tooth and wireless applications

STANDARD SPECIFICATIONS:

PARAMETERS	
ABRACON P/N	AB206J
Frequency	32.768 kHz
Operating Temperature	-40°C to + 85°C
Turn-over Temperature	25°C to $\pm 5^\circ\text{C}$
Storage Temperature	-55°C to +125°C
Frequency Tolerance	± 20 ppm max. at 25°C
Frequency Stability	$-0.034 \pm 0.006\text{ppm}/^\circ\text{C}^2$
Equivalent Series Resistance	50k Ω max.
Shunt Capacitance C0	1.35pF typical
Load Capacitance CL	12.5pF (see options)
Quality Factor	70,000 typ.
Drive Level	1 μW max.
Aging at 25°C first year	± 3 ppm max. at 25°C $\pm 3^\circ\text{C}$
Insulation Resistance	500 M Ω min. at 100 Vdc $\pm 15\text{V}$

OPTIONS & PART IDENTIFICATION:

[Left blank if standard]


AB206J-Frequency-☐☐

Load Capacitance	
Blank	12.5pF
6	6pF

*Contact ABRACON for non-standard load capacitance

Packaging	
Blank	Bulk
T	Tape and Reel (3Kpcs/ reel)

TUNING FORK CRYSTAL TEMPERATURE CURVE



32.768kHz SMD REFLOWABLE, CYLINDRICAL TYPE TUNING FORK CRYSTAL

AB206J




RoHS
Compliant




8.3 x 2.7mm

➤ OUTLINE DRAWING:





Recommended Land Pattern



Dimensions: mm

➤ TAPE & REEL: T = Tape and reel 3,000pcs/reel



Dimensions: mm

ATTENTION: Abracon Corporation's products are COTS – Commercial-Off-The-Shelf products; suitable for Commercial, Industrial and, where designated, Automotive Applications. Abracon's products are not specifically designed for Military, Aviation, Aerospace, Life-dependant Medical applications or any application requiring high reliability where component failure could result in loss of life and/or property. For applications requiring high reliability and/or presenting an extreme operating environment, written consent and authorization from Abracon Corporation is required. Please contact Abracon Corporation for more information.

ABRACON IS
ISO 9001 / QS 9000
CERTIFIED



Visit www.abracon.com for Terms & Conditions of Sale **Revised: 08.30.10**
30332 Esperanza, Rancho Santa Margarita, California 92688
tel 949-546-8000 | fax 949-546-8001 | www.abracon.com