


- through-hole or SMD
- 50mA/24VDC
- single pole/momentary
- 10.000.000 operations lifetime
- IP67 sealing
- temp. range: switch:-40/+160°C  
LED: -30/+85°C  
solid keycap: -40/+65°C  
transparent keycap: -40/+85°C
- actuation force: 2.0, 3.5, 6.5 N

[illegible]

Technical drawing of the 'Kubus' table. The top view shows a square table with an outer side length of 17,75 and an inner side length of 14,6. The side view shows a table with a height of 21 and a width of 16,4.

|   |   |
|---|---|
| 5 | G |
|---|---|

## Mounting

### Actuation force

**LED**

**Cap** frosted white

## Bezel

**TH9** through-hole  
**SH9** surface mount

20  
35  
65  
Q\*

01 blue  
22 green  
42 yellow  
61 white  
82 red  
2242 green/yellow  
8222 red/green  
8242 red/yellow

1KS  
1KBS  
1KCS

**03** grey  
**06** white  
**08** red  
**09** black

|   |   |
|---|---|
| 5 | G |
|---|---|

## Switch

## Mounting

### Actuation force

**Cap**

**Colour code**

## Bezel

**TH9** through-hole  
**SH9** surface mount

20  
35  
65  
Q\*

1KS

00 blue  
02 green  
03 grey  
04 yellow  
06 white  
08 red  
09 black

**03** grey  
**06** white  
**08** red  
**09** black

**Ordering example:** 5GTH93501+1KCS1116+2K09 with illumination  
5GSH965+1KS09+2K03 without illumination  
\*5GTH92082Q with illumination+ 1KCS1116 (quiet version)

See colour codes on our website: [www.mec.dk](http://www.mec.dk)

Dimensions (mm) Unless otherwise specified, all tolerances  $\pm 0.2$