



UNIT: mm




CABLE WHITE PRINT
HI-SPEED USB Revision 2.0 SHIELDED 28AWG/1P+24AWG/2C
E189529 **AWM** STYLE 2725 80°C 30V VW-1 VEGA TECH

PIN ASSIGNMENT:



Electrical test:
1. 100% short, open, miswire test
2. Conduct resistance: 2 Ohm(max)
3. Insulation resistance: 5Mohm(min)
4. dielectric test: DC 300V



⑨	PE BAG	1/10	CLEAR SIZE: 280*330*0.05mm	PRINT BLACK"MADE IN CHINA"+"10PCS"	及印生产周期,有透气孔.
⑧	PE BAG	1	CLEAR SIZE: 130*230*0.05mm	PRINT BLACK"MADE IN CHINA"	及印生产周期,有透气孔.
⑦	TIE	1	BLACK L=100mm		
⑥	IN JACKET	3g	CLEAR LDPE (MOULD NO: NM-027)		
⑤	OUT JACKET	7g	BLACK PVC-45P (MOULD NO: NM-83)		
④	OUT JACKET	6g	BLACK PVC-45P (MOULD NO: NM-40)		
③	CABLE	1	BLACK USB2.0 UI2725 28#/1P+24#/2C+AEB OD: 4.7mm	L=3000 ±15mm	
②	CONN	1	USB2.0 A FEMALE SHELL: NICKEL PIN G/F SHORT TYPE	INSULATOR COLOR: WHITE	
①	CONN	1set	USB2.0 A MALE SHELL: NICKEL PIN G/F 3PCS-TYPE	INSULATOR COLOR: WHITE	
NO.	NAME	Q'TY	SPECIFICATION		

CNC Tech, LLC			
Industrial Cable and Connector Technology			
DRAWED	ZHONGHS	DRAWING NO	
CHECKED		CUSTOMER	
APPROVAL		ITEM NO.	102-1010-BL-00300
DECIDED		DATE	2013-8-23
VERSIONS/EDITION	A/0	PROJECTION	

Cnc Tech, LLC

Industrial Cable and Connector Technology

DRAWN ZHONGHS DRAWING NO

CHECKED CUSTOMER

APPROVAL ITEM NO. 102-1010-BL-00300

DECIDED DATE 2013-8-23

VERSIONS/EDITION A/0 PROJECTION

