

## MINIATURE LAMP (335) Details



| Part #              | 335                             |                       |       |                        |                   |
|---------------------|---------------------------------|-----------------------|-------|------------------------|-------------------|
| Description         | T1 3/4 MID SCREW 28V .04A .34CP |                       |       |                        |                   |
| Bulb Shape          | T-1 3/4                         | Filament              | C-2F  | Base Style             | Midget Screw (E5) |
| Glass Diameter (in) | 0.22                            | MOL <sup>†</sup> (in) | 0.72  | LCL <sup>††</sup> (in) | 0.52              |
| Glass Diameter (mm) | 5.5                             | MOL (mm)              | 18.30 | LCL (mm)               | 13.21             |
| Volts               | 28                              | MSCP <sup>‡</sup>     | 0.34  | Avg Life Hrs           | 4000              |
| Watts               | 1.12                            | Amps                  | 0.04  | RoHS Compliant         |                   |

### <sup>†</sup> MOL (Maximum Overall Length):

The overall length of a lamp, from the top of the shell to the bottom of the base.

### <sup>‡</sup> MSCP (Mean Spherical Candlepower):

Candlepower produced at design volts. Candlepower is increased rapidly with an increase of applied voltage and conversely is reduced rapidly with a reduction of applied voltage.

### <sup>††</sup> LCL (Light Center Length):

The distance from a reference point, usually the bottom of the lamp base, to the center of the light source.