



Search Results

Evaluate

- FAQ's

Design a Solution

- Catalog Cut Sheet
- PDF-CMRPSH15 Pro
- Part Drawings
- PDF-RPSV303C139T ..
- Specification Sheets
- PDF-Power Strips

How to Buy

- Bill of Material
- Favorite Products List
- Locate Distributor

Install & Maintain

- Installation Instructions
- PDF-Panduit POU ..

Home > Product On-Line Catalog > Search Results >

Current refinements (click  to remove) Search Tips 

 Text Search: 'RPSV303C139TL6'

Your search criteria matched only one product, shown below

RPSV303C139TL6



Rack Mount Power Outlet Units

- Mounting brackets and screws included
- Integrated local power monitor display
- Power on indicator - green LED

▪ Part Number	RPSV303C139TL6
▪ RoHS Compliancy Status	Compliant
▪ Part Description	Vertical power strip 30 A, 208V, 24 IEC C-13 and six IEC C-19 receptacles, two 20 A double pole magnetic breaker/switch with integral switch guard, 10' power cord with NEMA L6-30P twist lock plug. UL and c-UL Listed. Dimensions: 66.3"H x 2.0"W x 2.0"D (1683mm x 51mm x 51mm)
▪ Product Type	Vertical Power Outlet Unit
▪ Color	Black
▪ Depth (In.)	2.0
▪ Depth (mm)	51
▪ Height (In.)	66.3
▪ Height (mm)	1683
▪ Width (In.)	2.0
▪ Width (mm)	51
▪ Plug Type	NEMA L6-30P
▪ Pricing Description	Power Strip Vertical 30 AMP With IEC 13 and 19 Outlets and Twist Lock Plug
▪ Min. Order UOM	PC
▪ Min. Order Qty.	1
▪ Voltage	208V
▪ BOM Qty. (# of Pkgs.)	0
▪ Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.