


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

RoHS Compliant ✓

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	CN RELEASE	2/25/08	D.GRIFFIN
B	ECN 4474: ADDED 1.0 FT LENGTH, UPDATED FORMAT, CHANGED NOTES, RoHS	1/7/10	D. CASTRO

"P1"
2X, DB9 MALE
CONNECTOR
GOLD PLATED PINS




WIRING MAP		
"P1"	COLOR	"P2"
1	BLACK	1
2	GRAY	2
3	RED	3
4	GREEN	4
5	BROWN	5
6	BLUE	6
7	ORANGE	7
8	YELLOW	8
9	PURPLE	9
SHELL	DRAIN WIRE	SHELL

PART NUMBER	LENGTH	
	FEET	METERS
CSMNB9MM-1	1.0	0.31
CSMNB9MM-2.5	2.5	.76
CSMNB9MM-5	5.0	1.52
CSMNB9MM-10	10.0	3.05
CSMNB9MM-15	15.0	4.57
CSMNB9MM-25	25.0	7.62
CSMNB9MM-50	50.0	15.24

NOTES:

1. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
2. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM PACKAGING SPEC. PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 .XX = ±.02 .XXX = ±.005	APPROVALS	DATE	 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845		
	DRAWN BY D.FRISIELLO	2/21/08			
	CHECKED BY D.FORTIN	2/21/08	CATEGORY	D-SUBMINIATURE	
	APPROVED BY S.SMITH	2/21/08	PRODUCT DESCRIPTION		CABLE, DB9M/M MOLDED BLK
PROJECTION 	COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321	DWG. NO. CSMNB9MM	REV. B
REF		SCALE: NONE	CAD FILE: CSMNB9MM.SLDDRW		SHEET 1 OF 1