


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

TWIST TIE



NOTES:

- **1. SEE CURRENT CATALOG FOR VARIOUS APPLICATIONS AND TO INDICATE COLOR AND OR PACKAGE QUANTITY.
2. SEE CATALOG FOR A COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
3. TERMINATED WITH (8 POSITION) SHIELDED MODULAR PLUGS AT BOTH ENDS PER T568B.
4. CONSTRUCTED WITH 26AWG STRANDED CAT6 FULLY SHIELDED, TWISTED PAIR LSZH/CM PATCH CABLE.
5. MATERIALS:
 - PLUG: POLYCARBONATE
 - PLUG SHIELD: PLATED CARTRIDGE BRASS
 - CABLE SHIELD: ALUMINUM
 - BOOT: TPE



CABLE COLORS	** = COLOR
INTERNATIONAL GRAY	- -
BLACK	BL
BLUE	BU
RED	RD
YELLOW	YL
GREEN	GR
ORANGE	OR
VIOLET	VL

T568B WIRING SCHEME
PLUG POSITION: CABLE WIRE:
1 RED
2 ORANGE
3 BLACK
4 BLUE
5 WHITE
6 GREEN
7 YELLOW
8 BROWN

SEE SHEET 2 FOR PATCH CORD LENGTHS AND PART NUMBERS

MODEL FILENAME M01438AA_SHLDPLUG_ASSY_26.PRT		SIZE A
DRAWING FILENAME M02085BA_DC01_26E.PRT		
TITLE TX6 10GIG SHIELDED PATCH CORD CUSTOMER DRAWING		
 PANDUIT CORP. TINLEY PARK, IL 60477		I.I. NUMBER
ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED. DIMENSIONAL TOLERANCES ARE: (.X) ± (.XXX) ± .010 (.XX) ± ANGLES ±		PRODUCT SPEC
THIRD ANGLE PROJECTION		WORK INSTRUCTION
DRAWN BY MDJr		SCALE NONE
DATE 8-29-02		PART NO. STP6X** 
CHK'D CEF		DRAWING NO. 02085-01 SHEET 1 OF 2



REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH
4	7-13-07	BJN	EJH	L. ADDED IDENTIFICATION LABELS	02085-01		REGA		
3	5-11-07	BJN	EJH	K. ADDED INT'L GRAY. REMVD OFF WHITE J. STP6X** WAS STP6XAAM**	02085-01		REGA		
2	4-23-07	BJN	EJH	1. ADDED CABLE LENGTHS J. ADDED MODULAR H. REMVD CATEGORY 6 & FOR 10GIG AP. F. ADDED NOTE 2 G. REVD NOTES 3-5 D. ADDED SH2 E. ADDED COLOR TABLE	02085-01		REGA		
1	12-15-04	MDJr	CEF	C. REVISED TITLE OF DRAWING. B. ADDED .5 METER CABLE. A. REMOVED 1.5, 4 AND 9 METER CABLES.	02085-01	CEF	CEF		CEF
R	11-29-04	MDJr	CEF	RELEASED TO PRODUCTION	02085-01	CEF		CEF	CEF

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

TX6 10GIG SHIELDED PATCH CORDS

PANDUIT PART NUMBER	MIN. CABLE LENGTH	PANDUIT PART NUMBER	MIN. CABLE LENGTH
STP6X2**	2 FT.	STP6X0.5M**	0.5 METER
STP6X3**	3 FT.	STP6X1M**	1 METER
STP6X4**	4 FT.	STP6X1.5M**	1.5 METER
STP6X5**	5 FT.	STP6X2M**	2 METERS
STP6X6**	6 FT.	STP6X2.5M**	2.5 METER
STP6X7**	7 FT.	STP6X3M**	3 METERS
STP6X8**	8 FT.	STP6X4M**	4 METERS
STP6X9**	9 FT.	STP6X5M**	5 METERS
STP6X10**	10 FT.	STP6X6M**	6 METERS
STP6X11**	11 FT.	STP6X7M**	7 METERS
STP6X12**	12 FT.	STP6X8M**	8 METERS
STP6X13**	13 FT.	STP6X9M**	9 METERS
STP6X14**	14 FT.	STP6X10M**	10 METERS
STP6X15**	15 FT.	STP6X15M**	15 METERS
STP6X16**	16 FT.	STP6X20M**	20 METERS
STP6X17**	17 FT.	STP6X25M**	25 METERS
STP6X18**	18 FT.	STP6X30M**	30 METERS
STP6X19**	19 FT.	STP6X35M**	35 METERS
STP6X20**	20 FT.	STP6X40M**	40 METERS
STP6X25**	25 FT.		
STP6X30**	30 FT.		
STP6X35**	35 FT.		
STP6X40**	40 FT.		



MODEL FILENAME M01438AA_SHLDPUG_ASSY_26.PRT		SIZE A
DRAWING FILENAME M02085BA_DC01_26E.PRT		
TITLE TX6 10GIG SHIELDED PATCH CORD CUSTOMER DRAWING		
		I.I. NUMBER
 PANDUIT ^R CORP. TINLEY PARK, IL 60477		PRODUCT SPEC
 THIRD ANGLE PROJECTION		WORK INSTRUCTION
ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED. DIMENSIONAL TOLERANCES ARE: (.X) ± (.XXX) ± .010 (.XX) ± ANGLES ±		SCALE NONE
DRAWN BY MDJr	REVIEW DRAWING NUMBERS	PART NO. STP6X** 
DATE 8-29-02		DRAWING NO. 02085-01
CHK'D CEF		SHEET 2 OF 2 

4	7-13-07	BJN	EJH	SEE SHEET 1 FOR REVISIONS	02085-01		REGA			
REV	DATE	BY	CHK	DESCRIPTION	ECN	-	R	CUST	SUP	OTH