


Phone Jack






161-3400-EX

KOBI CONN

Phone Jack



161-3400-EX



PCB Hole Layout

Circuit Diagram

Dimensions: mm.

Tolerance: $\pm .012"$ (.3mm)
(except where noted)

SPECIFICATIONS

Type:	3.5mm mono jack with switch
Contact resistance:	30mΩ max.
Insulation resistance:	100MΩ min. @ 500VAC
Breakdown voltage:	500VAC for 1 minute
Knurled nut:	Ø6 x .5mm
RoHS Compliant by Exemption	

Date Last Revised: 08/19/09

Available from Mouser Electronics
1-800-346-6873 / www.mouser.com

KC-301374

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.

161-3400-EX

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[161-3400-EX](#)