




ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

SPC-F005.DWG

REVISIONS

DOC. NO. SPC-F005 * Effective: 7/8/02 * DCP No: 1398

DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
1116	B	Drawing was CCS-DY-****	JWM	5/25/01	JC	6/20/01	JC	6/20/01
1369	C	Bulk items added; dwg updated	JWM	10/29/02	JC	10/29/02	JC	10/29/02



NOTES:

1. Material: Electro-Tin Plated Copper
Nylon 6/6 Sleeve
2. Continuous Operating Temp: -40°F to 221°F [-40°C to 105°C]
3. UL Listed and CSA Certified for 600V building wire and 1,000V signs and lighting fixtures (luminaries)

SPC Type No.	Pkg. Qty.	Wire Range (AWG)	Length	Thickness	Barrel Length	Barrel I.D.	Maximum Insulation Diameter	Color
CCS-DY-1010	50	12 ~ 10	1.15	.040	.25	.135	.250	Yellow
SPC3828	500							
CCS-DY-1414	50	16 ~ 14	1.00	.030	.25	.090	.170	Blue
SPC3827	500							
CCS-DY-1818	100	22 ~ 18	1.00	.030	.25	.070	.145	Red
SPC3826	1000							
CCS-DY-2222*	100	26 ~ 24	.88	.020	.12	.030	.093	Yellow
SPC3825*	1000							

*NOT UL or CSA Certified



DISCLAIMER:
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

TOLERANCES:

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.

DRAWN BY:	DATE:
JC	3/4/91
CHECKED BY:	DATE:
John Cole	111/21/91
APPROVED BY:	DATE:
J Liska	11/21/91

DRAWING TITLE:

Nylon Insulated "Sure-Grip" Butt Connectors

SIZE	DWG. NO.	ELECTRONIC FILE	REV
A	TA-371	TA-371.dwg	C
SCALE: NTS		U.O.M.: INCHES [mm]	SHEET: 1 OF 1