





CONNECTION ELEMENTS

ISO-K Clamp Flange Components

CLAMP	DN ... ISO-K	Part No.	A	B	C	Set of
Steel zinc plated 103/–	63-250	212-225	60	17	27	4 pcs.
	320-500	212-226	78	27	39	4 pcs.
	630	212-227	88	31	49	4 pcs.
Stainless steel 316/–	63-250	212-228	61	18	28	4 pcs.
	320-630	212-240	82	29	47	4 pcs.



CLAW	DN ... ISO-K	Part No.	A	B	C	Set of
Clamping flange / base plate	63-100	212-231	22.5	35	13.9	4 pcs.
	160-250	212-232	23	35	13.9	4 pcs.
	320-500	212-233	36.5	50	20.6	4 pcs.
	630	212-234	41.5	55	25.6	4 pcs.
Clamping flange/ base plate with groove	63-100	212-235	18.6	30	10	4 pcs.
	160-250	212-236	19	35	10	4 pcs.
	320-500	212-237	31	45	15	4 pcs.
	630	212-233	36.5	50	20.6	4 pcs.
Clamping flange with groove / base plate	63-100	212-247	20.6	30	12	4 pcs.
	160-250	212-248	21.1	35	12	4 pcs.
	320-500	212-249	33.9	45	18	4 pcs.
	630	212-233	36.5	50	20.6	4 pcs.



Steel zinc plated 103/–



GLOBAL HEADQUARTERS:

Two Technology Place, East Syracuse, NY 13057 USA
Tel: +1.315.434.1100 Fax: +1.315.437.3803 E-mail: reachus@inficon.com

UNITED STATES FRANCE GERMANY LIECHTENSTEIN SWITZERLAND UNITED KINGDOM CHINA JAPAN KOREA SINGAPORE TAIWAN

Visit our website for contact information and other sales offices worldwide. www.inficon.com
Due to our continuing program of product improvements, specifications are subject to change without notice.
qiba08e1 (2004-04) ©2003 INFICON Inc.