



main menu



home
 test & measurement
 products
 skills
 download

online catalogue T&M

clamp-type test probes
 crocodile clips
 test probes
 oscilloscope test probes
 measuring leads
 plugs
 sockets
 ▶ 2 mm system
 ▶ 2 mm safety system
 ▶ 4 mm system
 ▶ 4 mm safety system

sets
 miscellaneous

company

portrait
 corporate association
 location maps
 fairs and exhibitions
 jobs
 imprint
 terms and conditions

Home ▶ sockets ▶ sockets ▶ SEB 2600 G M4

SEB 2600 G M4

datasheet for SEB 2600 G M4
 article number: 972354188



View Full-Size Image



search online catalogue

Search

Search

Messetermine

SPS/IPC/DRIVES
 24. 11. 2016 - 24.
 11. 2016

QR-Code



product description:	order number: 972 354-188
description:	Safety built-in socket, 4 mm diameter, touch-protected, M 4 thread and solder connection, gold-plated brass. For installation into switch panels and equipment chassis with wall thicknesses up to 6 mm. Installation hole: 12.2 mm diameter, Tightening torque: 50 Ncm Accessory: assembly tool MW SEB
typ:	SEB 2600 G M4 gelb/gruen yellow/green
system:	4 mm safety system
order number:	972 354-188
color	
other color versions:	
technical data	
measurement category acc. to IEC 61010:	CAT III
type of contact:	4 mm socket (unsprung)
type of termination:	M4 thread, solder
rated voltage:	AC/DC 1000 V
rated current:	32 A
Please consider derating curve!	
contact resistance:	5 mOhm
mounting:	screw
material	
contact material:	brass
contact surface material:	gold
housing material:	PA
connecting nut material:	brass nickel - plated
environmental conditions:	
temperature range:	-40 °C to +80 °C
inflammable class:	
housing (basic material):	UL 94 V - 2
drawing	

