



CATALOGUE LISTING	ISSUE	STYLE	SUPPLY VOLTAGE	SENSING RANGE			OUTPUT NOMINAL	MAXIMUM COIL RESISTANCE AT 70°C	No. OF TURNS	SECONDARY CONNECTION	CABLE LENGTH
				NOMINAL	MAXIMUM DC	MAX AC Pk					
CSNS300M	1	1	±12V TO ±15V	300A	600A	600A	150mA	34Ω	2000	INTEGRAL CONNECTOR	
CSNS300P	1	2				PCB MOUNTING PINS					
CSNS300F	1	3				CONNECTOR ON RIBBON CABLE				200 ±5 (7.9 ±0.1)	
CSNS300F-001	2	4								330 (13)	
CSNS300F-002	2									64 (2.5)	
CSNS300M-001	1	5	±18V		825A		31Ω		INTEGRAL CONNECTOR		
CSNS300M-500	1	1									

- NOTES:-
1. HOUSING MATERIAL IS GLASS FILLED PBT.
 2. OPERATING TEMPERATURE : -40°C TO +85°C.
 3. PRIMARY CONNECTION : THROUGH HOLE.


STYLE 1




STYLE 4




STYLE 5



STYLE 2



STYLE 3



DIMENSIONS ARE IN MILLIMETRES [INCHES]			FOR EXPLANATION OF DIMENSIONS, TOLERANCES, NOTES ETC. SEE B.S. 308			THIRD ANGLE PROJECTION			THE COPYRIGHT OF THIS DRAWING IS THE PROPERTY OF HONEYWELL LTD. THE DRAWING IS SUPPLIED IN CONFIDENCE AND MUST NOT BE USED FOR ANY PURPOSE OTHER THAN THAT FOR WHICH IT IS SUPPLIED		
MODIFY ON PRO-ENGINEER SYSTEM ONLY											
DRAWN			TITLE			300A NULL BALANCE CURRENT SENSOR			SHT 1 OF 1		
DRAFTING CHECK									DRAWING NUMBER		
DESIGN CHECK									MTG-CSN-320		
AUTHORISATION									SCALE		
DIMENSIONS SPECIFIED ARE TO BE MET BEFORE PROTECTIVE COATINGS ARE APPLIED			TOLERANCES UNLESS OTHERWISE STATED			±0.2			DO NOT SCALE PRINT		
						Honeywell			A2 FORMAT		
									ISSUE		
									4		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[CSNS300M-001](#) [CSNS300M-002S](#)