

2014



Professional Screwdrivers & Nut Drivers



Screwdrivers & Nut Drivers



Wiha SoftFinish® CushionGrip Screwdrivers

Description	Page
 SoftFinish® Slotted/Phillips Drivers	4-8
Torx®/TR Torx® Screwdrivers	10-11
Stubby Slotted/Phillips Drivers	6-7
SoftFinish® TorxPlus® Drivers	11
SoftFinish® Pozidriv® Drivers	6
SoftFinish® Square Drivers	6
 SoftFinish® MagicSpring Drivers	9
 SoftFinish® MagicRing Drivers	12-13
 Measuring Scale Screwdrivers	8

Wiha Screw Holding Screwdrivers

Description	Page
 Screw Holding Screwdrivers	9

Wiha Stainless Steel Cushion Grip Drivers

Description	Page
 Slotted Drivers	14
Phillips Drivers	14
Torx Drivers	14
Pozidriv Drivers	14

Wiha ACR® Screwdrivers

Description	Page
 ACR® Slotted/Phillips Drivers	15

Wiha 3K Series Screwdrivers

Description	Page
 3K Series Slotted/Phillips	16-17
3K Series Torx Drivers	17-18
3K Series Pozidriv® Drivers	17
3K Series Bit Holders	16
3K Series Hex Inch & Metric	18-19

Wiha Drive-Loc VI Tools

Description	Page
 Drive-Loc VI Handles	20
 Drive-Loc VI Blades	20-21

Wiha Drive-Loc VI Sets

Description	Page
 Drive-Loc VI Blade Sets	22

Wiha Topra Ratchet Blade Set

Description	Page
 Topra Ratchet Blade Set	22

Wiha MicroFinish Non-Slip Grip Drivers

Description	Page
 MicroFinish Slotted Drivers	23-24
MicroFinish Phillips Drivers	23-24
MicroFinish Torx Drivers	25
MicroFinish Bit Holder	24

Wiha Powerhandle Screwdrivers

Description	Page
 Powerhandle Torx® Drivers	25

Wiha Protturn Screwdrivers

Description	Page
 Protturn Torx® Drivers	26

Wiha Dynamic Screwdrivers

Description	Page
 Dynamic Slotted/Phillips Drivers	27

Wiha Square Handle Screwdrivers

Description	Page
 Slotted & Phillips Drivers	28

Wiha Offset Screwdrivers

Description	Page
 Slotted & Phillips Offset Drivers	28
 TORX Offset Screwdrivers	28


Wiha Magnetizer/Demagnetizer



Description	Page
Magnetizer/Demagnetizer	27

Wiha Precision Screwdrivers

Description	Page
-------------	------



Precision Slotted Drivers	29-30
Precision Phillips Drivers	30
Precision Pozidriv® Drivers	31
Precision Hex Drivers	31
Precision Ball End Drivers	32
Precision Torx® Drivers	33
Precision Pentalobe Drivers	33
Precision Chip Lifters	29
Precision Screwdriver Sets	32-33

Wiha Precision PicoFinish Drivers


Description	Page
-------------	------



PicoFinish Screwdrivers	34-36
Slotted, Phillips, Torx, TorxPlus®, Hex, MagicSpring, Ball End Hex, Chip Lifter	

Wiha Protturn Precision Screwdrivers

Description	Page
-------------	------



Protturn Precision Screwdrivers	37
Slotted & Phillips	
Protturn Precision Blade Sets	37

Wiha ESD Safe Precision Handles/Blades


Description	Page
-------------	------



SYSTEM 4 Handles/Blades	38-39
SYSTEM 4 Sets	40-41

Wiha ESD Safe Precision Handle & Blades

Description	Page
-------------	------



SYSTEM 4 Drive-Loc Handle & Blades	39
SYSTEM 4 Drive-Loc Set	39

Wiha Nut Drivers

Description	Page
-------------	------

SoftFinish® Nut Drivers	42-43
Hollow Shaft Nut Drivers	44
T-handle Nut Drivers	45
Drive-Loc VI Blades	46
Precision Nut Drivers	47
PicoFinish® Nut Drivers	48
SYS 4 Nut Driver Blades/Sets	48-49

Wiha Insulated Screwdrivers



Insulated Slotted
 Insulated Phillips
 Insulated Terminal Block Xeno
 Insulated Square Drivers
 Insulated Hex Metric Drivers
 Insulated Torx® Drivers
 Insulated Nut Drivers
 Insulated Torque Drivers
 Insulated *SlimLine* Drivers
 Catalog 99919.wo

Wiha ESD Safe Screwdrivers

ESD Safe SoftFinish® Drivers
 Slotted/Phillips/Torx

ESD Safe Precision Drivers
 Slotted/Phillips/Torx®/
 TorxPlus®/Hex/Nut Drivers/
 Chip Lifter

ESD Safe Ceramic Drivers

ESD Safe SYSTEM 4
 Handles/Blades/Sets

ESD Safe Drive-Loc VI
 Handles/Blades/Sets



Catalog 99945.wo

Wiha SoftFinish® Handle - Ergonomic Cushion Grip

The Wiha SoftFinish® Handle: Featuring advanced technology dual material molding.

A remarkable improvement in handle design, comfort and performance.

The SoftFinish® ergonomic shape allows maximum torque and user comfort.

Wiha exclusive "SoftFinish® Zone" features solid molded core with soft outer cushion grip. Requires less force, yet achieves 40% more torque than conventional handles

All blades are made of Wiha's exclusive formula chrome-vanadium-molybdenum tool steel, super hardened & hard chrome finish for unmatched durability

Wiha tips are precision machined to exact tolerances for a perfect fit every time

Handle is molded directly onto the blade for a permanent bond. Large optimized handle diameter allows higher torque with less user hand fatigue

Wiha SoftFinish® Extra Heavy Duty



530 Slotted Screwdriver, With Wiha-SoftFinish® Handle & Solid Metal Cap Hex blade extending through handle manufactured from high alloy chrome-vanadium-molybdenum steel, hardened, hard chromed. Wiha-Chromtop finish on tips. Wiha-SoftFinish® handle, multi-component. Hex bolster for additional torque.

Item No.	mm	Inch	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
53010*	3.5	.139	75	3.0	0.6	.024	186	7.3	.16	10
53015*	4.5	.177	90	3.5	0.8	.031	201	7.9	.17	10
53020	5.5	.196	100	3.9	1.0	.039	213	8.4	.23	10
53025	6.5	.255	125	5.0	1.2	.047	238	9.4	.33	10
53027	8.0	.315	150	5.9	1.2	.047	268	10.6	.56	10
53035	10.0	.393	175	7.0	1.6	.063	293	11.6	.58	10
53040	12.0	.472	200	8.0	2.0	.079	318	12.5	.76	10

*No Hex Bolster



531 Phillips Screwdriver, With Wiha-SoftFinish® Handle & Solid Metal Cap Hex blade extending through handle manufactured from high alloy chrome-vanadium-molybdenum steel, hardened, hard chromed. Wiha-Chromtop finish on tips. Wiha-SoftFinish® handle, multi-component. Hex bolster for additional torque.

Item No.	Size	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
53110	1	80	3.1	5.0	13/64	186	7.3	.20	10
53115	2	100	3.9	6.0	1/4	213	8.4	.32	10
53120	3	150	5.9	8.0	5/16	268	10.6	.56	10



53090 5 Piece Slotted & Phillips Set - Extra Heavy Duty


Item No.		 mm	 mm		 Size	 mm	 lbs.
53090	53020	5.5	100	53110	1	80	1.85
	53025	6.5	125	53115	2	100	
	53027	8.0	150				



53097 7 Piece Slotted & Phillips Set - Extra Heavy Duty

Item											
No.		mm	mm		Size	mm		lbs.			
53097	53020	5.5	100	53110	1	80		3.15			
	53025	6.5	125	53115	2	100					
	53027	8.0	150	53120	3	150					
	53035	10.0	175								

Wiha SoftFinish® Extra Heavy Duty



53096 6 Piece Slotted & Phillips Set - Extra Heavy Duty

Item No.	Slotted	mm	mm	Phillips	Size	mm	lbs.
53096	53010	3.5	75	53110	1	80	1.69
	53015	4.5	90	53115	2	100	
	53020	5.5	100				
	53025	6.5	125				



53099 10 Piece Slotted & Phillips Set - Extra Heavy Duty

Item No.	Slotted	mm	mm	Phillips	Size	mm	lbs.
53099	53010	3.5	75	53110	1	80	4.20
	53015	4.5	90	53115	2	100	
	53020	5.5	100	53120	3	150	
	53025	6.5	125				
	53027	8.0	150				
	53035	10.0	175				
	53040	12.0	200				



53075 5 Piece Slotted & Phillips Set - Extra Heavy Duty

Item No.	Slotted	mm	mm	Phillips	Size	mm	lbs.
53075	53015	4.5	90	53110	1	80	1.53
	53020	5.5	100	53115	2	100	
	53025	6.5	125				

Wiha SoftFinish® Heavy Duty Screwdriver



308 Slotted Screwdriver, Wiha-SoftFinish® Cushion Grip Handle

Hex blade high alloy CVM steel, hardened, hard chromed. Wiha-Chromtop finish on tips. Hex bolster for additional torque (No Bolster 30813 & 30814)

Item No.	Slotted	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
30813		3.5	.137	75	2.9	0.6	.023	186	7.3 .16 10
30814		4.5	.177	90	3.5	0.8	.032	201	7.9 .17 10
30815		5.5	.216	100	3.9	1.0	.039	213	8.4 .19 10
30816		6.5	.216	100	3.9	1.2	.047	213	8.4 .22 10
30817		6.5	.255	125	5.0	1.2	.047	238	9.4 .23 10
30820		7.0	.275	125	5.0	1.1	.043	238	9.4 .23 10
30825		8.0	.315	150	5.9	1.2	.047	271	10.7 .37 10
30830		10.0	.393	175	7.0	1.6	.063	296	11.7 .40 10
30835		12.0	.472	200	8.0	2.0	.079	321	12.6 .58 10



312 Phillips Screwdriver, Wiha-SoftFinish® Cushion Grip Handle

Hex blade high alloy CVM steel, hardened, hard chromed.

Wiha-Chromtop finish on tips. Hex bolster for additional torque.

Item No.	Phillips	Size	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
31201		1	80	3.1	5.0	3/16	186	7.3	.13	10
31202		2	100	3.9	6.0	7/32	213	8.4	.21	10
31203		3	150	5.9	8.0	5/16	271	10.7	.37	10



30892 5 Piece Slotted & Phillips Set

Item No.	Slotted: 5.5, 7.0, 8.0mm	lbs.
30892	Phillips: #1, 2	1.33

30896 6 Piece Slotted & Phillips Set

Item No.	Slotted: 3.5, 4.5, 5.5, 7.0mm	lbs.
30896	Phillips: #1, 2	1.34



30898 8 Piece Slotted & Phillips Set

Item No.	Slotted: 5.5, 6.5, 7.0, 8.0, 10.0mm	lbs.
30898	Phillips: #1, 2, 3	2.52

Wiha SoftFinish® Handle - Standard Series



[SHOP](#)

302 Slotted Screwdriver, With Wiha-SoftFinish® Handle

Round blade, high alloy CVM, hardened, hard chromed.

Wiha-Chromtop tips. Handle, multi-component, cushion grip.

Item	+	+	+	+	+	+	+	+	+	+
No.	mm	Inch	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
30202*	2.0	.079	65	2.6	0.4	.016	169	6.7	.05	10
30203*	2.5	.098	75	3.0	0.4	.016	179	7.0	.05	10
30204*	3.0	.118	80	3.1	0.5	.020	184	7.2	.06	10
30205*	3.0	.118	100	3.9	0.5	.020	204	8.0	.06	10
30206*	3.0	.118	150	5.9	0.5	.020	254	10.0	.07	10
30208*	3.0	.118	200	8.0	0.5	.020	304	12.0	.07	10
30210*	3.5	.139	100	3.9	0.6	.024	204	8.0	.07	10
30212*	3.5	.139	200	8.0	0.6	.024	304	12.0	.09	10
30215*	4.0	.157	100	3.9	0.8	.031	211	8.3	.11	10
30217*	4.0	.157	150	5.9	0.8	.031	261	10.3	.12	10
30216*	4.0	.157	200	8.0	0.8	.031	311	12.2	.14	10
30218*	4.5	.187	80	3.1	0.8	.031	191	7.5	.11	10
30211*	4.5	.187	125	5.0	0.8	.031	236	9.3	.12	10
30219*	4.5	.187	150	5.9	0.8	.031	261	10.2	.12	10
30220*	5.5	.216	125	5.0	1.0	.039	236	9.3	.15	10
30238*	5.5	.216	300	11.8	1.0	.039	411	16.1	.24	10
30221*	5.5	.216	200	8.0	1.0	.039	311	12.2	.20	10
30222*	6.0	.250	100	3.9	1.2	.047	218	8.6	.17	10
30223	6.5	.255	100	3.9	1.0	.039	218	8.6	.20	10
30225	6.5	.255	150	5.9	1.2	.047	268	10.6	.22	10
30226	6.5	.255	200	8.0	1.2	.047	318	12.5	.22	10
30227	8.0	.315	150	5.9	1.2	.047	274	10.8	.29	10
30230	8.0	.315	175	7.0	1.2	.047	299	11.8	.30	10
30232	8.0	.315	300	11.8	1.2	.047	424	16.7	.36	10
30235	10.0	.393	200	8.0	1.6	.063	324	12.8	.36	10
30236	12.0	.472	250	9.8	2.0	.078	374	14.7	.52	10

*Cabinet Tips



[SHOP](#)

302 Stubby Slotted Screwdriver, With Wiha-SoftFinish® Handle

Item	+	+	+	+	+	+	+	+	+	+
No.	mm	Inch	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
30239	4.0	.157	25	1.0	0.8	.031	75	2.95	.09	10
30255	5.5	.216	25	1.0	1.0	.039	75	2.95	.09	10
30265	6.5	.255	25	1.0	1.2	.047	75	2.95	.10	10



[SHOP](#)

313 Pozidriv® Screwdriver, With Wiha-SoftFinish® Handle

Round blade high alloy chrome-vanadium-molybdenum steel, hardened, hard chromed. Wiha-Chromtop finish on tips. Wiha-SoftFinish® handle, multi-component, cushion grips.

Item	+	+	+	+	+	+	+	+	+	+
No.	Size	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.	
31305	0	60	2.4	3.0	.118	164	6.5	.06	10	
31310	1	80	3.1	4.5	.177	191	7.5	.11	10	
31312	1	200	8.0	4.5	.177	311	12.3	.15	10	
31315	2	100	3.9	6.0	.236	218	8.6	.20	10	
31320	3	150	5.9	8.0	.315	274	10.8	.33	10	



[SHOP](#)

311 Phillips Screwdriver, With Wiha-SoftFinish® Handle

Round blade, high alloy CVM steel, hardened, hard chromed.

Wiha-Chromtop tips. Handle, multi-component, cushion grip.

Item	+	+	+	+	+	+	+	+	+	+
No.	Size	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.	
31105	0	60	2.4	3.0	.118	164	6.5	.06	10	
31110	1	80	3.1	4.5	.177	191	7.5	.11	10	
31112	1	200	8.0	4.5	.177	311	12.3	.15	10	
31114	1	300	12.0	4.5	.177	411	16.2	.18	10	
31115	2	100	3.9	6.0	.236	218	8.6	.20	10	
31117	2	200	8.0	6.0	.236	318	12.5	.25	10	
31118	2	300	12.0	6.0	.236	418	16.5	.30	10	
31120	3	150	5.9	8.0	.315	274	10.8	.33	10	
31125	4	200	8.0	10.0	.393	323	12.7	.51	10	



[SHOP](#)

311 Stubby Phillips Screwdriver, With Wiha-SoftFinish® Handle

Item	+	+	+	+	+	+	+	+	+	+
No.	Size	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.	
31135	1	25	1.0	4.5	.177	75	3.0	.09	10	
31140	2	25	1.0	6.0	.236	75	3.0	.10	10	

Wiha SoftFinish® Handle - Square Drivers



[SHOP](#)

358 Square Screwdriver, With Wiha-SoftFinish® Handle

Round blade high alloy chrome-vanadium-molybdenum steel, hardened, hard chromed. Wiha-Chromtop finish on tips. Wiha-SoftFinish® handle, multi-component, cushion grips.

Item	+	+	+	+	+	+	+	+	+	+
No.	Size	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.	
35800	0	80	3.1	4.0	5/32	191	7.5	.11	10	
35801	1	100	3.9	4.5	5/32	210	8.2	.12	10	
35802	2	150	5.9	6.0	1/4	268	10.5	.19	10	
35803	3	150	5.9	6.0	1/4	268	10.5	.22	10	



[SHOP](#)

35894 4 Piece SoftFinish® Square Tip Screwdriver Set

Round blade high alloy chrome-vanadium-molybdenum steel, hardened, hard chromed. Wiha-Chromtop finish on tips.

Wiha-SoftFinish® handle, multi-component, cushion grips.

Item									
No.		Size	mm		Size	mm			lbs. .77
35894	35800	0	80	35802	2	150			
	35801	1	100	35806	3	150			

Wiha SoftFinish® Handle - Stubby Sets



[SHOP](#)

31190 2 Piece Slotted & Phillips Stubby Screwdriver Set

Item No.	Slotted mm	Phillips mm	Item No.	Slotted mm	Phillips mm	Weight lbs. .24
31190	30239	4.0 25	31135	1	25	



[SHOP](#)

31191 2 Piece Slotted & Phillips Stubby Screwdriver Set

Item No.	Slotted mm	Phillips mm	Item No.	Slotted mm	Phillips mm	Weight lbs. .24
31191	30265	6.5 25	31140	2	25	



[SHOP](#)

31192 2 Piece Phillips Stubby Screwdriver Set

Item No.	Size mm	Item No.	Size mm	Weight lbs. .24
31192	31135 1 25	31140	2 25	



[SHOP](#)

31193 2 Piece Slotted Stubby Screwdriver Set

Item No.	Slotted mm	Item No.	Slotted mm	Weight lbs. .24
31193	30239 4.0 25	30265	6.5 25	



[SHOP](#)

30294 6 Piece Slotted & Phillips Screwdriver Set

Item No.	Slotted mm	Phillips mm	Item No.	Slotted mm	Phillips mm	Weight lbs.
30294	30215 4.0 100	31110 1 80				1.29
	30225 6.5 150	31115 2 100				
	30227 8.0 150					
	*30239 4.0 25					

*Stubby screwdriver with Wiha SoftFinish® handle

Wiha SoftFinish® Handle - Standard Series



Inch & Metric scale on #2 Phillips
Perfect for measuring small parts on the go

[SHOP](#)

30295 5 Piece Slotted & Phillips Screwdriver Set

Item No.	Slotted mm	Phillips mm	Item No.	Slotted mm	Phillips mm	Weight lbs.
30295	30205 3.0 100	31110 1 80				1.02
	30215 4.0 100	31137 2 100				
	30225 6.5 150					



[SHOP](#)

30298 8 Piece Slotted & Phillips Screwdriver Set

Item No.	Slotted mm	Phillips mm	Item No.	Slotted mm	Phillips mm	Weight lbs.
30298	30205 3.0 100	31110 1 80				1.87
	30215 4.0 100	31115 2 100				
	30220 5.5 125	31120 3 150				
	30225 6.5 150					
	30230 8.0 175					



[SHOP](#)

30297 12 Piece Slotted & Phillips Screwdriver Set

Item No.	Slotted mm	Phillips mm	Item No.	Slotted mm	Phillips mm	Weight lbs.
30297	30205 3.0 100	31105 0 60				2.48
	30215 4.0 100	31110 1 80				
	30220 5.5 125	*31140 2 25				
	30225 6.5 150	31115 2 100				
	*30265 6.5 25	31120 3 150				
	30230 8.0 175					
	30235 10 200					

*Stubby screwdriver with Wiha SoftFinish® handle

Wiha SoftFinish® Handle - Standard Series



30291 6 Piece Slotted, Phillips & Square Cushion Grip Drivers

Item	Slotted: 4.5, 6.5mm	lbs.
No.	Phillips: 1, 2	1.00
30291	Square: 1, 2	

[SHOP](#)

30290 10 Piece Slotted, Phillips & Square Cushion Grip Drivers

Item	Slotted: 3.0, 3.5, 4.5, 6.5mm	lbs.
No.	Phillips: 0, 1, 2	1.54
30290	Square: 1, 2, 3	


[SHOP](#)

30276 7 Piece Slotted & Phillips Set CVM steel, hardened, hard chromed. Wiha-Chromtop tips. Handle, multi-component, cushion grip.

Item No.	Tip Size	Blade	Tip Style	lbs.
30816	1/4	4" Hex	Keystone	1.87
30825	5/16	6" Hex	Keystone	
30218	3/16"	3" Round	Cabinet	
30219	3/16"	6" Round	Cabinet	
30222	1/4"	4" Round	Cabinet	
31110	#1	3" Round	Phillips	
31115	#2	4" Round	Phillips	


[SHOP](#)

30299 20 Piece Slotted, Phillips, TORX®, Square & Pozidriv® Set

Item	Slotted: 3.0, 4.0, 5.5, 6.5, 8.0mm	lbs.
No.	Phillips: 0, 1, 2	
30299	TORX®: T6, T8, T10, T15, T20, T25, T30	3.27
	Square: 1, 2, 3	
	Pozidriv®: 1, 2	

Wiha SoftFinish® CushionGrip Drivers With Inch & MM Scale on Blades



Inch and Metric

- Perfect for measuring small parts on the go
- Quickly check drilled hole depths & diameters
- Patented design with permanent laser marking
- Chrome-vanadium-molybdenum tool steel shafts
- Hardened & tempered for long life performance
- Hard chrome surfaces for incredible wear resistance
- Precision machined exact fit tips



302 Measuring Scale Slotted Screwdriver, With Wiha-SoftFinish® Cushion Grip Handle Inch & Metric scales

Item	mm	Inch	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
30237	5.5	7/32	125	5.0	1.0	.039	236	9.3	.16	10



311 Measuring Scale Phillips Screwdriver, With Wiha-SoftFinish® Cushion Grip Handle Inch & Metric scales

Item	Size	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
31137	2	100	3.9	6.0	1/4	218	8.6	.21	10



31194 2 Pc Slotted & Phillips Measuring Scale Screwdriver Set

Item	mm	mm	Size	mm	lbs.
31194	30237	5.5 125	31137	2 100	.37

Wiha SoftFinish® Slotted Spanner Nut Drivers



305 Slotted Spanner Nut Drivers, With Wiha-SoftFinish® Handle

Round blade high alloy chrome-vanadium-molybdenum steel, hardened, hard chromed. Wiha-Chromtop finish on tips. Wiha-SoftFinish® handle, multi-component, cushion grips.

Item	Size	mm	Inch	mm	mm	mm	Inch	pkg.
30517	M1.7	80	3.1	0.5	4.0	184	7.2	1
30520	M2	80	3.5	1.0	4.5	184	7.2	1
30523	M2.3	90	3.5	1.0	5.0	201	7.9	1
30526	M2.6	100	3.9	1.2	5.5	201	7.9	1
30530	M3	100	3.9	1.2	6.0	211	8.3	1
30535	M3.5	100	3.9	1.4	7.0	218	8.6	1
30540	M4	100	3.9	1.4	8.0	218	8.6	1
30550	M5	125	4.9	2.0	10.0	243	9.6	1
30560	M6	125	4.9	2.5	11.0	243	9.6	1
30580	M8	150	5.9	3.0	14.0	274	10.8	1

Wiha Screw Holding Screwdrivers



Clamping sleeve
to hold screw

[SHOP](#)

398 Slotted Screw Holding Screwdriver, With Wiha-SoftFinish®

Handle Blade CVM steel, hardened, black finish. Clamping sleeve polyamide. Wiha-SoftFinish® handle cushion grip, impact resistant.

Item No.	↓	↓	↓	↓	↓	↓	↓	↓
	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
39825	2.5	.10	75	3.0	160	6.3	.09	10
39830	3.0	.12	100	3.9	195	7.6	.19	10
39840	4.0	.16	125	5.0	230	9.0	.27	10
39850	5.0	.20	150	5.9	265	10.4	.27	10
39860	6.0	.24	175	6.9	290	11.4	.32	10



Clamping sleeve
to hold screw

[SHOP](#)

397 Phillips Screw Holding Screwdriver, With Wiha-SoftFinish®

Handle Blade CVM steel, hardened, black finish. Clamping sleeve polyamide. Wiha-SoftFinish® handle cushion grip, impact resistant.

Item No.	+	+	+	+	+	+	+	+
	Size	mm	Inch	mm	Inch	lbs.	pkg.	
39700	0	100	3.9	195	7.6	.13	10	
39701	1	125	5.0	230	9.0	.27	10	
39702	2	175	7.0	290	11.4	.32	10	



[SHOP](#)

39892 5 Piece Screw Holding Slotted & Phillips Screwdriver Set

Item No.		
39892	Slotted: 2.5x75mm, 3.0x100mm, 4.0x125mm	lbs. 1.35
	Phillips: 0x100mm, 1x125mm	



[SHOP](#)

39896 8 Piece Screw Holding Slotted & Phillips Screwdriver Set

Item No.		
39896	Slotted: 2.5x75mm, 3.0x100mm, 4.0x125mm, 5.0x150mm, 6.0x175mm	lbs. 1.80
	Phillips: 0x100mm, 1x125mm, 2x175mm	

Wiha Screw Holding TORX® Tools

- Laser welded assembly
- Holds screws securely
- Won't damage screws
- Doesn't weaken tool
- Exact fit tips
- Hardened tool steel blades
- Holds standard Torx screws*



[SHOP](#)

362 MagicSpring Screw Holding TORX® Screwdriver, With Wiha-SoftFinish® Handle

Round blade high alloy chrome-vanadium-molybdenum steel, hardened, hard chromed. Wiha-Chromtop finish on tips. Wiha-SoftFinish® handle, multi-component, cushion grips.

Item No.	+	+	+	+	+	+	+	+
	Size	mm	Inch	mm	Inch	mm	Inch	lbs.
36202	T6	60	2.4	3.5	.139	164	6.5	.07
36203	T7	60	2.4	3.5	.139	164	6.5	.07
36207	T8	60	2.4	3.5	.139	164	6.5	.07
36234	T9	60	2.4	4.0	.157	171	6.7	.11
36244	T10	80	3.1	4.0	.157	191	7.5	.11
36249	T15	80	3.1	4.0	.157	191	7.5	.11
36254	T20	100	3.9	4.0	.157	211	8.3	.16
36256	T25	100	3.9	4.5	.177	211	8.3	.17
36257	T27	115	4.5	5.5	.216	233	9.2	.20
36258	T30	115	4.5	6.0	.236	233	9.2	.21



[SHOP](#)

36290 Set 6 Pcs. MagicSpring Screw Holding TORX® SoftFinish Screwdrivers Round blade high alloy chrome-vanadium-molybdenum steel, hardened, hard chromed. Wiha-Chromtop finish on tips. Wiha-SoftFinish® handle, multi-component, cushion grips. Molded on.

Item No.	+	+	+	+	+	+
	Size	mm	Size	mm	lbs.	
36290	36207	T8 60	36254	T20 100	.98	
	36244	T10 80	36256	T25 100		
	36249	T15 80	36258	T30 115		

*MagicSpring tools will hold Torx® screws made to CamCar Textron Torx® specifications

Wiha TORX® SoftFinish® Screwdrivers




362 TORX® Screwdriver, With Wiha-SoftFinish® Handle

Round blade high alloy chrome-vanadium-molybdenum steel, hardened, hard chromed. Wiha-Chromtop finish on tips.

Wiha-SoftFinish® handle, multi-component, cushion grips.

Item No.	Size	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
36264	T5	60	2.4	2.5	.098	164	6.5	.05	10
36266	T6	60	2.4	3.5	.139	164	6.5	.06	10
36268	T7	60	2.4	3.5	.139	164	6.5	.06	10
36270	T8	60	2.4	3.5	.139	164	6.5	.06	10
36272	T9	60	2.4	4.0	.157	171	6.7	.10	10
36274	T10	80	3.1	4.0	.157	191	7.5	.11	10
36276	T15	80	3.1	4.0	.157	191	7.5	.11	10
36278	T20	100	3.9	4.0	.157	211	8.3	.11	10
36280	T25	100	3.9	4.5	.177	211	8.3	.12	10
36282	T27	115	4.5	5.5	.216	233	9.2	.19	10
36284	T30	115	4.5	6.0	.236	233	9.2	.20	10
36286	T40	130	5.1	7.0	.275	254	10.0	.27	10
36288	T45	130	5.1	8.0	.315	254	10.0	.31	10

Wiha TORX® SoftFinish® Screwdrivers



#36291

#36201

36291 6 Piece TORX® SoftFinish® - Cusion Grip Set

Round blade high alloy CVM steel, hardened, hard chromed. Wiha-Chromtop finish on tips. Wiha-SoftFinish® handle, multi-component.

Item No.	Size	mm	Size	mm	lbs.
36291 36266	T6	60	36272 T9	60	.77
36268	T7	60	36274 T10	80	
36270	T8	60	36276 T15	80	

36201 Set 6 Pcs. TORX®

Item No.	Size	mm	Size	mm	lbs.
36201 36266	T6	60	36276 T15	80	.83
36270	T8	60	36278 T20	100	
36274	T10	80	36280 T25	100	



36294 8 Piece TORX® Set

Item No.	Size	mm	Size	mm	lbs.
36294 36266	T6	60	36278 T20	100	1.24
36270	T8	60	36280 T25	100	
36274	T10	80	36282 T27	115	
36276	T15	80	36284 T30	115	



36267 12 Piece TORX® Set

Item No.	Size	mm	Size	mm	lbs.
36267 36264	T5	60	36276 T15	80	2.03
36266	T6	60	36278 T20	100	
36268	T7	60	36280 T25	100	
36270	T8	60	36282 T27	115	
36272	T9	60	36284 T30	115	
36274	T10	80	36286 T40	130	

Wiha Security TORX® Drivers



SHOP

362 Security TORX® Screwdriver With Wiha-SoftFinish®

Handle Round blade high alloy chrome-vanadium-molybdenum steel, hardened, hard chromed. Wiha-Chromtop finish on tips. Wiha-SoftFinish® handle, multi-component, cushion grips.

Item No.	Size	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
36269	T7s	60	2.4	3.5	.139	164	6.5	.06	10
36271	T8s	60	2.4	3.5	.139	164	6.5	.06	10
36273	T9s	60	2.4	4.0	.157	171	6.7	.10	10
36275	T10s	80	3.1	4.0	.157	191	7.5	.11	10
36277	T15s	80	3.1	4.0	.157	191	7.5	.11	10
36279	T20s	100	3.9	4.0	.157	211	8.3	.11	10
36281	T25s	100	3.9	4.5	.177	211	8.3	.11	10
36283	T27s	115	4.5	5.5	.216	233	9.2	.19	10
36285	T30s	115	4.5	6.0	.236	233	9.2	.20	10
36287	T40s	130	5.1	7.0	.275	254	10.0	.28	10



36298 Set 7 Pcs. Security TORX®

Item No.	Size	mm	Size	mm	lbs.
36298	36269 T7s	60	36277 T15s	80	.95
	36271 T8s	60	36279 T20s	100	
	36273 T9s	60	36281 T25s	100	
	36275 T10s	80			



36259 Set 10 Pcs. Security TORX®

Item No.	Size	mm	Size	mm	lbs.
36259	36269 T7s	60	36279 T20s	100	1.5
	36271 T8s	60	36281 T25s	100	
	36273 T9s	60	36283 T27s	115	
	36275 T10s	80	36285 T30s	115	
	36277 T15s	80	36287 T40s	130	

Wiha TORXPlus® Cushion Grip Drivers




SHOP

Not for use in standard Torx fasteners

362 TORXPlus® Screwdriver With Wiha SoftFinish® Handle

Round blade high alloy Chrome-vanadium-molybdenum tool steel, hardened, hard chromed. Wiha-Chromtop finish on tips.

Item No.	Size	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
36211	IP6	60	2.4	3.5	.139	164	6.5	.06	10
36223	IP7	60	2.4	3.5	.139	164	6.5	.06	10
36228	IP8	60	2.4	4.0	.157	171	6.7	.10	10
36229	IP9	60	2.4	4.0	.157	171	6.7	.11	10
36233	IP10	80	3.1	4.0	.157	191	7.5	.11	10
36238	IP15	80	3.1	4.0	.157	191	7.5	.11	10
36239	IP20	100	3.9	4.5	.177	211	8.3	.11	10
36243	IP25	100	3.9	5.5	.216	211	8.3	.19	10
36248	IP27	115	4.5	6.0	.236	233	9.2	.20	10
36253	IP30	115	4.5	7.0	.275	233	9.2	.28	10
36255	IP40	130	5.1	7.0	.275	254	10.0	.28	10



SHOP

36299 Set 7 Pcs. TORXPlus® Blade high alloy CVM steel, hardened, hard chromed. Wiha-SoftFinish® handle, multi-component.

Item No.	Size	mm	Size	mm	lbs.
36299	36228 IP8	60	36243 IP25	100	1.23
	36233 IP10	80	36253 IP30	115	
	36238 IP15	80	36255 IP40	130	
	36239 IP20	100			



SHOP

36296 Set 6 Pcs. TORXPlus®

Blade high alloy CVM steel, hardened, hard chromed. Wiha-SoftFinish® handle, multi-component.

Item No.	Size	mm	Size	mm	lbs.
36296	36211 IP6	60	36229 IP9	60	.72
	36223 IP7	60	36233 IP10	80	
	36228 IP8	60	36238 IP15	80	

Wiha MagicRing SoftFinish® Hex Drivers

Screw Holding Hex Tools



[SHOP](#)


367 MagicRing Ball End Hex-Driver Inch, With Wiha-SoftFinish®

Handle Hex blade, high alloy CVM steel, hardened, hard chromed.

Wiha-SoftFinish® handle, multi-component, cushion grip.

Item						
No.	Inch	Inch	mm	mm	lbs.	pkg.
36710*	.050	3.1	80	179	.06	10
36713*	1/16	3.1	80	204	.06	10
36716*	5/64	3.9	100	204	.07	10
36719*	3/32	3.9	100	204	.07	10
36723*	7/64	3.9	100	211	.07	10
With MagicRing						
36726	1/8	3.9	100	243	.12	10
36728	9/64	3.9	100	243	.12	10
36732	5/32	5.0	125	271	.12	10
36734	3/16	6.0	150	271	.16	10
36736	7/32	6.0	150	271	.23	10
36738	1/4	6.0	150	271	.25	10
36742	5/16	8.0	200	271	.37	10
36744	3/8	8.0	200	271	.54	10

* Standard Ball - No Ring



[SHOP](#)

36793 8 Piece MagicRing Inch Ball End Screwdriver Set

Hex blade chrome-vanadium-molybdenum steel, hardened, hard chromed. Wiha-SoftFinish® handle, multi-component, cushion grip.

Item	No.	Inch	Inch	Inch	Inch	lbs.
36793	36726	1/8	4.0	36736	7/32	6.0
	36728	9/64	4.0	36738	1/4	6.0
	36732	5/32	5.0	36742	5/16	8.0
	36734	3/16	6.0	36744	3/8	8.0

Don't Drop That Screw!
Save Valuable Time!
Improve Productivity!
Make The Job Easy!




[SHOP](#)

36791 13 Piece MagicRing Inch Ball End Screwdriver Set

Hex blade chrome-vanadium-molybdenum steel, hardened, hard chromed. Wiha-SoftFinish® handle, multi-component, cushion grip.

Item	No.	Inch	Inch	Inch	Inch	lbs.
36791	36710*	.050	3.0	36732	5/32	5.0
	36713*	1/16	3.0	36734	3/16	6.0
	36716*	5/64	4.0	36736	7/32	6.0
	36719*	3/32	4.0	36738	1/4	6.0
	36723*	7/64	4.0	36742	5/16	8.0
	36726	1/8	4.0	36744	3/8	8.0
	36728	9/64	4.0			

* Standard Ball - No Ring



[SHOP](#)

36794 6 Piece MagicRing Inch Ball End Screwdriver Set

Hex blade chrome-vanadium-molybdenum steel, hardened, hard chromed. Wiha-SoftFinish® handle, multi-component, cushion grip.

Item	No.	Inch	Inch	Inch	Inch	lbs.
36794	36726	1/8	4.0	36734	3/16	6.0
	36728	9/64	4.0	36736	7/32	6.0
	36732	5/32	5.0	36738	1/4	6.0

Wiha MagicRing SoftFinish® Hex Drivers

Screw Holding Hex Tools



SHOP

367 MagicRing Ball End Hex Driver Metric, With Wiha-SoftFinish®

Handle Hex blade, high alloy CVM steel, hardened, hard chromed. Wiha-SoftFinish® handle, multi-component, cushion grip.

Item No.	mm	mm	mm	lbs.	pkg.
36715*	1.5	75	179	.06	10
36720*	2.0	100	204	.07	10
36725*	2.5	100	204	.07	10
With MagicRing					
36730	3.0	100	204	.07	10
36740	4.0	125	211	.12	10
36750	5.0	150	243	.16	10
36760	6.0	150	243	.23	10
36780	8.0	200	268	.37	10
36786	10.0	200	271	.54	10

* Standard Ball - No Ring

Hardened spring steel retaining ring holds screws on

Hard chrome super durable corrosion resistant finish

Precision machined for exact fit

Made from Wiha exclusive CVM hardened tool steel

Don't Drop That Screw!
Save Valuable Time!
Improve Productivity!
Make The Job Easy!



SHOP

36790 9 Piece MagicRing Metric Ball End Hex Screwdriver Set

Hex blade chrome-vanadium-molybdenum steel, hardened, hard chromed. Wiha-SoftFinish® handle, multi-component, cushion grip.

Item No.	mm	mm	mm	mm	lbs.
36715*	1.5	75	36750	5.0	150
36720*	2.0	100	36760	6.0	150
36725*	2.5	100	36780	8.0	200
36730	3.0	100	36786	10.0	200
36740	4.0	125			

* Standard Ball - No Ring



SHOP

36792 6 Piece MagicRing Metric Ball End Hex Screwdriver Set

Hex blade chrome-vanadium-molybdenum steel, hardened, hard chromed. Wiha-SoftFinish® handle, multi-component, cushion grip.

Item No.	mm	mm	mm	mm	lbs.
36730	3.0	100	36760	6.0	150
36740	4.0	125	36780	8.0	200
36750	5.0	150	36786	10.0	200

Wiha Stainless Steel Screwdrivers

Stainless Steel

Controls corrosion & contamination of stainless fasteners

Precision machined exact fit tips

Heavy Duty hex blade of premium hardened stainless steel

Non rusting stainless steel blade

Guaranteed quality-Made by Wiha

SoftFinish multi-component, cushion grip handles



308 Stainless Steel Slotted Screwdriver, With Wiha SoftFinish®

Handle High quality, non-rusting stainless steel blade. Wiha-SoftFinish® handle, multi-component, cushion grip.

Item	+	+	+	+	+	+	+	+	+
No.	mm	Inch	mm	Inch	mm	Inch	mm	Inch	lbs. pkg.
30836	3.5	.139	75	3.0	0.6	.024	179	7.0	.12 10
30845	4.5	.187	90	3.6	0.8	.031	201	7.9	.14 10
30855	5.5	.216	100	3.9	1.0	.039	213	8.4	.24 10
30865	6.5	.255	125	5.0	1.2	.047	238	9.4	.28 10



312 Stainless Steel Phillips Screwdriver, With Wiha

SoftFinish® Handle High quality, non-rusting stainless steel blade. Wiha-SoftFinish® handle, multi-component, cushion grip.

Item	+	+	+	+	+	+	+
No.	Size	mm	Inch	mm	Inch	lbs.	pkg.
31211	1	80	3.1	186	7.3	.14	10
31212	2	100	3.9	213	8.4	.22	10
31213	3	150	5.9	268	10.6	.28	10



30890 Set 5 Pcs. Slotted & Phillips Stainless Steel Screwdrivers

High quality, non-rusting stainless steel blade. Wiha-SoftFinish® handle, multi-component, cushion grip.

Item	+	+	+	+	+	+
No.	mm	mm	Size	mm	lbs.	
30890	30836	3.5	75	31211	1	80
	30845	4.5	90	31212	2	100
	30855	5.5	100			



314 Stainless Steel Pozidriv® Screwdriver, With Wiha SoftFinish®

Handle High quality, non-rusting stainless steel blade. Wiha-SoftFinish® handle, multi-component, cushion grip.

Item									
No.	Size	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
31401	1	80	3.1	5.0	.203	186	7.3	.14	10
31402	2	100	3.9	6.0	.236	213	8.4	.22	10
31403	3	150	5.9	8.0	.315	268	10.6	.28	10



376 Stainless Steel TORX® Screwdriver, With Wiha SoftFinish®

Handle High quality, non-rusting stainless steel blade. Wiha-SoftFinish® handle, multi-component, cushion grip.

Item									
No.	Size	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
37608	T8	60	2.4	4.0	.157	164	6.5	.09	10
37609	T9	60	2.4	4.0	.157	171	6.7	.11	10
37610	T10	80	3.1	4.0	.157	191	7.5	.11	10
37615	T15	80	3.1	4.0	.157	191	7.5	.11	10
37620	T20	100	3.9	4.0	.157	218	8.6	.16	10
37625	T25	100	3.9	4.5	.177	218	8.6	.17	10
37627	T27	115	4.5	5.5	.216	233	9.2	.20	10
37630	T30	115	4.5	6.0	.236	233	9.2	.21	10
37640	T40	130	5.1	7.0	.275	254	10.0	.24	10



37690 Set 5 Pcs. TORX® Stainless Steel Screwdrivers

High quality, non-rusting stainless steel blade. Wiha-SoftFinish® handle, multi-component, cushion grip.

Item	+	+	+	+	+	+
No.	Size	mm	Size	mm	lbs.	
37690	37608	T8	60	37620	T20	100
	37610	T10	80	37625	T25	100
	37615	T15	80			

Wiha Interchangeable Tools

Magnetize & Demagnetize



To Magnetize



To Demagnetize

[SHOP](#)

48190 4 Piece Slotted & Phillips Interchangeable Blade Set, In Durable Pouch Set includes Magnetizer/Demagnetizer handle & 3 interchangeable blades.

Item	
No. 48190	lbs. .62
Slotted: 3.0, 4.0, 6.0mm	Phillips: 0, 1, 2
Wiha Magnetizer/Demagnetizer Handle	



[SHOP](#)

48106 Magnetizer/Demagnetizer Handle


Wiha-Hex bolster for additional torque.

Advantages:

- Ergo soft grip panels for comfort
- Built in blade Magnetizer/Demagnetizer

Item						
No.	mm	mm	Inch	mm	Inch	lbs.
48106	6.0	109	4.1	29	1.1	.14

Switch Cabinet Key



[SHOP](#)

21103 Switch Cabinet Keys

For applications with all common switch cabinets and locking systems. Diecast Zinc

Item No.	mm	Inch	Pkg.	lbs.
21103	76	3.0"	5	.22

Wiha ACR® Slotted & Phillips Screwdrivers

ACR® Anti-Cam-Out Ribs



Anti-Cam-Out ribs give maximum grip in the screw head

Dual material handle has molded in soft grip panels & hang hole

Round blade made CVM special tool steel

Precision machined exact fit slotted tips ACR® ribs

3K overdrive maximum comfort molded on ergonomic handle



Precision Black Tips



469 ACR® Slotted Screwdriver, With Wiha-3K Series Handle

Blade chrome-vanadium-molybdenum steel, hardened, chrome nickel-plated. Wiha-3k Ergo handle, cushion grip. Precision black tips.

Item										
No.	mm	Inch	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
46912	4.5	.177	80	3.1	1.3	.050	186	7.3	.13	10
46915	4.5	.177	150	5.9	1.3	.050	256	10.0	.16	10
46921	6.0	.236	100	3.9	1.5	.058	218	8.5	.21	10
46924	6.0	.236	150	5.9	1.5	.058	269	10.5	.23	10
46933	8.0	.315	150	5.9	2.0	.078	269	10.5	.27	10

[SHOP](#)



468 ACR® Phillips Screwdriver, With Wiha-3K Series Handle

Blade chrome-vanadium-molybdenum steel, hardened, chrome nickel-plated. Wiha-3k Ergo handle, cushion grip. Precision black tips.

Item							
No.	Size	mm	Inch	mm	Inch	lbs.	pkg.
46803	1	80	3.1	186	7.3	.13	10
46806	1	150	5.9	257	10.1	.15	10
46812	2	100	3.9	218	8.5	.21	10
46815	2	150	5.9	269	10.6	.23	10

[SHOP](#)



46991 Set 6 Pcs. Slotted & Phillips 3K ACR® Soft Grip Set

Blade chrome-vanadium-molybdenum steel, hardened, chrome nickel-plated. Wiha-3k Ergo handle, cushion grip. Precision black tips.

Item						
No.		mm	mm	Size	mm	lbs.
46991	46912	4.5	80	46803	1	80
	46921	6.0	100	46806	1	150
	46933	8.0	150	46812	2	100

[SHOP](#)

Wiha 3K Series Screwdrivers and Sets

3K Ergonomic Series Screwdrivers & Sets



450 Slotted Screwdriver, With Wiha-3K Series Handle

Blade chrome-vanadium-molybdenum steel, chrome nickel-plated. Wiha-3K Ergo handle, cushion grip. Precision black tips.

Item No.	mm	Inch	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
45040**	2.5	.10	75	3.0	0.4	.02	161	6.3	.06	10
45050**	3.0	.12	100	3.9	0.5	.02	185	7.3	.07	10
45052**	3.5	.14	100	3.9	0.6	.02	197	7.7	.09	10
45054**	4.0	.16	100	3.9	0.8	.03	206	8.1	.12	10
45055	4.5	.18	100	3.9	1.0	.04	207	8.1	.13	10
45056	4.5	.18	150	5.9	1.0	.04	257	10.1	.14	10
45057	4.5	.18	200	8.0	1.0	.04	306	12.0	.15	10
45058	5.5	.22	125	5.0	1.0	.04	243	9.5	.19	10
45060	6.0	.24	100	3.9	0.9	.04	218	8.5	.20	10
45061	6.0	.24	150	5.9	0.9	.04	268	10.5	.23	10
45062	6.0	.24	200	8.0	0.9	.04	318	12.5	.25	10
45064*	6.5	.24	40	1.6	1.2	.05	90	3.5	.08	10
45065	6.5	.24	150	5.9	1.2	.05	268	10.5	.23	10
45067	8.0	.32	150	5.9	1.2	.05	268	10.5	.26	10
45069	10.0	.39	200	8.0	1.6	.06	318	12.5	.35	10

* Stubby screwdriver with Wiha Powerhandle - 45064

** Cabinet Tip



48401 1/4" Bit holding Screwdriver, With Wiha-Ergo 3K Handle

Magnetic, holds bit and screw. Retainer out of stainless steel. Shaft CVM tool steel, nickel plated.

Item No.	Size	mm	Inch	mm	Inch	lbs.	pkg.
48401	1/4"	125	5.0	211	8.3	.24	1



[SHOP](#)

451 Phillips Screwdriver, With Wiha-3K Series Handle

Item No.	mm	mm	Inch	mm	Inch	lbs.	pkg.
45135	0	60	2.4	145	5.7	.06	10
45137	1	80	3.1	187	7.3	.13	10
45140	1	200	8.0	307	12.0	.16	10
45142	2	100	3.9	218	8.5	.21	10
45144	2	150	5.9	268	10.5	.23	10
45147	2	200	8.0	318	12.5	.25	10
45150*	2	40	1.6	90	3.5	.08	10
45152	3	150	5.9	268	10.5	.31	10

* Stubby screwdriver with Wiha Powerhandle - 45150



[SHOP](#)

46098 4 Piece Slotted & Phillips Screwdriver Set

Item No.	mm	mm	Size	mm	lbs.
46098	45055	4.5	100	45137	1
	45060	6.0	100	45142	2



46099 40 Piece Slotted, Phillips, TORX®, Pozidriv®, Bit Holder & Folding Ruler Blade CVM steel, hardened. With 16" tool box

Item No.	lbs.
46099	10.4
Slotted: 2.5, 3.0, 3.5, 4.0, 4.5x100, 4.5x150, 4.5x200, 5.5, 6.0x100, 6.0x150, 6.0x200, 6.5x40, 6.5x150, 8.0, 10mm	
Phillips: 0x60, 1x80, 1x200, 2x100, 2x150, 2x200, 2x40, 3x150	
TORX®: T6, T7, T8, T9, T10, T15, T20, T25, T27, T30, T40, T45, T50	
Pozidriv®: 1x80, 2x100	
3K 1/4" Magnetic Bit Holder 61601 Folding Ruler	

Wiha 3K Series Screwdrivers and Sets



[SHOP](#)

46095 5 Piece Slotted & Phillips Screwdriver Set

Blade chrome-vanadium-molybdenum steel, chrome nickel-plated. Wiha-3k Ergo handle, cushion grip. Precision black tips.

Item						
No.	mm	mm		Size	mm	lbs.
46095	45055	4.5	100	45135	0 60	1.04
	45060	6.0	100	45137	1 80	
				45142	2 100	



[SHOP](#)

46094 6 Piece Slotted & Phillips Screwdriver Set

Blade chrome-vanadium-molybdenum steel, chrome nickel-plated. Wiha-3k Ergo handle, cushion grip. Precision black tips.

Item							
No.	mm	mm		Size	mm	lbs.	
46094	45050	3.0	100	45137	1	80	.91
	45055	4.5	100	45144	2	150	
	45058	5.5	125				
	45065	6.5	150				



[SHOP](#)

46097 8 Piece Slotted & Phillips Set

Blade CVM steel, chrome nickel-plated. Wiha-3k Ergo handle, cushion grip. Precision black tips.

Item							
No.		mm	mm		Size	mm	lbs.
46097	45050	3.0	100	45137	1	80	1.70
	45055	4.5	100	45142	2	100	
	45060	6.0	100	45150	2	40	
	45067	8.0	150	45152	3	150	



[SHOP](#)

452 Pozidriv® Screwdriver, With Wiha-3K Series Handle

Blade chrome-vanadium-molybdenum steel, hard chromed shaft. Wiha-3k Ergo handle, cushion grip. Black tip.

Item No.	Size	mm	Inch	mm	Inch	lbs.	pkg.
45205	0	60	2.4	146	5.7	.06	10
45207	0	100	3.9	186	7.3	.07	10
45215	1	80	3.1	187	7.3	.13	10
45220	1	100	3.9	207	8.1	.14	10
45225	2	100	3.9	219	8.6	.21	10
45230	2	150	5.9	269	10.6	.23	10
45235	3	150	5.9	269	10.6	.31	10

Wiha TORX® 3K Series Drivers and Sets



[SHOP](#)

455 TORX® Screwdriver, With Wiha-3K Series Handle

Blade high alloy CVM steel, hardened, precision black tip. Molded on ergonomic Wiha-3K Series handle, impact resistant.

Item No.	Size	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
45504	T6	60	2.4	3.2	9/64	145	5.7	.06	10
45507	T7	60	2.4	3.5	9/64	129	5.1	.05	10
45508	T8	60	2.4	3.5	9/64	139	5.5	.06	10
45509	T9	60	2.4	4.0	5/32	149	5.8	.08	10
45510	T10	80	3.1	4.0	5/32	170	6.7	.10	10
45515	T15	80	3.1	4.0	5/32	190	7.5	.11	10
45520	T20	100	3.9	5.5	7/32	215	8.4	.11	10
45525	T25	100	3.9	6.0	1/4	215	8.4	.20	10
45527	T27	115	4.5	7.0	9/32	240	9.4	.28	10
45530	T30	115	4.5	6.0	1/4	233	9.1	.21	10
45540	T40	130	5.1	7.0	9/32	248	9.7	.25	10
45545	T45	130	5.1	8.0	5/16	249	9.8	.30	10
45550	T50	130	5.1	9.0	3/8	249	9.8	.33	10



[SHOP](#)

45593 Set 5 Pcs. TORX® Blade CVM steel, hardened, precision black tip. Wiha-3k Ergo handle, cushion grip.

Item No.							
	Size	mm		Size	mm	lbs.	
45593	45508	T8	60	45520	T20	100	.86
	45510	T10	80	45525	T25	100	
	45515	T15	80				

Wiha 3K Series Drivers & Sets



[SHOP](#)

45598 Set 6 Pcs. TORX® Blade CVM steel, hardened, precision black tip. Wiha-3k Ergo handle, cushion grip.

Item No.	Size	mm	Size	mm	lbs.
45598	45504	T6 60	45509	T9 60	.88
	45507	T7 60	45510	T10 80	
	45508	T8 60	45515	T15 80	



[SHOP](#)

45595 Set 8 Pcs. TORX® Wiha-3k Ergo handle, cushion grip.

Item No.	Size	mm	Size	mm	lbs.
45595	45508	T8 60	45520	T20 100	1.36
	45509	T9 60	45525	T25 100	
	45510	T10 80	45527	T27 115	
	45515	T15 80	45530	T30 115	



[SHOP](#)

45597 Set 11 Pcs. TORX® 3K Ergo Series Screwdriver Set
Blade chrome-vanadium-molybdenum steel, hardened, precision black tip. Wiha-3k Ergo handle, cushion grip.

Item No.	Size	mm	Size	mm	lbs.
45597	45504	T6 60	45520	T20 100	1.72
	45507	T7 60	45525	T25 100	
	45508	T8 60	45527	T27 115	
	45509	T9 60	45530	T30 115	
	45510	T10 80	45540	T40 130	
	45515	T15 80			

Wiha Ball End 3K Series Drivers & Sets




Metric / Soft Grip

[SHOP](#)

467 Ball End Hex Metric Screwdriver, With Wiha-3K Ergo Handle

Blades of CVM special steel, hardened, black finish. Molded on Wiha-3K Ergo soft grip handles.


Item No.	mm	mm	mm	lbs.	pkg.
46715	1.5	75	161	.07	10
46720	2.0	100	186	.07	10
46725	2.5	100	186	.07	10
46730	3.0	100	186	.07	10
46740	4.0	100	197	.11	10
46750	5.0	100	197	.13	10
46760	6.0	150	257	.21	10
46780	8.0	200	307	.34	10
46786	10.0	200	319	.52	10



[SHOP](#)

46796 7 Piece Metric Ball End Hex Screwdriver Set

Item No.	mm	mm	mm	mm	lbs.
46796	46715	1.5 75	46740	4.0 100	1.15
	46720	2.0 100	46750	5.0 100	
	46725	2.5 100	46760	6.0 150	
	46730	3.0 100			




[SHOP](#)

46799 9 Piece Metric Ball End Hex Screwdriver Set

Item No.	mm	mm	mm	mm	lbs.
46799	46715	1.5 75	46750	5.0 100	1.93
	46720	2.0 100	46760	6.0 150	
	46725	2.5 100	46780	8.0 200	
	46730	3.0 100	46786	10.0 200	
	46740	4.0 100			

Wiha Ball End 3K Series Drivers & Sets




Inch / Soft Grip

[SHOP](#)

467 Ball End Hex Inch Drivers, With 3K Ergo Soft Grip Handles

Blades of CVM special steel, hardened, black finish. Molded on Wiha-3K Ergo soft grip handles.

Item No.	Hex	Inch	Inch	lbs.	pkg.
46702	.050	2.9	6.3	.07	10
46704	1/16	2.9	6.3	.07	10
46706	5/64	3.9	7.3	.07	10
46708	3/32	3.9	7.3	.07	10
46710	7/64	3.9	7.3	.07	10
46712	1/8	3.9	7.7	.09	10
46714	9/64	3.9	7.7	.10	10
46716	5/32	3.9	7.7	.11	10
46718	3/16	3.9	7.7	.12	10
46722	7/32	5.9	10.0	.19	10
46724	1/4	5.9	10.0	.22	10
46726	5/16	7.9	12.0	.34	10
46728	3/8	7.9	12.5	.48	10




[SHOP](#)

46797 13 Piece 3K Ergo Inch Ball End Hex Screwdriver Set

Blades of CVM special steel, hardened, black finish. Molded on Wiha-3k Ergo soft grip handles.

Item No.	Hex	Inch	Inch	lbs.
46797	46702	.050	2.9	2.40
	46704	1/16	2.9	
	46706	5/64	3.9	
	46708	3/32	3.9	
	46710	7/64	3.9	
	46712	1/8	3.9	
	46714	9/64	3.9	
	46716	5/32	3.9	
	46718	3/16	2.9	
	46722	7/32	5.9	
	46724	1/4	5.9	
	46726	5/16	7.9	
	46728	3/8	7.9	

- Soft panel grip
- Convenient hang hole
- Hardened CVM tool steel
- Exact fit precision machined tips
- Fast angle entry



[SHOP](#)

46793 8 Piece 3K Ergo Inch Ball End Hex Screwdriver Set

Item No.	Hex	Inch	Inch	lbs.
46793	46702	.050	2.9	1.19
	46704	1/16	2.9	
	46706	5/64	3.9	
	46708	3/32	3.9	
	46710	7/64	3.9	
	46712	1/8	3.9	
	46714	9/64	3.9	
	46716	5/32	3.9	



[SHOP](#)


46794 6 Piece 3K Ergo Inch Ball End Hex Screwdriver set

Item No.	Hex	Inch	Inch	lbs.
46794	46712	1/8	3.9	.97
	46714	9/64	3.9	
	46716	5/32	3.9	
	46718	3/16	3.9	
	46722	7/32	5.9	
	46724	1/4	5.9	

Yellow = Inch
Red = Metric

Wiha Drive-Loc VI Handles

Drive-Loc VI For Adjustable Length Locking Blades



The blade length can be adjusted from 40mm-120mm. (1.7 to 4.7")

Locking mechanism in SoftFinish cushion grip ergonomic handle. Blade length can be adjusted from 40mm-120mm. (1.7 to 4.7" In 1/8" increments)

Drive-Loc mechanism guarantees a secure hold & rapid blade exchange

Adjust interchangeable blades from 40 to 120mm

Ergonomic handles in ESD Safe, cushioned & non-slip grip

Blades high quality CVM steel, hard chrome finish

 See Drive-Loc VI Nut drivers on Page 46



[SHOP](#)

28488 Drive-Loc VI Cushion Grip Handle

Wiha-SoftFinish® impact resistant, with roll off protection.

Advantages: Ergonomic cushion grip, Drive-Loc mechanism guarantees a secure hold and rapid blade exchange.

Item						
No.	mm	mm	Inch	mm	Inch	lbs.
28488	6.0	115	4.5	36.0	1.41	.26



[SHOP](#)

28486 ESD Safe Drive-Loc VI Cushion Grip Handle

Wiha-SoftFinish® impact resistant, with roll off protection.

Advantages: Ergonomic cushion grip, Drive-Loc mechanism guarantees a secure hold and rapid blade exchange. Static Dissipative.

Item						
No.	mm	mm	Inch	mm	Inch	lbs.
28486	6.0	115	4.5	36.0	1.41	.21



[SHOP](#)

28487 Drive-Loc VI MicroFinish Non-Slip Grip Handle

Wiha-MicroFinish handle, won't peel, crack or deteriorate when exposed to petroleum solvents. Ideal for Hex, TORX® & Nut Drivers.

Advantages: Ergonomic handle shape for maximum comfort, Drive-Loc mechanism guarantees a secure hold & rapid blade exchange.

Item						
No.	mm	mm	Inch	mm	Inch	lbs.
28487	6.0	115	4.5	36.0	1.41	.20



281 Slotted Drive-Loc VI Interchangeable Blade High alloy CVM steel, through hardened, hard chrome finish. Over all blade length 150mm/5.9". Blades fit all Drive-Loc VI handles.

Item				
No.	mm + mm	lbs.	pkg.	
28106	3.5 4.5	.10	1	
28108	5.5 6.5	.10	1	

[SHOP](#)



281 Slotted & Phillips Drive-Loc VI Interchangeable Blade

High alloy CVM steel, through hardened, hard chrome finish. Over all blade length 150mm/5.9". Blades fit all Drive-Loc VI handles.

Item				
No.	mm + Size	lbs.	pkg.	
28107	3.0 0	.10	1	
28109	4.0 1	.10	1	
28110	6.0 2	.10	1	

[SHOP](#)



28112 Phillips Drive-Loc VI Interchangeable Blade

High alloy CVM steel, through hardened, hard chrome finish. Over all blade length 150mm/5.9". Blades fit all Drive-Loc VI handles.

Item				
No.	Size + Size	lbs.	pkg.	
28112	1 2	.10	1	

[SHOP](#)



28137 Square Drive-Loc VI Interchangeable Blade

High alloy CVM steel, through hardened, hard chrome finish. Over all blade length 150mm/5.9". Blades fit all Drive-Loc VI handles.

Item				
No.	Size + Size	lbs.	pkg.	
28137	1 2	.10	1	

[SHOP](#)

Wiha Drive-Loc VI Blades



281 TORX® Drive-Loc VI Interchangeable Blade

High alloy CVM steel, through hardened, hard chrome finish.
Over all blade length 150mm/5.9". Blades fit all Drive-Loc VI handles.

Item No.	Size + Size	lbs.	pkg.	SHOP
28126	T6 T8	.10	1	
28127	T7 T9	.10	1	
28128	T10 T15	.10	1	
28129	T20 T25	.10	1	
28130	T30 T40	.10	1	



281 Security TORX® Drive-Loc VI Interchangeable Blade

High alloy CVM steel, through hardened, hard chrome finish.

Over all blade length 150mm/5.9". Blades fit all Drive-Loc VI handles.

Item No.	Size + Size	lbs.	pkg.	SHOP
28132	T6s T8s	.10	1	
28133	T7s T9s	.10	1	
28134	T10s T15s	.10	1	
28135	T20s T25s	.10	1	
28136	T30s T40s	.10	1	



28114 Pozidriv® Drive-Loc VI Interchangeable Blade

High alloy CVM steel, through hardened, hard chrome finish.

Over all blade length 150mm/5.9". Blades fit all Drive-Loc VI handles.

Item No.	Size + Size	lbs.	pkg.	SHOP
28114	1 2	.10	1	



281 Tri-wing® Drive-Loc VI Interchangeable Blade

High alloy CVM steel, through hardened, hard chrome finish.

Over all blade length 150mm/5.9". Blades fit all Drive-Loc VI handles.

Item No.	Size + Size	lbs.	pkg.	SHOP
28138	0 1	.10	1	
28139	2 3	.10	1	
28140	4 5	.10	1	



281 Torq Set® Drive-Loc VI Interchangeable Blade

High alloy CVM steel, through hardened, hard chrome finish.

Over all blade length 150mm/5.9". Blades fit all Drive-Loc VI handles.

Item No.	Size + Size	lbs.	pkg.	SHOP
28142	2 4	.08	1	
28143	6 8	.10	1	

Wiha Drive-Loc VI Blades



281 Ball End Hex & Hex Metric Drive-Loc VI Interchangeable Blade

High alloy CVM steel, through hardened, hard chrome finish.

Ball end enables the user to work at angles up to 25°. Over all blade length 150mm/5.9". Blades fit all Drive-Loc VI handles.

Item No.	mm + mm	lbs.	pkg.	SHOP
28116	2.5 2.5	.10	1	
28117	3 3	.10	1	
28118	4 4	.10	1	
28119	5 5	.10	1	
28120	6 6	.10	1	



281 Hex Metric Drive-Loc VI Interchangeable Blade

High alloy CVM steel, through hardened, hard chrome finish.

Over all blade length 150mm/5.9". Blades fit all Drive-Loc VI handles.

Item No.	mm + mm	lbs.	pkg.	SHOP
28149	2.0 2.5	.09	1	
28150	3.0 4.0	.10	1	
28151	5.0 6.0	.10	1	



281 Hex Inch Drive-Loc VI Interchangeable Blade

High alloy CVM steel, through hardened, hard chrome finish.

Over all blade length 150mm/5.9". Blades fit all Drive-Loc VI handles.

Item No.	Inch + Inch	lbs.	pkg.	SHOP
28122	3/32 7/64	.10	1	
28123	1/8 9/64	.10	1	
28124	5/32 3/16	.10	1	



28191 33 Pc. Drive-Loc VI Interchangeable Blade Set, In Tool Box Tray

Set includes Drive-Loc VI handle & 31 interchangeable blades.

Item No.	28191	lbs.	3.48	SHOP
Slotted:	3.5+4.5, 5.5+6.5	Slotted/Phillips:	3.0+0, 4.0+1, 6.0+2	
Security TORX®:	T6s+T8s, T7s+T9s, T10s+T15s, T20s+T25s, T30s+T40s			
Square:	1+2	Hex Inch:	3/32+7/64, 1/8+9/64, 5/32+3/16	
Hex Metric:	2.0+2.5, 3.0+4.0, 5.0+6.0			
Nut Drivers Inch:	1/4, 9/32, 5/16, 11/32, 3/8, 7/16, 1/2"			
Nut Drivers Metric:	5.5, 6.0, 7.0, 8.0, 9.0, 10.0, 11.0mm			
Wiha SoftFinish® Cushion Grip & MicroFinish Non-Slip Grip Handles				

Drive-Loc VI Nut Driver Blades & Sets


[SHOP](#)

281 Drive-Loc VI Inch Nut Driver Blades

High alloy CVM steel, through hardened, hard chrome finish.
OAL blade length 150mm/5.9". Blades fit all Drive-Loc VI handles.

Item				
No.	Inch	OAL	lbs.	pkg.
28156	3/16	5.9"	.11	1
28157	7/32	5.9"	.11	1
28158	1/4	5.9"	.11	1
28159	9/32	5.9"	.12	1
28160	5/16	5.9"	.13	1
28161	11/32	5.9"	.14	1
28162	3/8	5.9"	.15	1
28163	7/16	5.9"	.17	1
28164	1/2	5.9"	.18	1


[SHOP](#)

281 Drive-Loc VI Metric Nut Driver Blades

High alloy CVM steel, through hardened, hard chrome finish.
OAL blade length 150mm/5.9". Blades fit all Drive-Loc VI handles.

Item				
No.	mm	OAL	lbs.	pkg.
28168	4.0	150mm	.10	1
28169	4.5	150mm	.10	1
28170	5.0	150mm	.11	1
28171	5.5	150mm	.11	1
28172	6.0	150mm	.12	1
28173	7.0	150mm	.13	1
28174	8.0	150mm	.13	1
28177	9.0	150mm	.14	1
28175	10.0	150mm	.15	1
28176	11.0	150mm	.20	1


[SHOP](#)

28196 8 Pc. Drive-Loc VI Interchangeable Blade Set, In Durable Pouch

Set includes Drive-Loc VI handle & 7 Inch Nut Driver blades.

Item		lbs.
No. 28196		1.22
Inch: 3/16, 1/4, 5/16, 11/32, 3/8, 7/16, 1/2"		
Wiha SoftFinish® Cushion Grip Blade Lock Handle		



28198 8 Pc. Drive-Loc VI Interchangeable Blade Set, In Durable Pouch

Set includes Drive-Loc VI handle & 7 Metric Nut Driver blades.

Item		lbs.
No. 28198		1.00
Metric: 5.0, 5.5, 6.0, 7.0, 8.0, 9.0, 10.0mm		
Wiha SoftFinish® Cushion Grip Blade Lock Handle		

Drive-Loc VI Interchangeable Blade Sets


[SHOP](#)

28194 5 Pc. Drive-Loc VI Interchangeable Blade Set, In Durable Pouch

Set includes Drive-Loc VI handle & 4 interchangeable blades.

Item		lbs.
No. 28194		.80
Slotted: 3.5+4.5, 5.5+6.5 Phillips: 1+2 Square: 1+2		
Wiha SoftFinish® Cushion Grip Blade Lock Handle		


[SHOP](#)

28197 6 Pc. Drive-Loc VI Interchangeable Blade Set, In Durable Pouch

Set includes Drive-Loc VI handle & 5 interchangeable blades.

Item		lbs.
No. 28197		.83
Security TORX®: T6s+T8s, T7s+T9s, T10s+T15s, T20s+T25s, T30s+T40s & SoftFinish® Cushion Grip Blade Lock Handle		


[SHOP](#)

28199 10 Pc. Drive-Loc VI Interchangeable Blade Set, In Durable Pouch

Set includes Drive-Loc VI handle & 9 interchangeable blades.

Item		lbs.
No. 28199		1.11
Slotted/Phillips: 4.0+1, 6.0+2 TORX®: T6+T8, T7+T9, T10+T15, T20+T25 Hex Inch: 3/32+7/64, 1/8+9/64, 5/32+3/16"		
Wiha SoftFinish® Cushion Grip Blade Lock Handle		


[SHOP](#)

28189 15 Pc. Drive-Loc VI Interchangeable Blade Set, In Durable Pouch

Set includes Drive-Loc VI handle & 14 interchangeable blades.

Item No. 28189		lbs. 1.28
Slotted: 3.5+4.5, 5.5+6.5 Phillips: 1+2 Security TORX®: T6s+T8s, T7s+T9s, T10s+T15s, T20s+T25s, T30s+T40s Hex Inch: 3/32+7/64, 1/8+9/64, 5/32+3/16 Hex Metric: 2.0+2.5, 3.0+4.0, 5.0+6.0mm		
Wiha SoftFinish® Cushion Grip Blade Lock Handle		

Wiha MicroFinish Handle - Non-Slip Grip

Wiha MicroFinish handle has a patented non-slip surface - it won't peel, crack or deteriorate when exposed to petroleum solvents. Oil and moisture flow away from the handle surface for a powerful, non-slip grip. You get maximum force and comfort with dry, oily or wet hands.

Blade Chrome-vanadium-molybdenum, hardened and tempered tool steel, gives exceptional tool life, wear resistance and high torque performance

Exact fit precision ground tips

Through hardened blades & hard chrome finish

Safe, high density material, eliminates risk of sharp objects becoming embedded in the handle

MicroFinish Handle with patented non slip surface. Ergo handle shape for maximum comfort and exceptional torque transfer

Hex bolster & steel strike cap on 533 & 534 series



[SHOP](#)

520 Slotted Screwdriver, With Wiha-MicroFinish Handle

Blade high alloy chrome-vanadium-molybdenum steel, hardened, hard chromed. Wiha-MicroFinish handle, cellulose-acetate, impact resistant, non-slip, oil and grease resistant. Round blades.

Item No.	mm	Inch	mm	Inch	mm	Inch	mm	Inch	lbs	pkg.
52005*	4.0	.157	100	3.9	0.8	.031	211	8.3	.16	10
52010*	4.0	.157	150	5.9	0.8	.031	261	10.3	.17	10
52020*	5.5	.216	125	5.0	1.0	.039	236	9.3	.20	10
52025*	5.5	.216	150	5.9	1.0	.039	261	10.3	.21	10
52035	6.5	.255	150	5.9	1.2	.047	268	10.6	.28	10
52040	8.0	.315	150	5.9	1.2	.047	274	10.8	.37	10
52050	10.0	.393	200	8.0	1.6	.063	324	12.8	.50	10

*Cabinet Tips



#52090



#52097



52090 5 Piece Slotted & Phillips Screwdriver Set

Blade CVM steel, hardened, hard chromed. Wiha-MicroFinish handle, cellulose acetate, impact resistant, non-slip, oil and grease resistant.

Item No.		lbs.
52090	Slotted: 4.0x100, 5.5x125, 8.0x150mm	lbs.
	Phillips: 1x80, 2x100mm	1.23

52097 7 Piece Slotted & Phillips Screwdriver Set

Item No.		lbs.
52097	Slotted: 4.0x100, 5.5x125, 8.0x150mm	lbs.
	Phillips: #1x80, #1x200, #2x100, #2x200mm	1.34



[SHOP](#)

521 Phillips Screwdriver, With Wiha-MicroFinish Handle

Blade high alloy chrome-vanadium-molybdenum steel, hardened, hard chromed. Wiha-MicroFinish handle, cellulose-acetate, impact resistant, non-slip, oil and grease resistant. Round blades.

Item No.	Size	mm	Inch	mm	Inch	lbs.	pkg.
52105	1	80	3.1	191	7.5	.15	10
52110	1	200	8.0	311	12.2	.21	10
52115	2	100	3.9	218	8.6	.26	10
52120	2	200	8.0	318	12.5	.34	10
52125	3	150	5.9	274	10.8	.41	10



#52098



#52099

52098 8 Piece Slotted & Phillips Screwdriver Set

Blade high alloy CVM steel, hardened, hard chromed. Wiha-MicroFinish® handle, cellulose-acetate, impact resistant, non-slip, oil and grease resistant.

Item No.		lbs.
52098	Slotted: 4.0x100, 5.5x125, 6.5x150, 8.0x150, 10.0x200mm	2.58
	Phillips: 1x80, 2x100, 3x150mm	

52099 12 Piece MicroFinish® Slotted & Phillips Screwdriver Set

Item No.		lbs.
52099	Slotted: 4.0x100, 4.0x150, 5.5x125, 5.5x150, 6.5x150, 8.0x150, 10.0x200mm	4.20
	Phillips: 1x80, 1x200, 2x100, 2x200, 3x150mm	

Wiha MicroFinish Extra Heavy Duty Handle



[SHOP](#)

533 Heavy Duty Slotted Screwdriver, Wiha-MicroFinish Handle & Steel Striking Cap Blade high alloy chrome-vanadium-molybdenum steel, hardened, hard chromed. Hex blade extending through handle with striking plate. Hex bolster for additional torque. Wiha-MicroFinish handle, cellulose-acetate, impact resistant, non-slip, oil and grease resistant.

Item No.	mm	Inch	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
53310*	4.5	.177	90	3.6	1.0	.039	201	7.9	.20	10
53315	5.5	.216	100	3.9	1.0	.039	213	8.4	.33	10
53320	6.5	.255	125	5.0	1.2	.047	238	9.4	.38	10
53325	8.0	.315	150	5.9	1.2	.047	271	10.7	.61	10
53330	10.0	.393	175	7.0	1.6	.063	296	11.7	.65	10

*No hex bolster



[SHOP](#)

534 Heavy Duty Phillips Screwdriver, Wiha-MicroFinish Handle & Steel Striking Cap Blade high alloy chrome-vanadium-molybdenum steel, hardened, hard chromed. Hex blade extending through handle with striking plate. Hex bolster for additional torque. Wiha-MicroFinish handle, cellulose-acetate, impact resistant, non-slip, oil and grease resistant.

Item No.	Size	mm	Inch	mm	Inch	lbs.	pkg.
53405	1	80	3.1	186	7.3	.22	10
53410	2	100	3.9	213	8.4	.37	10
53425	3	150	5.9	268	10.6	.71	10



Safe Non-Slip Grip



[SHOP](#)

53390 5 Piece Slotted & Phillips, Heavy Duty Set Blade chrome-vanadium-molybdenum steel, hardened, hard chromed. Hex blade extending through handle with steel striking cap. Hex bolster for additional torque. Wiha-MicroFinish handle, cellulose-acetate, impact resistant, non-slip, oil and grease resistant.

Item							
No.		mm	mm		Size	mm	lbs.
53390	53315	5.5	100	53405	1	80	2.1
	53320	6.5	125	53410	2	100	
	53325	8.0	150				



[SHOP](#)

53398 8 Piece Slotted & Phillips, Heavy Duty Set Blade chrome-vanadium-molybdenum steel, hardened, hard chromed. Hex blade extending through handle with steel striking cap. Hex bolster for additional torque. Wiha-MicroFinish handle, cellulose-acetate, impact resistant, non-slip, oil and grease resistant.

Item							
No.	mm	mm	Size	mm	lbs.		
53398	53310*	4.5	90	53405	1	80	3.7
	53315	5.5	100	53410	2	100	
	53320	6.5	125	53425	3	150	
	53325	8.0	150				
	53330	10.0	175				

*No hex bolster



[SHOP](#)

52650 1/4 inch Bit holding Screwdriver, With Wiha-MicroFinish Handle Magnetic, holds bit and screw. Retainer out of stainless steel. Shaft chrome-vanadium steel, nickel-plated. Wiha-MicroFinish handle, cellulose-acetate, impact resistant, non-slip, oil and grease resistant.

Item No.	Size	mm	Inch	mm	Inch	lbs.	pkg.
52650	1/4	125	5.0	243	9.6	.24	10

Wiha TORX® MicroFinish Handle Non-Slip Grip

[SHOP](#)
527 TORX® Screwdriver, With Wiha-MicroFinish Handle

Blade high alloy chrome-vanadium-molybdenum steel, hardened, hard chromed. Wiha-MicroFinish handle, cellulose-acetate, impact resistant, non-slip, oil and grease resistant. Round blades.

Item No.	Size	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
52711	T9	60	2.4	4.0	.157	171	6.7	.15	10
52713	T10	80	3.1	4.0	.157	191	7.5	.15	10
52716	T15	80	3.1	4.0	.157	191	7.5	.15	10
52719	T20	100	3.9	4.0	.157	211	8.3	.15	10
52722	T25	100	3.9	4.5	.177	211	8.3	.16	10
52726	T27	115	4.5	5.5	.216	233	9.2	.25	10
52729	T30	115	4.5	6.0	.236	233	9.2	.27	10
52732	T40	130	5.1	7.0	.275	254	10.0	.40	10


[SHOP](#)
52790 Set 5 Pcs. TORX®

Blade chrome-vanadium-molybdenum steel, hardened, round blades hard chromed. Wiha-MicroFinish handle, cellulose-acetate, impact resistant, non-slip, oil and grease resistant.

Item No.	Size	mm	Size	mm	lbs.
52790	52713 T10	80	52722 T25	100	1.0
	52716 T15	80	52729 T30	115	
	52719 T20	100			


[SHOP](#)
52791 Set 8 Pcs. TORX®

Blade chrome-vanadium-molybdenum steel, hardened, round blades hard chromed. Wiha-MicroFinish handle, cellulose-acetate, impact resistant, non-slip, oil and grease resistant.

Item No.	Size	mm	Size	mm	lbs.
52791	52711 T9	60	52722 T25	100	1.89
	52713 T10	80	52726 T27	115	
	52716 T15	80	52729 T30	115	
	52719 T20	100	52732 T40	130	

Wiha Powerhandle TORX®

Made in Germany


[SHOP](#)
362 TORX® Screwdriver, With Wiha-Powerhandle CVM steel

blade, hardened, hard chromed. Wiha-powerhandle cellulose-acetate.

Item No.	Size	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
36205	T5	50	2.0	2.5	.098	110	4.3	.03	10
36210	T6	50	2.0	3.5	.139	125	4.9	.06	10
36212	T7	50	2.0	3.5	.139	125	4.9	.06	10
36215	T8	60	2.4	3.5	.139	135	5.3	.06	10
36220	T9	60	2.4	4.0	.157	140	5.5	.09	10
36225	T10	80	3.1	4.0	.157	170	6.7	.13	10
36230	T15	80	3.1	4.0	.157	170	6.7	.13	10
36235	T20	100	3.9	4.0	.157	200	7.9	.17	10
36240	T25	100	3.9	4.5	.177	200	7.9	.18	10
36245	T27	115	4.5	5.5	.216	215	8.5	.20	10
36250	T30	115	4.5	6.0	.236	225	8.9	.28	10



[SHOP](#)
36292 8 Pc. Set TORX® Blade high alloy CVM steel, hardened, hard chromed. Wiha-powerhandle cellulose-acetate, impact resistant.

Item No.	Includes:	lbs.
36292	T6, T8, T10, T15, T20, T25, T27, T30	1.45


[SHOP](#)
36293 6 Pc. Set TORX® Blade high alloy CVM steel, hardened, hard chromed. Wiha-powerhandle cellulose-acetate, impact resistant.

Item No.	Includes:	lbs.
36293	T6, T7, T8, T9, T10, T15	.78

Wiha **TORX®** Protturn Screwdrivers




45591 Set 6 Pcs. TORX®

Item No.	Size	mm	Size	mm	lbs.
45506	T7	50	45521	T10	80
45511	T8	60	45526	T15	80
45516	T9	60	45531	T20	100

45592 Set 8 Pcs. TORX®

Item No.	Size	mm	Size	mm	lbs.
45511	T8	60	45531	T20	100
45516	T9	60	45536	T25	100
45521	T10	80	45541	T27	115
45526	T15	80	45546	T30	115



45589 Set 14 Pcs. TORX®

Item No.	Size	mm	Size	mm	lbs.
45505	T6	50	45531	T20	100
45506	T7	50	45536	T25	100
45511	T8	60	45541	T27	115
45516	T9	60	45546	T30	115
45521	T10	80	45551	T40	130
45522	T10	275	45556	T45	130
45526	T15	80	45561	T50	130



48400 1/4" Bit Holding Screwdriver, With Wiha-Protturn Handle

Magnetic, holds bit and screw. Retainer out of stainless steel. Shaft CVM steel, nickel-plated. Handle, molded on, impact resistant.



Item No.	Size	mm	Inch	mm	Inch	lbs.	pcs.
48400	1/4	125	5.0	243	9.6	.24	10

455 TORX® Screwdriver, With Wiha-Protturn Handle

Blade high alloy CVM steel, hardened, black finish. Molded on ergonomic Wiha-Protturn handle, impact resistant.

Item No.	Size	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
45505	T6	50	2.0	3.5	.139	129	5.1	.05	10
45506	T7	50	2.0	3.5	.139	129	5.1	.05	10
45511	T8	60	2.4	3.5	.139	139	5.5	.06	10
45516	T9	60	2.4	4.0	.157	149	5.8	.08	10
45521	T10	80	3.1	4.0	.157	170	6.7	.10	10
45522	T10	275	10.8	4.0	.157	363	14.2	.13	10
45526	T15	80	3.1	4.0	.157	170	6.7	.10	10
45531	T20	100	3.9	4.0	.157	190	7.5	.11	10
45536	T25	100	3.9	4.5	.177	190	7.5	.11	10
45541	T27	115	4.5	5.5	.216	215	8.4	.11	10
45546	T30	115	4.5	6.0	.236	215	8.4	.20	10
45551	T40	130	5.1	7.0	.275	240	9.4	.28	10
45556	T45	130	5.1	8.0	.315	240	9.4	.27	10
45561	T50	130	5.1	9.0	.354	240	9.4	.31	10

Wiha Dynamic Series Screwdrivers - Slotted & Phillips



[SHOP](#)

51090 5 Piece Slotted & Phillips Set, Wiha-Dynamic Handle

Item										
No.	mm	Inch	mm	Inch	Size	mm	Inch	lbs.	pkg.	
51090	3.0	.118	80	3.1	0	60	2.3	.68	1	
	4.0	.157	100	3.9	1	80	3.1			
	5.5	.216	125	4.9						



[SHOP](#)

510 Slotted Screwdriver, With Wiha-Dynamic Handle

Blade high alloy chrome-vanadium-molybdenum steel, hardened, hard chromed. Wiha-Dynamic-handle high quality plastic.

Item										
No.	mm	Inch	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
51020	2.0	.08	65	2.5	0.4	.02	165	6.5	.04	10
51025	2.5	.10	75	3.0	0.4	.02	175	6.9	.04	10
51030	3.0	.12	80	3.1	0.5	.02	180	7.1	.05	10
51035	3.5	.14	100	3.9	0.6	.02	205	8.1	.07	10
51040	4.0	.16	100	3.9	0.8	.03	205	8.1	.08	10
51055	5.5	.22	125	5.0	1.0	.04	236	9.3	.14	10
51065	6.5	.26	150	5.9	1.2	.05	267	10.5	.20	10
51080	8.0	.32	175	7.0	1.2	.05	267	11.6	.29	10



[SHOP](#)

51099 11 Piece Slotted & Phillips Set, Wiha-Dynamic Handle

Item	Slotted: 2.0, 2.5, 3.0, 3.5, 4.0,	Phillips
No.	5.5, 6.5, 8.0mm	0, 1, 2
51099		



[SHOP](#)

511 Phillips Screwdriver, With Wiha-Dynamic Handle

Item									
No.	Size	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
51105	0	60	2.4	3.0	1/8	160	6.3	.05	10
51110	1	80	3.1	4.5	3/16	191	7.5	.11	10
51120	2	100	3.9	6.0	1/4	217	8.5	.17	10



[SHOP](#)

90000 Plastic Screwdriver Tool Rack Rack holds all Wiha screwdrivers, with holes for hanging. Made from high quality plastic.

Item	Slotted	Phillips
No.	lbs.	pkg.
90000		

Wiha Magnetizer/Demagnetizer

Magnetize or Demagnetize tools and small parts instantly

Shatterproof Box is made from high quality plastic

Uses 2 C8 industrial permanent magnets



(+) to Magnetize

(-) to Demagnetize

40010 Magnetizer and Demagnetizer

To magnetize and demagnetize steel screwdriver blades, tweezers and similar tools. Box high quality plastic, shock-resistant, green, cadmium free.

Application:

To magnetize, lead tool slowly through the (+) opening, to demagnetize guide tool slowly through the (-) opening.

Item	Slotted	Phillips
No.	Dimensions	lbs.
40010	2.1" x 2.0" x 1.1"	.30

(Parts under 1" Length or 1/8" Diameter may not demagnetize)

[SHOP](#)

Wiha Cabinet Tip Screwdrivers


[SHOP](#)

186 Slotted Cabinet Tip Screwdriver, With Wiha-Square Handle

Blade chrome-vanadium-molybdenum steel, hardened, nickel-plated. Tip parallel to shaft. Series includes extra long dimensions for screws in difficult to reach locations.

Wiha-square handle cellulose-acetate, impact resistant.

Item No.	mm	Inch	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
18601	2.0	.08	40	1.6	0.40	.02	100	4.0	.02	10
18603	2.5	.10	50	2.0	0.40	.02	110	4.3	.02	10
18606	3.0	.12	75	3.0	0.50	.02	150	5.9	.05	10
18609	3.0	.12	100	3.9	0.50	.02	175	6.9	.06	10
18612	3.0	.12	150	5.9	0.50	.02	225	8.9	.06	10
18615	3.0	.12	200	8.0	0.50	.02	285	11.2	.08	10
18624	4.0	.16	100	3.9	0.60	.02	185	7.3	.08	10
18627	4.0	.16	150	5.9	0.60	.02	235	9.3	.10	10
18630	4.0	.16	200	8.0	0.60	.02	285	11.2	.11	10
18642	5.0	.20	100	3.9	0.70	.03	195	7.7	.13	10
18645	5.0	.20	150	5.9	0.70	.03	245	9.6	.15	10
18648	5.0	.20	200	8.0	0.70	.03	295	11.6	.17	10
18651	5.0	.20	300	12.0	0.70	.03	395	15.6	.20	10
18654	6.0	.24	100	3.9	0.90	.04	205	8.1	.19	10
18657	6.0	.24	150	5.9	0.90	.04	255	10.0	.21	10
18663	6.0	.24	300	12.0	0.90	.04	405	15.9	.29	10
18678	8.0	.32	300	12.0	1.20	.05	415	16.3	.39	10
18681	10.0	.39	200	8.0	1.60	.06	315	12.4	.37	10


[SHOP](#)

153 Phillips Screwdriver, With Wiha-Square Handle

Blade chrome-vanadium-molybdenum steel, hardened, nickel-plated.

Wiha-square handle cellulose-acetate, impact resistant.

Item No.	Size	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
15305	0	60	2.4	3.0	.12	135	5.3	.05	10
15310	1	80	3.1	4.5	.18	175	6.9	.11	10
15315	1	200	8.0	4.5	.18	295	11.6	.15	10
15325	2	100	3.9	6.0	.24	205	8.1	.18	10
15330	2	250	10.0	6.0	.24	355	14.0	.27	10
15335	2	350	13.7	6.0	.24	455	17.8	.33	10
15340	3	150	5.9	8.0	.32	265	10.4	.33	10


[SHOP](#)

222 Pozidriv® Screwdriver, With Wiha-Square Handle

Blade chrome-vanadium-molybdenum steel, hardened, nickel-plated.

Wiha-square handle cellulose-acetate, impact resistant.

Item No.	Size	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
22220	1	200	8.0	4.5	.17	295	11.6	.15	10
22230	2	250	9.8	6.0	.23	355	13.9	.27	10
22240	3	150	5.9	8.0	.31	265	10.4	.30	10

Wiha Offset Screwdrivers


[SHOP](#)

161 Phillips Offset Screwdriver, With Handle

For working in confined spaces. Blade CVM special steel, hardened, hard chromed. Handle high quality plastic, impact resistant.

Item No.	Size	mm	Inch	mm	Inch	lbs.	pkg.
16112	1 + 2	125	4.9	5.5	.217	.08	10
16134	3 + 4	200	8.0	10.0	.315	.33	10

207 Slotted Offset Screwdriver, With Handle

Item No.	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
20700	3.5	9/64	90	3.5	0.6	.02	.02	10
20705	4.0	5/32	100	3.9	0.8	.03	.03	10
20710	5.5	7/32	125	5.0	1.0	.04	.06	10
20715	6.5	1/4	125	5.0	1.2	.05	.07	10
20720	8.0	5/16	150	5.9	1.2	.05	.15	10
20725	10.0	3/8	175	6.9	1.6	.06	.23	10


[SHOP](#)

20790 5 Piece Slotted & Phillips Offset Screwdriver Set

Item No.	lbs.	Set includes the following drivers:
20790	.92	Slotted: 6.5, 8.0, 10.0 Phillips: 1 + 2, 3 + 4


[SHOP](#)

207 TORX® Offset Screwdriver With Molded Handle

For working in confined spaces. Blade CVM special steel, hardened, black finish.

Item No.	Size	lbs.	pkg.
20756	T6 + T8	.02	1
20757	T7 + T9	.02	1
20758	T10 + T15	.02	1
20759	T20 + T25	.07	1
20760	T27 + T30	.10	1

20799 TORX® Offset Screwdriver Set, 5 Pcs.

With Molded Handle Blade CVM special steel, hardened, black finish.

Item No.	Set Includes:	lbs.	pkg.
20799	T6+T8, T7+T9, T10+T15, T20+T25, T27+T30	.24	1



Rotating cap
for precise turning and control with fingertip

Precision handle
high quality plastic, cadmium free

Molded on tapered handle
allows rapid rotation

High performance blades
chrome-vanadium-molybdenum steel, Hard chrome finished

Tip
precision ground for exact fit, hard chromed non-slip surface

Wiha Long Life Precision Series



260 Slotted Screwdriver, With Precision Handle

Blade high alloy chrome-vanadium-molybdenum steel.

Item No.	mm	Inch	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
26008	.80	1/32	40	1.6	0.16	.01	120	4.7	.02	10
26010	1.0	.039	40	1.6	0.18	.01	120	4.7	.02	10
26012	1.2	3/64	40	1.6	0.20	.01	120	4.7	.02	10
26015	1.5	1/16	40	1.6	0.25	.01	120	4.7	.02	10
26018	1.8	.070	40	1.6	0.30	.01	120	4.7	.02	10
26020	2.0	5/64	40	1.6	0.40	.02	120	4.7	.02	10
26022	2.0	5/64	50	2.0	0.40	.02	145	5.7	.02	10
26023	2.0	5/64	100	3.9	0.40	.02	180	7.1	.03	10
26025	2.5	3/32	50	2.0	0.40	.02	145	5.7	.03	10
26027	2.5	3/32	100	3.9	0.40	.02	195	7.7	.03	10
26028	2.5	3/32	150	6.0	0.40	.02	245	9.6	.04	10
26030	3.0	1/8	50	2.0	0.50	.02	145	5.7	.03	10
26032	3.0	1/8	60	2.4	0.50	.02	170	6.7	.04	10
26033	3.0	1/8	100	3.9	0.50	.02	210	8.3	.04	10
26034	3.0	1/8	150	5.9	0.50	.02	260	10.2	.05	10
26035	3.5	9/64	60	2.4	0.60	.02	170	6.7	.05	10
26040	4.0	5/32	60	2.4	0.80	.03	170	6.7	.05	10
26041	4.0	5/32	100	3.9	0.80	.03	210	8.3	.06	10
26042	4.0	5/32	150	5.9	0.80	.03	260	10.2	.07	10

*Metric dimensions actual - Inch dimensions approximate

Wiha Precision Chip Lifter & Accessories



26810 Precision Chip Lifter

Blade chrome-vanadium-molybdenum steel, hardened, chrome-plated. Precision handle high quality plastic, impact resistant.

Item No.	mm	mm	mm	mm	Inch	lbs.	pkg.
26810	1	3.5	50	145	5.7	.07	1

Standard handle

*Metric dimensions actual - Inch dimensions approximate



26001 Pocket Clip for Precision Screwdrivers

Tool clips turn Precision Screwdrivers into Pocket Screwdrivers.

Item No.		lbs.	pkg.
26001	Fits all Precision handles	.0035	1



26000 Plastic Precision Tool Rack

Rack holds 6 precision screwdrivers, can be set on workbench. Also has holes for hanging. Made from high quality plastic.

Item No.		lbs.	pkg.
26000	Rack for 6 Precision screwdrivers	.08	1



26090 6 Piece Precision Slotted Set

Blade high alloy chrome-vanadium-molybdenum steel. Hard chrome finished.

Item No.		lbs.
26090	Slotted:	
	1.5, 2.0 x 40mm	.27
	2.5, 3.0 x 50mm	
	3.5, 4.0 x 60mm	



26099 8 Piece Precision Slotted Set

Blade high alloy chrome-vanadium-molybdenum steel.

Hard chrome finished. In canvas storage pouch

Item No.		lbs.
26099	Slotted: 1.0, 1.2, 1.5, 2.0 x 40mm	
	2.5, 3.0 x 50mm, 3.5, 4.0 x 60mm	.54

Wiha Precision Slotted/Phillips Drivers




261 Phillips Screwdriver, With Precision Handle

Blade high alloy chrome-vanadium-molybdenum steel.

[SHOP](#)

Item No.	Size	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
26102	000	40	1.6	2.0	.08	120	4.7	.02	10
26100	00	40	1.6	2.0	.08	120	4.7	.02	10
26101	00	75	3.0	2.0	.08	155	6.1	.02	10
26105	0	50	2.0	3.0	.12	145	5.7	.02	10
26108	0	75	3.0	3.0	.12	170	6.7	.03	10
26107	0	100	3.9	3.0	.12	195	7.6	.05	10
26109	0	150	5.9	3.0	.12	245	9.6	.06	10
26110	1	60	2.4	4.0	.16	170	6.7	.05	10
26113	1	80	3.1	4.0	.16	190	7.5	.05	10
26114	1	100	3.9	4.0	.16	210	8.2	.06	10
26115	1	150	5.9	4.0	.16	260	10.2	.07	10

*Metric dimensions actual - Inch dimensions approximate



26190 7 Piece Precision Slotted & Phillips Set

Blade high alloy chrome-vanadium-molybdenum steel.

[SHOP](#)

Item No.	Slotted:	lbs.
26190	1.5 x 40mm	.31
	2.0, 2.5 x 50mm	
	3.0 x 60mm	
	Phillips:	
	00 x 40mm	
	0 x 50mm, 1 x 60mm	




In canvas storage pouch

[SHOP](#)

26199 8 Piece Precision Slotted/Phillips Set

Blade high alloy CVM steel, hard chrome finished.

Item No.	Slotted:	lbs.
26199	1.0, 2.0 x 40mm, 3.0 x 50mm	.55
	4.0 x 60mm	
	Phillips: 000, 00 x 40mm, 0 x 50mm,	
	1 x 60mm	



[SHOP](#)

26092 7 Piece Precision Slotted & Phillips Set

Blade high alloy chrome-vanadium-molybdenum steel.

Item No.	Slotted:	lbs.
26092	2.5 x 50mm,	.30
	2.5, 3.0, 4.0 x 100mm	
	3.0, 4.0 x 150mm	
	Phillips:	
	0 x 75mm	



[SHOP](#)

26194 4 Piece Precision Phillips Set

Blade high alloy chrome-vanadium-molybdenum steel.
Hard chrome finished.

Item No.	Phillips:	lbs.
26194	000, 00 x 40mm	.18
	0 x 50mm, 1 x 60mm	



[SHOP](#)

26192 5 Piece Precision Slotted & Phillips Set

Blade high alloy chrome-vanadium-molybdenum steel.

Item No.	Slotted:	lbs.
26192	2.5, 3.0, 4.0 x 150mm	.44
	Phillips:	
	0, 1 x 150mm	



[SHOP](#)

91118 Rugged Polyester Canvas Storage Pouch

Holds 8 Precision Tools up to 170mm in length. Folding pouch.
Has security flaps and velcro closer.

Item No.	Size	lbs.	pkg.
91118	14 1/2" W x 7 3/4" L	.13	1

Wiha Pozidriv® Precision Series



SHOP

262 Pozidriv® Screwdriver, With Precision Handle

Blade high alloy chrome-vanadium-molybdenum steel.

Item									
No.	Size	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
26205	0	50	2.0	3.0	.12	145	5.7	.03	10
26210	1	60	2.4	4.0	.16	170	6.7	.05	10

*Metric dimensions actual - Inch dimensions approximate

Wiha Hex Metric Precision Series



SHOP

263 Metric Metric Hex Driver, With Precision Handle

Metric sizes. Blade high alloy chrome-vanadium-molybdenum steel.

Item									
No.	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.	
26307	0.7	.028	40	1.6	120	4.7	.02	10	
26309	0.9	.035	40	1.6	120	4.7	.02	10	
26313	1.3	.050	40	1.6	120	4.7	.02	10	
26315	1.5	-	50	2.0	145	5.7	.03	10	
26320	2.0	5/64	50	2.0	145	5.7	.03	10	
26325	2.5	-	60	2.4	170	6.7	.04	10	
26330	3.0	-	60	2.4	170	6.7	.04	10	
26340	4.0	-	60	2.4	170	6.7	.05	10	

*Metric dimensions actual - Inch dimensions approximate

Wiha Hex Inch Precision Series



SHOP

263 Inch Inch Hex Driver, With Precision Handle

Inch sizes. Blade high alloy chrome-vanadium-molybdenum steel.

Item									
No.	Inch	mm	mm	Inch	mm	Inch	lbs.	pkg.	
26307	0.028	0.7	40	1.6	120	4.7	.02	10	
26309	0.035	0.9	40	1.6	120	4.7	.02	10	
26313	0.05	1.3	40	1.6	120	4.7	.02	10	
26316	1/16	-	50	2.0	145	5.7	.03	10	
26320	5/64	2.0	50	2.0	145	5.7	.03	10	
26323	3/32	-	60	2.4	170	6.7	.04	10	
26327	7/64	-	60	2.4	170	6.7	.04	10	
26331	1/8	-	60	2.4	170	6.7	.04	10	
26333	9/64	-	60	2.4	170	6.7	.05	10	
26336	5/32	-	60	2.4	170	6.7	.05	10	

*Metric dimensions actual - Inch dimensions approximate



SHOP

26391 8 Pc. Precision Hex Driver Set - Inch

Blade high alloy chrome-vanadium-molybdenum steel.

Item No.		
26391	Hex Inch:	lbs.
	0.028, 0.035, 0.05 x 1.6"	.32
	1/16, 5/64 x 2.0"	
	3/32, 7/64, 1/8 x 2.4"	



SHOP

26390 7 Pc. Precision Hex Driver Set - Metric

Blade high alloy chrome-vanadium-molybdenum steel.

Item No.		
26390	Hex Metric:	lbs.
	0.7, 0.9, 1.3 x 40mm	.28
	1.5, 2.0 x 50mm	
	2.5, 3.0 x 60mm	



SHOP


26399 8 Piece Precision Hex Driver Set - Inch

Blade high alloy chrome-vanadium-molybdenum steel.

Hard chrome finished. In canvas storage pouch

Item No.		
26399	Hex Inch: 0.028, 0.035, 0.05 x 1.6"	lbs.
	1/16, 5/64 x 2.0", 3/32, 7/64, 1/8 x 2.4"	.55

Wiha Ball End Precision Series




[SHOP](#)

264 Inch Ball End Hex Inch Screwdriver With Precision Handle

Angle entry up to 30°. Blade high alloy chrome-vanadium-molybdenum steel. Hard chrome finish.

Item No.	Inch	mm	Inch	mm	Inch	lbs.	pkg.
26413	.050	40	1.6	120	4.7	.02	10
26416	1/16	50	2.0	145	5.7	.03	10
26419	5/64	50	2.0	145	5.7	.03	10
26423	3/32	50	2.0	145	5.7	.03	10
26427	7/64	60	2.4	170	6.7	.03	10
26431	1/8	60	2.4	170	6.7	.05	10
26436	9/64	60	2.4	170	6.7	.05	10
26439	5/32	60	2.4	170	6.7	.05	10

*Metric dimensions actual - Inch dimensions approximate



[SHOP](#)

264 Metric Ball End Hex Metric Screwdriver With Precision Handle

Angle entry up to 30°. Blade high alloy CVM steel.

Item No.	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
26413	1.3	0.05	40	1.6	120	4.7	.02	10
26415	1.5	-	50	2.0	145	5.7	.03	10
26420	2.0	-	50	2.0	145	5.7	.03	10
26425	2.5	-	60	2.4	170	6.7	.04	10
26430	3.0	-	60	2.4	170	6.7	.05	10
26440	4.0	-	60	2.4	170	6.7	.05	10

*Metric dimensions actual - Inch dimensions approximate



[SHOP](#)

26491 5 Piece Ball End Hex Driver Set - Metric

Angle entry up to 30°. Blade high alloy chrome-vanadium-molybdenum-steel.

Item No.	Ball End Hex Metric:	lbs.
26491	1.3 x 40mm	.25
	1.5, 2.0 x 50mm	
	2.5, 3.0 x 60mm	



[SHOP](#)

26490 8 Piece Ball End Hex Driver Set - Inch

Angle entry up to 30°.

Blade high alloy chrome-vanadium-molybdenum steel.

Item No.	Ball End Hex Inch:	lbs.
26490	0.05 x 1.6"	.28
	1/16, 5/64, 3/32 x 2.0"	
	7/64, 1/8, 9/64, 5/32 x 2.4"	



[SHOP](#)

26499 8 Piece Ball End Hex Driver Set - Inch

Blade high alloy chrome-vanadium-molybdenum steel. Hard chrome finished. In canvas storage pouch

Item No.	Ball End Hex Inch:	lbs.
26499	0.05 x 1.6", 1/16, 5/64, 3/32 x 2.0"	.62
	7/64, 1/8, 9/64, 5/32 x 2.4"	

Wiha Precision Screwdriver Set



[SHOP](#)

92191 51 Piece Precision Tool Tray Set

Tool box tray. Equipped with 51 precision drivers.

Item No.	Slotted: .8, 1.0, 1.2, 1.5, 1.8, 2.0, 2.5, 3.0, 3.5, 4.0
92191	Phillips: #000, #00, #0, #1
	Torx®: T1, T2, T3, T4, T5, T6, T7, T8, T9, T10
lbs. 3.14	Metric Hex: 1.3, 1.5, 2.0, 2.5, 3.0, 4.0
	Inch Hex: .028, .035, .05, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"
	Metric Nut Drivers: 1.5, 1.8, 2.0, 2.5, 3.0, 3.5, 4.0, 4.5, 5.0, 5.5
	26810 Chip Lifter

Wiha TORX® Precision Series



267 TORX® Screwdriver, With Precision Handle

Blade high alloy chrome-vanadium-molybdenum steel.

Item No.	Size	mm	Inch	mm	Inch	lbs.	pkg.
26701	T1	40	1.6	120	4.7	.01	10
26702	T2	40	1.6	120	4.7	.02	10
26703	T3	40	1.6	120	4.7	.02	10
26704	T4	40	1.6	120	4.7	.02	10
26705	T5	40	1.6	120	4.7	.02	10
26706	T6	40	1.6	120	4.7	.02	10
26707	T7	40	1.6	120	4.7	.02	10
26708	T8	40	1.6	120	4.7	.03	10
26709	T9	50	2.0	145	5.7	.03	10
26710	T10	50	2.0	145	5.7	.03	10
26715	T15	60	2.4	170	6.7	.05	10
26720	T20	60	2.4	170	6.7	.05	10

*Metric dimensions actual - Inch dimensions approximate

SHOP

Wiha Pentalobe IPR Precision Series

Wiha Pentalobe IPR drivers will fit fasteners used in "Apple" brand products including iPhone, Mac Book & Mac Air



- Exact fit precision machined Pentalobe tips
- High performance CRM72 tool steel
- Hard chromed finish blades & tips
- Tapered ergonomic handle
- Easy spin finger tip control cap



267 Pentalobe IPR Screwdriver, With Precision Handle

Blade high alloy chrome-vanadium-molybdenum steel.

Item No.	Size	mm	Inch	mm	Inch	lbs.	pkg.
26761	P1	40	1.6	120	4.7	.01	1
26762	P2	40	1.6	120	4.7	.02	1
26763	P3	40	1.6	120	4.7	.02	1
26764	P4	40	1.6	120	4.7	.02	1
26765	P5	40	1.6	120	4.7	.02	1
26766	P6	40	1.6	120	4.7	.02	1

*Metric dimensions actual - Inch dimensions approximate

SHOP



26790 6 Pc. TORX® Screwdriver Set

Blade high alloy chrome-vanadium-molybdenum steel.

Item No.	lbs.
26790 TORX®:	
T6, T7, T8 x 40mm	.30
T9, T10 x 50mm	
T15 x 60mm	

26791 Set 8 Pcs. TORX® Screwdriver Set

Item No. 26791 T1, T2, T3, T4, T5, T6, T7, T8

SHOP



26794 6 Pc. Precision Pentalobe IPR Screwdriver Set

Blade high alloy chrome-vanadium-molybdenum steel.

Hard chrome finished. Super hardened best wear resistance long life

Item No.	Pentalobe IPR Drivers:	lbs.
26794	P1, P2, P3, P4, P5, P6	.35

SHOP

Wiha Precision Screwdriver Set



SHOP

92190 Master Technicians Bench Top Set

Metal frame. Equipped with 50 precision drivers.

Item No.	Slotted: .8, 1.0, 1.2, 1.5, 1.8, 2.0, 2.5, 3.0, 3.5, 4.0
92190	Phillips: #000, #00, #0, #1
	Torx®: T1, T2, T3, T4, T5, T6, T7, T8, T9, T10
lbs. 2.86	Metric Hex: 1.3, 1.5, 2.0, 2.5, 3.0
	Inch Hex: .028, .035, .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"
	Metric Nut Drivers: 1.5, 1.8, 2.0, 2.5, 3.0, 3.5, 4.0, 4.5, 5.0, 5.5
	26810 Chip Lifter



SHOP

26799 8 Pc. TORX® Screwdriver Set

Blade high alloy chrome-vanadium-molybdenum steel.

Hard chrome finished. In canvas storage pouch

Item No.	lbs.
26799 TORX®:	
T3, T4, T5, T6, T7, T8 x 40mm	.50
T9 x T10 x 50mm	



SHOP

26792 7 Pc. TORX® Screwdriver Set

Blade high alloy chrome-vanadium-molybdenum steel.

Item No.	lbs.
26792 TORX®:	
T5, T6, T7, T8 x 40mm	.33
T9, T10 x 50mm	
T15 x 60mm	

Wiha Soft Grip PicoFinish Precision Screwdrivers

The Comfortable Precision Screwdriver



Color coded symbols on rotating cap gives easy recognition of individual styles & sizes

CVM tool steel blade, hardened, hard chrome finish



Soft Grip Handle



Ergonomic multi-component handle with rotating cap for maximum user comfort and precise control



SHOP

260 Slotted Precision Screwdriver, With PicoFinish Handle

Blade CVM steel, hardened, hard chrome.

Item No.	mm	Inch	mm	Inch	mm	Inch	Pkg.
26050	0.8	.03	40	1.6	134	5.3	10
26051	1.0	.04	40	1.6	134	5.3	10
26052	1.2	.05	40	1.6	134	5.3	10
26053	1.5	.06	40	1.6	134	5.3	10
26054	1.5	.06	60	2.4	154	6.1	10
26055	1.8	.07	40	1.6	134	5.3	10
26056	1.8	.07	60	2.4	154	6.1	10
26060	2.0	.08	40	1.6	140	5.5	10
26061	2.0	.08	60	2.4	160	6.3	10
26063	2.0	.08	100	3.9	200	7.9	10
26065	2.5	.09	50	2.0	150	5.9	10
26066	2.5	.09	75	3.0	175	6.9	10
26068	2.5	.09	100	3.9	200	7.9	10
26070	3.0	.13	50	2.0	150	5.9	10
26072	3.0	.13	100	3.9	200	7.9	10
26073	3.0	.13	150	5.9	250	9.8	10
26074	3.5	.14	60	2.4	160	6.3	10
26076	4.0	.16	60	2.4	160	6.3	10
26079	4.0	.16	100	3.9	200	7.9	10
26080	4.0	.16	150	5.9	250	9.8	10

*Metric dimensions actual - Inch dimensions approximate



SHOP

261 Phillips Precision Screwdriver, With Soft PicoFinish

Precision Handle Blade high alloy chrome-vanadium-molybdenum steel. Hard chrome finished.

Item No.	Size	mm	Inch	mm	Inch	mm	Inch	pkg.
26130	000	40	1.6	2.0	.08	134	5.3	10
26132	00	40	1.6	2.0	.08	134	5.3	10
26133	00	60	2.4	2.0	.08	154	6.1	10
26135	0	50	2.0	3.0	.12	150	5.9	10
26136	0	75	3.0	3.0	.12	175	6.9	10
26140	1	60	2.4	4.0	.16	160	6.3	10
26142	1	80	3.1	4.0	.16	180	7.1	10
26145	1	150	5.9	4.0	.16	250	9.8	10

*Metric dimensions actual - Inch dimensions approximate



SHOP

26193 8 Pc. Slotted & Phillips Precision Driver Set, With Soft

PicoFinish Handle Blade high alloy CVM steel, hardened, hard chrome. ChromTop finish on tip for a perfect fit. In storage pouch

Item No.		
26193	Slotted: 1.0, 1.5, 2.0 x 40mm 2.5 x 50mm, 3.5 x 60mm Phillips: 00 x 40mm 0 x 50mm, 1 x 60mm	lbs. .55



SHOP

26093 8 Pc. Slotted Precision Screwdriver Set, With Soft

PicoFinish Handle In storage pouch

Item No.		
26093	Slotted: .8, 1.2, 1.5, 2.0 x 40mm 2.5, 3.0 x 50mm, 3.5, 4.0 x 60mm	lbs. .54

Wiha Pico Soft Grip TORX®



[SHOP](#)

267 TORX® Screwdriver, With Precision Soft PicoFinish Handle

Blade high alloy chrome-vanadium-molybdenum tool steel, hardened, hard chrome finish.

Item No.	Size	mm	Inch	mm	Inch	pkg.
26732	T1	40	1.6	134	5.3	10
26733	T2	40	1.6	134	5.3	10
26735	T3	40	1.6	134	5.3	10
26736	T4	40	1.6	134	5.3	10
26737	T5	40	1.6	134	5.3	10
26739	T6	40	1.6	140	5.5	10
26741	T7	40	1.6	140	5.5	10
26743	T8	40	1.6	140	5.5	10
26745	T9	50	2.0	150	5.9	10
26747	T10	50	2.0	150	5.9	10
26749	T15	60	2.4	160	6.3	10
26751	T20	60	2.4	160	6.3	10

*Metric dimensions actual - Inch dimensions approximate



[SHOP](#)

26793 8 Pc. TORX® Precision Driver Set, With Soft PicoFinish Handle

Blade high alloy CVM steel, hardened, hard chromed. ChromTop finish on tip for a perfect fit. In storage pouch

Item No.		lbs.
26793	TORX® : T1, T2, T3, T4, T5, T6, T7, T8 x 40mm	.50



[SHOP](#)

26796 8 Pc. TORX® Precision Driver Set, Soft PicoFinish Handle

Blade high alloy CVM steel, hardened, hard chromed. ChromTop finish on tip for a perfect fit. In storage pouch

Item No.		lbs.
26796	TORX®: T5, T6, T7, T8 x 40mm T9, T10 x 50mm, T15, T20 x 60mm	.57

Wiha Pico Soft Grip Screw Holding



[SHOP](#)

267 MagicSpring Screw Holding TORX® Screwdriver, With

Wiha-Precision Soft PicoFinish Handle Blade high alloy CVM steel, hardened, hard chromed. Molded on ergonomic Wiha-PicoFinish precision handle, molded on, soft grips.

Item No.	Size	mm	Inch	mm	Inch	lbs.	pkg.
26721	T6	40	1.6	140	5.5	.03	10
26723	T7	40	1.6	140	5.5	.03	10
26725	T8	40	1.6	140	5.5	.03	10
26727	T9	50	2.0	150	5.9	.04	10
26729	T10	50	2.0	150	5.9	.04	10
26731	T15	60	2.4	160	6.3	.04	10

*Metric dimensions actual - Inch dimensions approximate



[SHOP](#)

26798 6 Pc. MagicSpring Screw Holding TORX® Screwdriver Set, With Wiha-Precision Soft PicoFinish Handle

Blade high alloy CVM steel, hardened, hard chromed. Molded on ergonomic Wiha-PicoFinish precision handle, molded on, soft grips. In storage pouch

Item No.		lbs.
26798	MagicSpring TORX® : T6, T7, T8 x 40mm T9, T10 x 50mm, T15 x 60mm	.45

Pico Soft Grip Precision Chip Lifter



[SHOP](#)

26815 Soft PicoFinish Precision Chip Lifter

Blade chrome-vanadium-molybdenum steel, hardened, hard chromed.

Item No.	mm	mm	mm	mm	Inch	lbs.	pkg.
26815	1	3.5	50	150	5.9	.03	1

Standard Soft PicoFinish handle

Pico Soft Grip Hex Inch & Metric



[SHOP](#)

263 Hex Inch Screwdriver, With Precision Soft PicoFinish Handle

Blade high alloy CVM tool steel, hardened, hard chrome finish.

Item No.	Inch	mm	Inch	mm	Inch	pkg.
26341	0.028(0.7)	40	1.6	134	5.3	10
26343	0.035(0.9)	40	1.6	134	5.3	10
26345	0.05(1.3)	40	1.6	134	5.3	10
26349	5/64(2.0)	50	2.0	150	5.9	10
26363	1/16	50	2.0	144	5.7	10
26367	3/32	60	2.4	160	6.3	10
26369	7/64	60	2.4	160	6.3	10
26371	1/8	60	2.4	160	6.3	10

*Metric dimensions actual - Inch dimensions approximate



[SHOP](#)

26392 8 Piece Hex Inch Precision Driver Set, Soft PicoFinish Handle

Blade high alloy CVM steel, hardened, hard chromed.

Item No.	Hex Inch:	lbs.
26392	0.028, 0.035, 0.05 x 1.6"	
	5/64, 1/16 x 2.0", 3/32, 7/64, 1/8 x 2.4"	.24



[SHOP](#)

263 Hex Metric Driver, With Precision Soft PicoFinish Handle

Blade high alloy CVM tool steel, hardened, hard chrome finish.

Item No.	mm	mm	Inch	mm	Inch	pkg.
26341	0.7(0.028)	40	1.6	134	5.3	10
26343	0.9(0.035)	40	1.6	134	5.3	10
26345	1.3(0.05)	40	1.6	134	5.3	10
26347	1.5	50	2.0	144	5.7	10
26349	2.0(5/64)	50	2.0	150	5.9	10
26351	2.5	60	2.4	160	6.3	10
26353	3.0	60	2.4	160	6.3	10

*Metric dimensions actual - Inch dimensions approximate



[SHOP](#)

26393 7 Piece Hex Metric Precision Driver Set, Soft PicoFinish Handle

Blade high alloy CVM steel, hardened, hard chromed.

Item No.	Hex Metric:	lbs.
26393	0.7, 0.9, 1.3 x 40mm	
	1.5, 2.0 x 50mm, 2.5, 3.0 x 60mm	.22

Pico Soft Grip Ball End Inch & Metric



[SHOP](#)

264 Ball End Hex Inch Screwdriver, With Precision Soft

PicoFinish Handle Blade high alloy chrome-vanadium-molybdenum tool steel, hardened, hard chrome finish.

Item No.	Inch	Inch	mm	Inch	mm	pkg.
26455	1/16	2.0	50	5.9	150	10
26457	5/64	2.0	50	5.9	150	10
26459	3/32	2.0	50	5.9	150	10
26461	7/64	2.4	60	6.3	160	10
26463	1/8	2.4	60	6.3	160	10
26465	9/64	2.4	60	6.3	160	10
26467	5/32	2.4	60	6.3	160	10

*Metric dimensions actual - Inch dimensions approximate



[SHOP](#)

26493 7 Piece Inch Ball End Hex Precision Driver Set, With

Soft PicoFinish Handle Blade high alloy CVM steel, hardened, hard chromed. ChromTop finish on tip for a perfect fit.

Item No.	Ball End Hex Inch:	lbs.
26493	1/16, 5/64, 3/32 x 2.0"	
	7/64, 1/8, 9/64, 5/32 x 2.4"	.27



[SHOP](#)


264 Ball End Hex Metric Screwdriver, With Precision Soft

PicoFinish Handle. Blade high alloy chrome-vanadium-molybdenum tool steel, hardened, hard chrome finish.

Item No.	mm	mm	Inch	mm	Inch	pkg.
26441	1.3	40	1.6	134	5.3	10
26443	1.5	50	2.0	150	5.9	10
26445	2.0	50	2.0	150	5.9	10
26447	2.5	60	2.4	160	6.3	10
26449	3.0	60	2.4	160	6.3	10

*Metric dimensions actual - Inch dimensions approximate

Wiha Protturn Precision Screwdrivers



[SHOP](#)

62990 5 Piece Slotted & Phillips Pocket Pack Set Wiha Protturn precision ball retainer handle & 4 Wiha interchangeable blades.

62990 Set includes the following blades:

⌚ **Slotted:** 1.5, 2.0, 3.0, 4.0

⊕ **Phillips:** #000, #00, #0, #1

⚖ **lbs.** .15



[SHOP](#)

95190 6 Piece Slotted/Phillips Protturn Precision Screwdriver Set

Molded on precision handle. Blade high alloy chrome-vanadium-molybdenum tool steel, black finish.

Item No.	⌚ mm	⌚ mm	⊕ Size	⊕ mm	⚖ lbs.
95190	Slotted:	1.5mm	40	Phillips:	.27
		2.5mm	50		
		3.5mm	60		



[SHOP](#)

65090 9 Piece Slotted/Phillips Protturn Precision Screwdriver Set

Molded on precision handle. Blade high alloy chrome-vanadium-molybdenum tool steel, black finish.

Item No.	⌚ mm	⌚ mm	⌚ mm	⌚ mm	⊕ Size	⊕ mm
65090	Slotted:	1.5	40	3.0	60	Phillips:
		2.0	50	3.5	60	
		2.5	60	4.0	60	



[SHOP](#)

96800 Protturn Precision Chip Lifter

Molded on precision handle. Blade chrome-vanadium-molybdenum tool steel, hardened, black finish.

Item No.	Size	mm	mm	Inch	lbs.	pkg.
96800	1.0	50	145	5.7	.07	1



[SHOP](#)

62993 9 Piece Slotted/Phillips/TORX® Work Station Set Wiha Protturn precision ball retainer handle & 8 Wiha interchangeable blades.

62993 Set includes the following blades:

⌚ **Slotted:** 1.5, 2.0, 3.0, 4.0


⊕ **Phillips:** #000, #00, #0, #1

⚙ **TORX®:** T6, T7, T8, T9, T10, T15, T20

⚖ **lbs.** .35

#62995

#62994



[SHOP](#)

62995 22 Piece Slotted/Phillips/TORX®/Ball End Hex Inch & Metric Tech Pack Wiha Protturn precision ball retainer handle & 21 Wiha interchangeable blades. Set in canvas storage pouch

62995 Set includes the following blades:

⌚ **Slotted:** 1.5, 2.0, 3.0, 4.0 ⊕ **Phillips:** #000, #00, #0, #1

⚙ **TORX®:** T6, T7, T8, T9, T10, T15, T20

⬡ **Hex Inch:** .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"

⬡ **Hex Metric:** 1.5, 2.0, 2.5, 3.0, 4.0mm

⚖ **lbs.** .87

62994 14 Piece Inch/Metric Ball End Hex Work Tech Pack

Protturn precision ball retainer handle & 13 Wiha interchangeable blades.

62994 Set includes the following blades:

⬡ **Hex Inch:** .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"

⬡ **Hex Metric:** 1.5, 2.0, 2.5, 3.0, 4.0mm

⚖ **lbs.** .66 Set in canvas storage pouch



Wiha SYSTEM 4 Precision Handles and Blades


[SHOP](#)

26900 SYS 4 Standard Precision Handle, with rotating control cap. Accepts all SYSTEM 4 interchangeable blades. Wiha Precision handle, tapered, impact resistant. Ball retainer hold. 110mm/4.3" OAL

Item					
No.	mm	Inch	mm	Inch	lbs.
26900	4.0	.1574	14.0	.55	.04


[SHOP](#)

26901 SYSTEM 4 Standard Precision Adjustable handle with rotating control cap. **Advantages:**

- Allows adjustable blade from 15 to 95mm.
- Collet lock allows for quick & easy adjustment.
- Holds blade securely in place. Accepts all SYSTEM 4 blades. 110mm/4.3" OAL

Item					
No.	mm	Inch	mm	Inch	lbs.
26901	4.0	.1574	14.0	.55	.06


[SHOP](#)

28000 ESD Safe Dissipative Precision Handle with rotating control cap. Surface resistant 10⁶-10⁹ Ohms. 4 mm hex retainer for all SYSTEM 4 interchangeable blades. Tapered handle, high quality plastic, impact resistant. Ball retainer hold. 110mm/4.3" OAL

Item					
No.	mm	Inch	mm	Inch	lbs.
28000	4.0	.1574	14.0	.55	.04


[SHOP](#)

28001 ESD Safe Dissipative Precision Adjustable Handle with rotating control cap. **Advantages:**

- Use in ESD sensitive applications. Surface resistant 10⁶-10⁹ Ohms.
- Collet lock allows for quick & easy adjustment.
- Holds blade securely in place. Accepts all SYSTEM 4 blades. 110mm/4.3" OAL

Item					
No.	mm	Inch	mm	Inch	lbs.
28001	4.0	.1574	14.0	.55	.04

Rotating Cap for precise turning and control

Tapered Handle allows rapid rotation, requires less clearance

Precision Handle high quality plastic. ESD Safe or Standard styles

Tips Exact fit, precision machined

Blades CVM steel, hardened, hard chromed. On 4mm Hex shafts


[SHOP](#)

269 SYSTEM 4 Slotted Reversible Blade High alloy CVM steel, hardened, hard chromed. Wiha vapor Chrome-Top finish on tips.

Item					
No.	mm	mm	mm	Inch	lbs.
26903	1.5 + 3.0	120	4.7	.05	
26904	2.0 + 3.5	120	4.7	.05	
26905	2.5 + 4.0	120	4.7	.06	


[SHOP](#)

269 SYSTEM 4 Phillips Reversible Blade High alloy CVM steel, hardened, hard chromed. Wiha vapor Chrome-Top finish on tips.

Item					
No.	Size	Size	mm	Inch	lbs.
26911	000 + 00	120	4.7	.03	
26912	0 + 1	120	4.7	.03	


[SHOP](#)

269 SYSTEM 4 Combined Slotted/Phillips Reversible Blade

Item					
No.	mm	Size	mm	Inch	lbs.
26971	1.5 + 000	120	4.7	.05	
26972	2.0 + 00	120	4.7	.05	
26973	3.0 + 0	120	4.7	.05	
26974	4.0 + 1	120	4.7	.06	


[SHOP](#)

269 SYSTEM 4 Pozidriv® Reversible Blade High alloy CVM steel, hardened, hard chromed. Wiha vapor Chrome-Top finish on tips.

Item					
No.	Size	Size	mm	Inch	lbs.
26922	0 + 1	120	4.7	.03	


[SHOP](#)

269 SYSTEM 4 Metric Ball End & Standard Hex, Reversible Blade CVM steel, hardened, hard chromed. Wiha vapor Chrome-Top finish on tips. One side hex, other side ballpoint hex.

Item					
No.	mm	mm	mm	Inch	lbs.
26932	1.3 + 1.3	120	4.7	.05	
26933	1.5 + 1.5	120	4.7	.05	
26934	2.0 + 2.0	120	4.7	.06	
26935	2.5 + 2.5	120	4.7	.06	
26936	3.0 + 3.0	120	4.7	.06	
26937	4.0 + 4.0	120	4.7	.06	


[SHOP](#)

280 SYSTEM 4 Metric Ball End Hex Interchangeable Blade High alloy tool steel, hardened, corrosion protected. Ball end works at 30° angle entry for easy access to fasteners.

Item					
No.	mm	mm	Inch	lbs.	pkg.
28033	1.5	120	4.7	.06	1
28034	2.0	120	4.7	.06	1
28035	2.5	120	4.7	.06	1
28036	3.0	120	4.7	.06	1
28037	4.0	120	4.7	.06	1


[SHOP](#)

280 SYSTEM 4 Inch Ball End Hex Interchangeable Blade High alloy tool steel, hardened, corrosion protected. Ball end works at 30° angle entry for easy access to fasteners.

Item					
No.	Inch	mm	Inch	lbs.	
28021	0.05	120	4.7	.06	
28023	1/16	120	4.7	.06	
28024	5/64	120	4.7	.06	
28025	3/32	120	4.7	.06	
28026	7/64	120	4.7	.06	
28027	1/8	120	4.7	.06	
28028	9/64	120	4.7	.06	
28029	5/32	120	4.7	.06	

Wiha SYSTEM 4 Precision Blades


[SHOP](#)

269 SYSTEM 4 Metric Hex Sizes, Interchangeable Blade High alloy CVM steel, hardened, corrosion protected.

Item				
No.	mm	mm	Inch	lbs.
26913	0.7	120	4.7	.06
26914	0.9	120	4.7	.06
26915	1.3	120	4.7	.06
26916	1.5	120	4.7	.06
26917	2.0	120	4.7	.06
26918	2.5	120	4.7	.06
26919	3.0	120	4.7	.06
26920	4.0	120	4.7	.06


[SHOP](#)

269 SYSTEM 4 Inch Hex Sizes, Interchangeable Blade High alloy CVM steel, hardened, corrosion protected.

Item				
No.	Inch	mm	Inch	lbs.
26921	0.05	120	4.7	.06
26923	1/16	120	4.7	.06
26924	5/64	120	4.7	.06
26925	3/32	120	4.7	.06
26926	7/64	120	4.7	.06
26927	1/8	120	4.7	.06
26928	9/64	120	4.7	.06
26929	5/32	120	4.7	.06


[SHOP](#)

269 SYSTEM 4 TORX® Reversible Blade High alloy CVM steel, hardened, vapor chrome protected, Wiha vapor Chrome-Top finish on tips. 120mm/4.7" OAL.

Item			
No.	Size	Size	lbs.
26951	T6 + T8		.03
26952	T7 + T9		.03
26953	T10 + T15		.03
26954	T15 + T20		.03


[SHOP](#)

269 SYSTEM 4 TORX® Interchangeable Blade High alloy CVM steel, hardened, Wiha vapor Chrome-Top finish on tips. 120mm/4.7" OAL.

Item		
No.	Size	lbs.
26955	T3	.03
26956	T4	.03
26957	T5	.03

Wiha SYSTEM 4 Drive-Loc Precision Locking Tools


[SHOP](#)

26961 ESD Safe Dissipative Precision Drive-Loc Handle Surface resistant 10⁶-10⁹ Ohms. 4 mm hex retainer for all SYSTEM 4 interchangeable blades. Ball retainer hold. 105mm/4.13" OAL

Item					
No.	mm	Inch	mm	Inch	lbs.
26961	4.0	.1574	23	.91	.08



269 SYSTEM 4 Slotted Drive-Loc Reversible Locking Blades On 4mm Hex

Item			
No.	mm	mm	lbs.
26958	1.5 + 3.0		.02
26959	2.0 + 3.5		.02
26960	2.5 + 4.0		.02



269 SYSTEM 4 Phillips Drive-Loc Reversible Locking Blades On 4mm Hex

Item			
No.	Size	Size	lbs.
26975	000 + 00		.02
26976	0 + 1		.02



269 SYSTEM 4 TORX® Drive-Loc Reversible Locking Blades On 4mm Hex

Item			
No.	Size	Size	lbs.
26977	T1 + T2		.02
26978	T3 + T4		.02
26979	T5 + T6		.02
26980	T6 + T8		.02
26981	T7 + T9		.02
26982	T10 + T15		.02



280 SYSTEM 4 Pozidriv® Drive-Loc Reversible Locking Blades On 4mm Hex

Item			
No.	Size	Size	lbs.
28002	0 + 1		.02



280 SYSTEM 4 Metric Hex Drive-Loc Reversible Locking Blades On 4mm Hex blades

Item			
No.	mm	mm	lbs.
28003	1.3 + 1.3		.02
28004	1.5 + 1.5		.02
28005	2.0 + 2.0		.02
28006	2.5 + 2.5		.02
28007	3.0 + 3.0		.02
28008	4.0 + 4.0		.02



280 SYSTEM 4 Metric Nut Drivers Drive-Loc Reversible Locking Blades On 4mm Hex blades

Item			
No.	mm	mm	lbs.
28009	1.5 + 1.8		.02
28010	2.0 + 2.5		.02
28011	3.0 + 3.0		.02
28012	3.2 + 3.2		.02
28013	3.5 + 3.5		.02
28014	4.0 + 4.0		.02
28015	4.5 + 4.5		.02
28016	5.0 + 5.0		.02
28017	5.5 + 5.5		.02


[SHOP](#)

26985 12 Piece SYSTEM 4 Precision ESD Drive-Loc Set In storage pouch

Item No.	
26985	ESD Safe Drive-Loc Handle
	Slotted: 1.5x3.0, 2.0x3.5, 2.5x4.0
	lbs. .44
	Phillips: 000x00, 0x1
	TORX®: T1xT2, T3xT4, T5xT6, T6xT8, T7xT9, T10xT15

Wiha Canvas Pouch Sets


[SHOP](#)

26990 4 Piece Slotted & Phillips Precision Interchangeable Blade Set

Wiha ESD Safe  precision collet lock handle and 3 Wiha interchangeable blades.



26990 Set includes the following blades:

↓  **Slotted:** 2.0, 3.0, 4.0mm

⊕ **Phillips:** 00, 0, 1

↪ lbs. .17

Canvas Pouch


[SHOP](#)

26991 6 Piece Slotted & Phillips Precision Interchangeable Blade Set

Wiha ESD Safe  precision collet lock handle and 5 Wiha interchangeable blades. In canvas pouch.


26991 Set includes the following blades:

↓  **Slotted:** 1.5, 2.0, 2.5, 3.0, 3.5, 4.0mm

⊕ **Phillips:** 000, 00, 0, 1

↪ lbs. .29

Canvas Pouch


[SHOP](#)

26992 17 Pc. Slotted, Phillips and Ball End Hex Metric/Inch Precision Interchangeable Blade Set

Wiha ESD Safe  precision collet lock handle and 15 Wiha interchangeable blades.

26992 Set include the following blades:

↓  **Slotted:** 1.5, 2.0, 3.0, 4.0mm

⊕ **Phillips:** 000, 00, 0, 1

⬢ **Ball End Hex Inch:** .050, 1/16, 5/64, 7/64, 3/32, 1/8"

⬢ **Ball End Hex Metric:** 1.5, 2.0, 2.5, 3.0, 4.0mm

Protturn Chip Lifter - #96800

↪ lbs. .63

Canvas Pouch



Slotted, Phillips, TORX® Set In Steel Box


[SHOP](#)

28094 11 Piece Slotted, Phillips & TORX® Precision Interchangeable Blade Set

Wiha ESD Safe  precision collet lock handle and 10 Wiha interchangeable blades.

28094 Set includes the following blades:

↓  **Slotted:** 1.5, 2.0, 3.0, 4.0mm

⊕ **Phillips:** 000, 00, 0, 1

⬢ **TORX®:** T3, T4, T5, T6, T7, T8, T9, T10, T15

↪ lbs. 1.51


[SHOP](#)

28080 22 Piece Slotted, Phillips, TORX® & Hex Precision Interchangeable Blade Set

Wiha ESD Safe  precision collet lock handle and 20 Wiha interchangeable blades.

28080 Set includes the following blades:

↓  **Slotted:** 1.5, 2.0, 3.0, 4.0mm

⊕ **Phillips:** 000, 00, 0, 1

⬢ **TORX®:** T3, T4, T5, T6, T7, T8, T9, T10, T15

⬢ **Hex Sizes:** .028, .035

⬢ **Ball Hex:** .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"


Protturn Chip Lifter - #96800

↪ lbs. .33

Canvas Pouch



ESD Technicians Kit Precision Screwdrivers & Tweezers


[SHOP](#)


44590 12 Pc. Slotted, Phillips and TORX® Precision Interchangeable Blade Set

Wiha ESD Safe  precision collet lock handle, 7 Wiha interchangeable blades & 4 ESD Safe Tweezers.

44590 Set includes the following blades:

↓  **Slotted:** 2.0, 3.0, 4.0mm

⊕ **Phillips:** 00, 0, 1

⬢ **TORX®:** T6, T7, T8, T9, T10, T15

ESD Safe Precision Tweezers:

44501 Fine Point - AA SA


44509 Extra Fine Point - 5 SA

44505 Flat and Blunt - 2a SA


44510 Curved Fine Point - 7a SA

↪ lbs. .60

Canvas Pouch



Slotted & Phillips Set In Steel Box


[SHOP](#)

26993 6 Piece Slotted & Phillips Precision Interchangeable Blade Set

Wiha ESD Safe  precision collet lock handle and 5 Wiha interchangeable blades.

26993 Set includes the following blades:

↓  **Slotted:** 1.5, 2.0, 2.5, 3.0, 3.5, 4.0mm

⊕ **Phillips:** 000, 00, 0, 1

↪ lbs. .87



ESD Anti-Static Vinyl Pouch Set



[SHOP](#)

28091 6 Piece Slotted & Phillips Precision Interchangeable Blade Set

Wiha-ESD Safe  precision collet lock handle and 5 Wiha interchangeable blades.

28091 Set includes the following blades:

↓  **Slotted:** 1.5, 2.0, 2.5, 3.0, 3.5, 4.0mm

⊕ **Phillips:** 000, 00, 0, 1

↔ **lbs.** .25



[SHOP](#)

28097 9 Piece Slotted, Phillips and TORX® Precision Interchangeable Blade Set

Wiha ESD Safe  precision collet lock handle and 8 Wiha Interchangeable blades.


28097 Set includes the following blades:

↓  **Slotted:** 1.5, 2.0, 3.0, 4.0mm

⊕ **Phillips:** 000, 00, 0, 1

⊗ **TORX®:** T5, T6, T7, T8, T9, T10, T15

↔ **lbs.** .33



[SHOP](#)

28084 13 Piece Slotted, Phillips and Ball End Hex Inch Precision Interchangeable Blade Set

Wiha ESD Safe  precision collet lock handle and 12 Wiha interchangeable blades.

28084 Set includes the following blades:

↓  **Slotted:** 1.5, 2.0, 3.0, 4.0mm

⊕ **Phillips:** 000, 00, 0, 1

⬢ **Ball End Hex Inch:** .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"

↔ **lbs.** .44



[SHOP](#)

28087 8 Piece TORX® Precision Interchangeable Blade Set

Wiha-ESD Safe  precision collet lock handle and 7 Wiha interchangeable blades.


28087 Set includes the following blades:

⊗ **TORX® sizes on standard blades:** T3, T4, T5

⊗ **TORX® sizes on reversible blades:**

T6, T7, T8, T9, T10, T15, T20

↔ **lbs.** .29



[SHOP](#)

26996 5 Piece Slotted & Phillips Precision Interchangeable Blade Set

Wiha ESD Safe  precision collet lock handle and 4 Wiha interchangeable blades. In metal storage box.

26996 ⊕ **Phillips:** 000, 00, 0, 1

↓  **Slotted:** 1.5, 2.0, 3.0, 3.5mm

↔ **lbs.** .24



[SHOP](#)

26997 9 Pc. Slotted, Phillips and TORX® Precision Interchangeable Blade Set

Wiha ESD Safe  precision collet lock handle & 8 Interchangeable blades. In metal storage box.

26997 ⊕ **Phillips:** 000, 00, 0, 1

↓  **Slotted:** 1.5, 2.0, 2.5, 3.0, 3.5, 4.0mm

⊗ **TORX®:** T6, T7, T8, T9, T10, T15

↔ **lbs.** .34



[SHOP](#)

26999 9 Piece Hex Metric Precision Blade Set

Wiha ESD Safe  precision collet lock handle & 8 Wiha interchangeable blades. In metal storage box.

26999 ⬢ **Hex Metric:** .71, .89, 1.27, 1.5, 2.0, 2.5, 3.0, 4.0mm

↔ **lbs.** .36



[SHOP](#)

26989 9 Piece Hex Inch Precision Blade Set

Wiha ESD Safe  precision collet lock handle & 8 Wiha interchangeable blades. In metal storage box.

26989 ⬢ **Hex Inch:** .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"

↔ **lbs.** .35



[SHOP](#)

26995 5 Piece TORX® Precision Blade Set

Wiha ESD Safe  precision collet lock handle & 4 interchangeable blades. In metal storage box.

26995 ⊗ **TORX®:** T6, T7, T8, T9, T10, T15, T20

↔ **lbs.** .24



[SHOP](#)

26987 8 Piece TORX® Precision Blade Set

Wiha ESD Safe  precision collet lock handle & 7 interchangeable blades. In metal storage box.

26987 Set includes the following blades:

⊗ **TORX® standard blades:** T3, T4, T5

⊗ **TORX® reversible blades:**

T6, T7, T8, T9, T10, T15, T20

↔ **lbs.** .33




Wiha SoftFinish® Handle - Ergonomic Cushion Grip

Wiha SoftFinish® Handle: Featuring advanced technology dual material molding. A remarkable improvement in handle design, comfort and performance. The SoftFinish® ergonomic shape allows maximum torque and user comfort.

Wiha Nut Drivers are precision formed to exact tolerances for a perfect fit every time

All blades are made of Wiha's exclusive formula chrome-vanadium-molybdenum tool steel, super hardened plated for unmatched durability

Wiha exclusive "SoftFinish® Zone" features solid molded core with soft outer cushion grip. Requires less force, yet achieves 40% more torque than conventional handles



Handle is molded directly onto the blade for a permanent bond. Large optimized handle diameter allows higher torque with less user hand fatigue



[SHOP](#)

341 Nut Driver, With Wiha-SoftFinish® Handle Inch sizes

Blade CVM steel, hardened. Deep drawn 1" socket. Solid shafts. Wiha-SoftFinish® handle, multi-component, cushion grips.

Item No.	Inch	Inch	mm	mm	Inch	lbs.	pkg.
34134	9/64	5.0	125	238	9.4	.18	10
34135	5/32	5.0	125	238	9.4	.24	10
34136	3/16	5.0	125	238	9.4	.25	10
34137	7/32	5.0	125	238	9.4	.26	10
34138	1/4	5.0	125	246	9.7	.38	10
34139	5/16	5.0	125	246	9.7	.40	10
34140	11/32	5.0	125	246	9.7	.40	10
34141	3/8	5.0	125	246	9.7	.40	10
34142	7/16	5.0	125	246	9.7	.40	10
34143	1/2	5.0	125	246	9.7	.40	10
34144	9/16	5.0	125	246	9.7	.40	10
34145	5/8	5.0	125	246	9.7	.40	10



[SHOP](#)

341 Nut Driver, With Wiha-SoftFinish® Handle Metric sizes

Blade CVM steel, hardened. Deep drawn 1" socket. Solid shafts. Wiha-SoftFinish® handle, multi-component, cushion grips.

Item No.	mm	mm	Inch	mm	Inch	lbs.	pkg.
34120	5.0	125	5.0	238	9.4	.14	10
34121	5.5	125	5.0	238	9.4	.14	10
34122	6.0	125	5.0	238	9.4	.15	10
34123	7.0	125	5.0	238	9.4	.25	10
34124	8.0	125	5.0	238	9.4	.25	10
34125	9.0	125	5.0	238	9.4	.26	10
34126	10.0	125	5.0	238	9.4	.27	10
34127	11.0	125	5.0	247	9.7	.37	10
34128	12.0	125	5.0	247	9.7	.40	10
34129	13.0	125	5.0	247	9.7	.40	10
34130	14.0	125	5.0	247	9.7	.40	10
34131	15.0	125	5.0	247	9.7	.40	10
34132	16.0	125	5.0	249	9.8	.42	10
34133	17.0	125	5.0	249	9.8	.42	10



#34193

#34195

[SHOP](#)

34193 7 Pcs. Nut Driver Set Inch sizes. Blade CVM steel, hardened. Deep drawn 1" socket. Wiha-SoftFinish® handle, multi-component.

Item								
No.		Inch	Inch			Inch	Inch	lbs.
34193	34136	3/16	5.0	34141	3/8	5.0		1.89
	34138	1/4	5.0	34142	7/16	5.0		
	34139	5/16	5.0	34143	1/2	5.0		
	34140	11/32	5.0					

34195 10 Piece Nut Driver Set Inch sizes

Item								
No.		Inch	Inch			Inch	Inch	lbs.
34195	34136	3/16	5.0	34141	3/8	5.0		3.12
	34137	7/32	5.0	34142	7/16	5.0		
	34138	1/4	5.0	34143	1/2	5.0		
	34139	5/16	5.0	34144	9/16	5.0		
	34140	11/32	5.0	34145	5/8	5.0		



[SHOP](#)

34194 7 Piece Nut Driver Set Metric sizes

1. Presidential Cover Set - Metric sizes							
Item							
No.	mm	mm		mm	mm	lbs.	
34194	34120	5.0	125	34124	8.0	125	1.93
	34121	5.5	125	34126	10.0	125	
	34122	6.0	125	34129	13.0	125	
	34123	7.0	125				

Wiha SoftFinish® Heavy Duty Nut Drivers



[SHOP](#)

347 Nut Driver, With Hex Bolster & Wiha-SoftFinish® Handle

Blade CVM steel, hardened. Deep drawn 1" socket. Hex bolster for additional torque, Solid shafts. Wiha-SoftFinish® cushion grip handle.

Item								
No.	mm	mm	mm	mm	Inch	lbs.	pkg.	
34712	7.0	125	10.0	238	9.4	.25	10	
34715	8.0	125	10.0	238	9.4	.25	10	
34718	9.0	125	10.0	238	9.4	.26	10	
34721	10.0	125	10.0	238	9.4	.27	10	
34724	11.0	125	13.0	247	9.7	.37	10	
34727	12.0	125	13.0	247	9.7	.40	10	
34730	13.0	125	13.0	247	9.7	.40	10	

[SHOP](#)

347 Nut Driver, Hex Bolster & Wiha-SoftFinish® Handle Inch sizes

Item								
No.	Inch	Inch	mm	Inch	mm	Inch	lbs.	pkg.
34753	3/16	5.0	125	5/16	231	9.1	.18	10
34759	1/4	5.0	125	3/8	238	9.4	.24	10
34765	5/16	5.0	125	3/8	238	9.4	.25	10
34771	3/8	5.0	125	3/8	238	9.4	.26	10
34774	7/16	5.0	125	1/2	246	9.7	.38	10
34777	1/2	5.0	125	1/2	246	9.7	.40	10



[SHOP](#)

34791 5 Piece Nut Driver Set Metric sizes

Item						
No.	mm	mm	mm	mm	mm	lbs.
34791	34120*	5.0	125	34721	10.0	1.42
	34122*	6.0	125	34724	11.0	
	34715	8.0	125			

*Standard blade - no hex bolster



[SHOP](#)

34792 6 Piece Nut Driver Set Inch sizes

Item						
No.	Inch	Inch	Inch	Inch	Inch	lbs.
34792	34753	3/16	5.0	34771	3/8	1.94
	34759	1/4	5.0	34774	7/16	
	34765	5/16	5.0	34777	1/2	

Long Flexible Shaft Nut Drivers, SoftFinish® Handle - Ergonomic Cushion Grip



[SHOP](#)

372 Long Flexible Shaft Nut Driver, With Wiha-SoftFinish®

Handle Inch sizes. Heavy Duty flexible shaft of braided steel with protective sleeve. Hardened mounted socket for optimal torque.

Wiha-SoftFinish® handle, multi-component, cushion grips.

Item							
No.	Inch	Inch	mm	mm	Inch	lbs.	pkg.
37220	3/16	5.9	150	261	10.2	.30	1
37222	1/4	5.9	150	261	10.2	.42	1
37224	5/16	5.9	150	261	10.2	.44	1
37226	3/8	6.9	175	261	10.2	.44	1
37228	7/16	6.9	175	261	10.2	.44	1
37230	1/2	6.9	175	261	10.2	.44	1



[SHOP](#)

37290 6 Piece Flexible Shaft Nut Driver Set, Inch Sizes

Item						
No.	Inch	Inch	Inch	Inch	Inch	lbs.
37290	37220	3/16	5.9	37226	3/8	2.50
	37222	1/4	5.9	37228	7/16	
	37224	5/16	5.9	37230	1/2	



[SHOP](#)

372 Long Flexible Shaft Nut Driver, With Wiha-SoftFinish®

Handle Metric sizes. Heavy Duty flexible shaft of braided steel with protective sleeve. Hardened mounted socket for optimal torque.

Wiha-SoftFinish® handle, multi-component, cushion grips.

Item							
No.	mm	mm	Inch	mm	Inch	lbs.	pkg.
37235	5.0	150	5.9	261	10.2	.16	1
37236	5.5	150	5.9	261	10.2	.16	1
37237	6.0	150	5.9	261	10.2	.17	1
37238	7.0	150	5.9	261	10.2	.28	1
37239	8.0	150	5.9	261	10.2	.28	1
37241	10.0	175	6.9	261	10.2	.44	1
37244	13.0	175	6.9	261	10.2	.44	1



[SHOP](#)

37291 7 Piece Flexible Shaft Nut Driver Set, Metric Sizes

Item							
No.	mm	mm	mm	mm	mm	mm	lbs.
37291	37235	5.0	150	37239	8.0	150	1.93
	37236	5.5	150	37241	10.0	175	
	37237	6.0	150	37244	13.0	175	
	37238	7.0	150				

Wiha SoftFinish® Nut Drivers - Hollow Shaft



343 Hollow Shaft Nut Driver-Wiha-SoftFinish® Handle Inch sizes

Item							
No.	Inch	Inch	mm	mm	Inch	lbs.	pkg.
34336	3/16	2.75	70	175	7.0	.18	10
34338	1/4	2.75	70	175	7.0	.24	10
34339	5/16	2.75	70	175	7.0	.25	10
34340	11/32	2.75	70	182	7.5	.25	10
34341	3/8	2.75	70	182	7.5	.26	10
34342	7/16	2.75	70	187	7.6	.38	10
34343	1/2	2.75	70	187	7.6	.40	10



Inch Color Coded To Size

- Hollow shafts allow for fit over extended bolts
- Finally a handle that makes Nut Drivers useful
- Get 40% more power with SoftFinish cushion grip
- Soft ergonomic molded shape for maximum comfort
- Heavy duty hollow shaft - 3.7" depth
- Hardened for maximum torque and wear resistance
- Chrome plated anti corrosion finish



343 Hollow Shaft Nut Driver With Wiha-SoftFinish® Handle Metric

Item							
No.	mm	mm	mm	Inch	lbs.	pkg.	
34302	5.0	70	175	7.0	.14	10	
34304	5.5	70	175	7.0	.14	10	
34306	6.0	70	175	7.0	.15	10	
34308	7.0	70	182	7.5	.25	10	
34310	8.0	70	182	7.5	.25	10	
34312	10.0	70	187	7.6	.27	10	
34314	13.0	70	187	7.6	.40	10	



34390 7 Piece Hollow Shaft Nut Driver Set Inch Sizes

Item							
No.	Inch	Inch	Inch	Inch	lbs.		
34390	34336	3/16	2.75	34341	3/8	2.75	1.55
	34338	1/4	2.75	34342	7/16	2.75	
	34339	5/16	2.75	34343	1/2	2.75	
	34340	11/32	2.75				



34391 7 Piece Hollow Shaft Nut Driver Set Metric Sizes

Item							
No.		mm	mm		mm	mm	lbs.
34391	34302	5.0	70	34310	8.0	70	1.41
	34304	5.5	70	34312	10.0	70	
	34306	6.0	70	34314	13.0	70	
	34308	7.0	70				

Wiha SoftFinish® Triangle Nut Drivers


[SHOP](#)

344 Triangle Nut Driver, With Wiha-SoftFinish® Handle

Blade Chrome-vanadium-molybdenum steel, hardened.

Wiha-SoftFinish® cushion grip handle.

Item No.	Size	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
34474	M4	6.8	.267"	125	5"	236	9.3	.00	10
34475	M5	8.3	.326"	125	5"	236	9.3	.00	10
34476	M6	10.1	.413"	125	5"	236	9.3	.00	10
34478	M8	12.1	.474"	125	5"	243	9.6	.00	10
34480	M10	15.1	.592"	125	5"	243	9.6	.00	10
34482	M12	16.1	.651"	125	5"	243	9.6	.00	10

Wiha T-Handle Nut Drivers


[SHOP](#)

336 Nut Driver, With Wiha T-handle Blade CVM steel, hardened,

nickel-plated. Wiha T-handle high quality plastic, impact resistant.

Deep drawn 1" socket, solid shaft.

Item No.	mm	mm	mm	lbs.	pkg.
33603	6.0	125	100	.16	10
33606	8.0	125	100	.18	10
33607	8.0	200	100	.22	10
33609	9.0	125	100	.23	10
33612	10.0	125	100	.24	10
33614	10.0	230	100	.26	10
33620	12.0	125	100	.26	10
33622	13.0	125	100	.27	10
33623	13.0	230	100	.30	10


[SHOP](#)

336 Nut Driver, With Wiha T-handle Blade CVM steel, hardened,

nickel-plated. Wiha T-handle high quality plastic, impact resistant.

Deep drawn 1" socket, solid shaft.

Item No.	Inch	Inch	Inch	lbs.	pkg.
33653	3/16	6.0	4.0	.16	10
33659	1/4	6.0	4.0	.18	10
33665	5/16	6.0	4.0	.19	10
33671	3/8	6.0	4.0	.20	10
33674	7/16	6.0	4.0	.26	10
33677	1/2	6.0	4.0	.30	10


[SHOP](#)

33691 5 Piece Nut Driver T-handle Set Metric Sizes

Blade CVM steel, hardened, nickel-plated. Wiha T-handle high quality plastic, impact resistant. Deep drawn 1" socket, solid shaft.

Item No.	mm	mm	mm	mm	lbs.
33691	33603	6.0	125	33612	10.0
	33606	8.0	125	33622	13.0
	33609	9.0	125		


[SHOP](#)

33690 6 Piece Nut Driver T-handle Set Inch Sizes

Blade CVM steel, hardened, nickel-plated. Wiha T-handle high quality plastic, impact resistant. Deep drawn 1" socket, solid shaft.

Item No.	Inch	Inch	Inch	Inch	lbs.
33690	33653	3/16	6.0	33671	3/8
	33659	1/4	6.0	33674	7/16
	33665	5/16	6.0	33677	1/2


[SHOP](#)

38800 Bit Holder With Wiha T-handle

Magnetic, holds bit and screw. Retainer out of stainless steel.

Hex shaft chrome-vanadium-molybdenum steel, nickel-plated.

Wiha T-handle high quality plastic, impact resistant.

Item No.	Size	mm	Inch	mm	Inch	lbs.	pkg.
38800	1/4	150	6.0	80	3.0	.18	1

Wiha Drive-Loc VI Nut Drivers

Drive-Loc VI

For Adjustable Length
Locking Blades



Locking mechanism in SoftFinish cushion grip ergonomic handle. Blade length can be adjusted from 40mm-120mm. (1.7 to 4.7" in 1/8" increments)

See Drive-Loc VI
Handles &
Screwdrivers on
pages 20-22



The blade length
can be adjusted from
40mm-120mm. (1.7 to 4.7")



[SHOP](#)

281 Drive-Loc VI Inch Nut Driver Blades

High alloy CVM steel, through hardened, hard chrome finish.
OAL blade length 150mm/5.9". Blades fit all Drive-Loc VI handles.

Item				
No.	Inch	OAL	lbs.	pkg.
28156	3/16	5.9"	.11	1
28157	7/32	5.9"	.11	1
28158	1/4	5.9"	.11	1
28159	9/32	5.9"	.12	1
28160	5/16	5.9"	.13	1
28161	11/32	5.9"	.14	1
28162	3/8	5.9"	.15	1
28163	7/16	5.9"	.17	1
28164	1/2	5.9"	.18	1



[SHOP](#)

281 Drive-Loc VI Metric Nut Driver Blades

High alloy CVM steel, through hardened, hard chrome finish.
OAL blade length 150mm/5.9". Blades fit all Drive-Loc VI handles.

Item				
No.	mm	OAL	lbs.	pkg.
28168	4.0	150mm	.10	1
28169	4.5	150mm	.10	1
28170	5.0	150mm	.11	1
28171	5.5	150mm	.11	1
28172	6.0	150mm	.12	1
28173	7.0	150mm	.13	1
28174	8.0	150mm	.13	1
28177	9.0	150mm	.14	1
28175	10.0	150mm	.15	1
28176	11.0	150mm	.20	1



[SHOP](#)

28196 8 Pc. Drive-Loc VI Interchangeable Blade Set, In Durable Pouch

Set includes Drive-Loc VI handle & 7 Inch Nut Driver blades.

Item	lbs.
No. 28196	1.22
Inch:	3/16, 1/4, 5/16, 11/32, 3/8, 7/16, 1/2"
Wiha SoftFinish® Cushion Grip Blade Lock Handle	



[SHOP](#)

28198 8 Pc. Drive-Loc VI Interchangeable Blade Set, In Durable Pouch

Set includes Drive-Loc VI handle & 7 Metric Nut Driver blades.

Item	lbs.
No. 28198	1.00
Metric:	5.0, 5.5, 6.0, 7.0, 8.0, 9.0, 10.0mm
Wiha SoftFinish® Cushion Grip Blade Lock Handle	



[SHOP](#)

28144 Extension Blade For Drive-Loc VI Blades

High alloy CVM steel, through hardened, hard chrome finish.
OAL blade length 6.5". Blades fit all Drive-Loc VI handles.

Item				
No.	mm	OAL	lbs.	pkg.
28144	6.0	150mm	.14	1

Wiha Nut Driver Precision Series



265 Metric Metric Nut Driver With Precision Handle

Metric sizes. Blade CVM steel. Hard chrome finished.

Item No.	mm	mm	Inch	mm	Inch	mm	mm	lbs.	pkg.
26510	1.5	60	2.4	140	5.5	2.5	3.0	.03	10
26515	1.8	60	2.4	140	5.5	2.9	3.5	.03	10
26520	2.0	60	2.4	140	5.5	3.2	4.0	.04	10
26525	2.5	60	2.4	155	6.1	4.0	4.0	.04	10
26530	3.0	60	2.4	155	6.1	5.0	5.0	.05	10
26532	3.2	60	2.4	155	6.1	5.0	5.0	.05	10
26535	3.5	60	2.4	155	6.1	5.3	6.0	.05	10
26540	4.0	60	2.4	155	6.1	5.5	6.0	.05	10
26545	4.5	60	2.4	155	6.1	6.2	7.0	.05	10
26550	5.0	60	2.4	155	6.1	6.8	7.0	.05	10
26555	5.5	60	2.4	170	6.7	7.6	8.0	.06	10
26560	6.0	60	2.4	170	6.7	8.2	9.0	.06	10
26570	7.0	60	2.4	170	6.7	9.6	10.0	.06	10

*Metric dimensions actual - Inch dimensions approximate



265 Inch Inch Nut Driver With Precision Handle

Inch sizes. Blade CVM steel. Hard chrome finished.

Item No.	Inch	mm	Inch	mm	Inch	Inch	Inch	lbs.	pkg.
26523	3/32	60	2.4	155	6.1	.16	.16	.04	10
26527	7/64	60	2.4	155	6.1	.20	.20	.05	10
26531	1/8	60	2.4	155	6.1	.20	.20	.05	10
26536	9/64	60	2.4	155	6.1	.21	.24	.05	10
26539	5/32	60	2.4	155	6.1	.22	.24	.05	10
26547	3/16	60	2.4	155	6.1	.25	.28	.05	10
26556	7/32	60	2.4	170	6.7	.30	.32	.06	10
26563	1/4	60	2.4	170	6.7	.34	.36	.06	10

*Metric dimensions actual - Inch dimensions approximate



26590 8 Pc. Precision Nut Driver Set - Metric

Blade CVM steel.

Item No.	lbs.
26590 Metric Nut Drivers:	.48
2.5, 3.0, 3.5, 4.0, 4.5, 5.0, 5.5, 6.0mm x 60mm	

26592 Set 7 Pcs. Nut Driver Metric

Item No.	26592	1.5, 1.8, 2.0, 2.5, 3.0, 3.5, 4.0mm
----------	-------	-------------------------------------



26591 8 Pc. Precision Nut Driver Set - Inch

Blade CVM steel.

Item No.	lbs.
26591 Inch Nut Drivers:	.47
3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4" x 2.4"	



26598 8 Pc. Precision Nut Driver Set - Metric

Blade high alloy chrome-vanadium-molybdenum steel. Hard chrome finished. In canvas storage pouch

Item No.	lbs.
26598 Metric Nut Drivers:	.70
2.5, 3.0, 3.5, 4.0, 4.5, 5.0, 5.5, 6.0mm x 60mm	



26599 8 Pc. Precision Nut Driver Set - Inch

Blade high alloy chrome-vanadium-molybdenum steel. Hard chrome finished. In canvas storage pouch

Item No.	lbs.
26599 Inch Nut Drivers:	.72
3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4" x 2.4"	

Pico Soft Grip Nut Drivers Inch & Metric



[SHOP](#)

265 Inch Nut Drivers, With Precision Soft PicoFinish Handle

Blade high alloy CVM tool steel, hardened, hard chrome finish.

Item No.	Inch	Inch	mm	Inch	mm	pkg.
26571	3/32	2.4	60	6.3	160	10
26572	7/64	2.4	60	6.3	160	10
26573	1/8	2.4	60	6.3	160	10
26574	9/64	2.4	60	6.3	160	10
26575	5/32	2.4	60	6.3	160	10
26576	3/16	2.4	60	6.3	160	10
26577	7/32	2.4	60	6.3	160	10
26578	1/4	2.4	60	6.3	160	10

*Metric dimensions actual - Inch dimensions approximate



[SHOP](#)

26593 8 Piece Inch Nut Driver Set, With Precision Soft PicoFinish Handle In storage pouch

Item No.		lbs.
26593	Inch Nut Drivers: 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4" x 2.4"	.72



[SHOP](#)

265 Metric Nut Drivers, With Precision PicoFinish Handle

Blade high alloy CVM tool steel, hardened, hard chrome finish.

Item No.	mm	mm	Inch	mm	Inch	pkg.
26579	1.5	60	2.4	160	6.3	10
26581	2.0	60	2.4	160	6.3	10
26582	2.5	60	2.4	160	6.3	10
26583	3.0	60	2.4	160	6.3	10
26584	3.5	60	2.4	160	6.3	10
26585	4.0	60	2.4	160	6.3	10
26586	4.5	60	2.4	160	6.3	10
26587	5.0	60	2.4	160	6.3	10
26588	5.5	60	2.4	160	6.3	10
26589	6.0	60	2.4	160	6.3	10

*Metric dimensions actual - Inch dimensions approximate



[SHOP](#)

26596 8 Piece Metric Nut Driver Set, With Precision Soft PicoFinish Handle In storage pouch

Item No.		lbs.
26596	Metric Nut Drivers: 2.0, 2.5, 3.0, 3.5, 4.0, 4.5, 5.0, 5.5 x 60mm	.66

Rotating Cap
for precise turning and control

Precision Handle
high quality plastic, cadmium free. ESD Safe or Standard styles

Tapered Handle
allows rapid rotation, requires less clearance

Blades
CVM steel, hardened, hard chromed

Collet Lock Handle
adjustable blade length from 15 to 95mm/.6" to 3.75"

Tips
Exact fit, precision machined

15mm
95mm

See **SYSTEM 4** Handles & Blades on pages 38-41




[SHOP](#)

269 SYSTEM 4 Nut Driver Inch, Interchangeable Blade.

High alloy chrome-vanadium-molybdenum steel, hardened, corrosion protected. On 4mm Hex shaft. 120mm/4.7" OAL

Item No.	Inch	Inch	Inch	lbs.
26962	3/32	.16	.16	.04
26963	7/64	.20	.20	.04
26964	1/8	.20	.20	.04
26965	9/64	.21	.24	.04
26966	5/32	.22	.24	.04
26967	3/16	.26	.28	.04
26968	7/32	.30	.32	.04
26969	1/4	1.34	.36	.04



[SHOP](#)

269 SYSTEM 4 Nut Driver Metric, Interchangeable Blade High alloy chrome-vanadium-molybdenum steel, hardened, corrosion protected. On 4mm Hex Shaft. 120mm/4.7" OAL

Item					
No.	mm	mm	Inch	Inch	lbs.
26940	1.5 + 1.8		.12	.12	.03
26941	2.0 + 2.5		.16	.16	.03
26938	1.5 -		.11	.11	.04
26939	1.8 -		.12	.12	.04
26949	2.0 -		.13	.13	.06
26950	2.5 -		.16	.16	.06
26942	3.0 -		.20	.20	.06
26943	3.2 -		.20	.20	.06
26944	3.5 -		.22	.24	.06
26945	4.0 -		.22	.24	.06
26946	4.5 -		.25	.28	.06
26947	5.0 -		.27	.28	.06
26948	5.5 -		.30	.32	.06

SYSTEM 4 Sets in Compact Fold-out box



- ESD Safe Precision Handle
- High alloy CVM steel, hardened
- Exact fit tips
- In metal storage box



SHOP

26988 9 Pc. Nut Driver Inch Precision

Blade Set Wiha ESD Safe precision collet lock handle & 8 Wiha interchangeable blades.

26988 Set includes the following blades:

 **Nut Driver Inch:**

3/32, 7/64, 1/8, 9/64, 5/32,
3/16, 7/32, 1/4"

 **lbs. .39**



In metal storage boxes



SHOP

26998 9 Pc. Nut Driver Metric Precision

Blade Set Wiha ESD Safe precision collet lock handle and 8 Wiha interchangeable blades.

26998 Set includes the following blades:

 **Nut Driver Metric:**

2.0, 2.5, 3.0, 3.2, 3.5, 4.0,
4.5, 5.0, 5.5mm

 **lbs. .40**



SYSTEM 4 Nut Driver Sets



SHOP

28088 9 Piece Nut Driver Inch Precision

Blade Set Wiha ESD Safe precision collet lock handle and 8 Wiha interchangeable blades.

28088 Set includes the following blades:

 **Nut Driver Inch:**

3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4"

 **lbs. .37**



ESD Safe



SHOP

28098 8 Piece Nut Driver Metric Precision

Blade Set Wiha ESD Safe precision collet lock handle and 7 Wiha interchangeable blades.

28098 Set includes the following blades:

 **Nut Driver Metric:**

3.0, 3.2, 3.5, 4.0, 4.5, 5.0, 5.5mm

 **lbs. .40**



Item No.	Page	Item No.	Page	Item No.	Page
15305	28	26042	29	26340	31
15310	28	26050	34	26341	36
15315	28	26051	34	26343	36
15325	28	26052	34	26345	36
15330	28	26053	34	26347	36
15335	28	26054	34	26349	36
15340	28	26055	34	26351	36
16112	28	26056	34	26353	36
16134	28	26060	34	26363	36
18601	28	26061	34	26367	36
18603	28	26063	34	26369	36
18606	28	26065	34	26371	36
18609	28	26066	34	26390	31
18612	28	26068	34	26391	31
18615	28	26070	34	26392	36
18624	28	26072	34	26393	36
18627	28	26073	34	26399	31
18630	28	26074	34	26413	32
18642	28	26076	34	26415	32
18645	28	26079	34	26416	32
18648	28	26080	34	26419	32
18651	28	26090	29	26420	32
18654	28	26092	30	26423	32
18657	28	26093	34	26425	32
18663	28	26099	29	26427	32
18678	28	26100	30	26430	32
18681	28	26101	30	26431	32
20700	28	26102	30	26436	32
20705	28	26105	30	26439	32
20710	28	26107	30	26440	32
20715	28	26108	30	26441	36
20720	28	26109	30	26443	36
20725	28	26110	30	26445	36
20756	28	26113	30	26447	36
20757	28	26114	30	26449	36
20758	28	26115	30	26455	36
20759	28	26130	34	26457	36
20760	28	26132	34	26459	36
20790	28	26133	34	26461	36
20799	28	26135	34	26463	36
21103	15	26136	34	26465	36
22220	28	26140	34	26467	36
22230	28	26142	34	26490	32
22240	28	26145	34	26491	32
26000	29	26190	30	26493	36
26001	29	26192	30	26499	32
26008	29	26193	34	26510	47
26010	29	26194	30	26515	47
26012	29	26199	30	26520	47
26015	29	26205	31	26523	47
26018	29	26210	31	26525	47
26020	29	26307	31	26527	47
26022	29	26309	31	26530	47
26023	29	26313	31	26531	47
26025	29	26315	31	26532	47
26027	29	26316	31	26535	47
26028	29	26320	31	26536	47
26030	29	26323	31	26539	47
26032	29	26325	31	26540	47
26033	29	26327	31	26545	47
26034	29	26330	31	26547	47
26035	29	26331	31	26550	47
26040	29	26333	31	26555	47
26041	29	26336	31	26556	47

Item No.	Page	Item No.	Page	Item No.	Page	Item No.	Page	Item No.	Page	Item No.	Page
26560	47	26790	33	26962	48	28080	40	28194	22	30835	5
26563	47	26791	33	26963	48	28084	41	28196	22,46	30836	14
26570	47	26792	33	26964	48	28087	41	28197	22	30845	14
26571	48	26793	35	26965	48	28088	49	28198	22,46	30855	14
26572	48	26794	33	26966	48	28091	41	28199	22	30865	14
26573	48	26796	35	26967	48	28094	40	28486	20	30890	14
26574	48	26798	35	26968	48	28097	41	28487	20	30892	5
26575	48	26799	33	26969	48	28098	49	28488	20	30896	5
26576	48	26810	29	26971	38	28106	20	30202	6	30898	5
26577	48	26815	35	26972	38	28107	20	30203	6	31105	6
26578	48	26900	38	26973	38	28108	20	20204	6	31110	6
26579	48	26901	38	26974	38	28109	20	30205	6	31112	6
26581	48	26903	38	26975	39	28110	20	30206	6	31114	6
26582	48	26904	38	26976	39	28112	20	30208	6	31115	6
26583	48	26905	38	26977	39	28114	21	30210	6	31117	6
26584	48	26911	38	26978	39	28116	21	30211	6	31118	6
26585	48	26912	38	26979	39	28117	21	30212	6	31120	6
26586	48	26913	39	26980	39	28118	21	30215	6	31125	6
26587	48	26914	39	26981	39	28119	21	30216	6	31135	6
26588	48	26915	39	36982	39	28120	21	30217	6	31137	8
26589	48	26916	39	26985	39	28122	21	30218	6	31140	6
26590	47	26917	39	26987	41	28123	21	30219	6	31190	7
26591	47	26918	39	26988	49	28124	21	30220	6	31191	7
26592	47	26919	39	26989	41	28126	21	30221	6	31192	7
26593	48	26920	39	26990	40	28127	21	30222	6	31193	7
26596	48	26921	39	26991	40	28128	21	30223	6	31194	8
26598	47	26922	38	26992	40	28129	21	30225	6	31201	5
26599	47	26923	39	26993	40	28130	21	30226	6	31202	5
26701	33	26924	39	26995	41	28132	21	30227	6	31203	5
26702	33	26925	39	26996	41	28133	21	30230	6	31211	14
26703	33	26926	39	26997	41	28134	21	30232	6	31212	14
26704	33	26927	39	26998	49	28135	21	30235	6	31213	14
26705	33	26928	39	26999	41	28136	21	30236	6	31305	6
26706	33	26929	39	28000	38	28137	20	30237	8	31310	6
26707	33	26932	38	28001	38	28138	21	30238	6	31312	6
26708	33	26933	38	28002	39	28139	21	30239	6	31315	6
26709	33	26934	38	28003	39	28140	21	30255	6	31320	6
26710	33	26935	38	28004	39	28142	21	30265	6	31401	14
26715	33	26936	38	28005	39	28143	21	30276	8	31402	14
26720	33	26937	38	28006	39	28144	46	30290	8	31403	14
26721	35	26938	48	28007	39	28149	21	30291	8	33603	45
26723	35	26939	48	28008	39	28150	21	30294	7	33606	45
26725	35	26940	48	28009	39	28151	21	30295	7	33607	45
26727	35	26941	48	28010	39	28156	22,46	30297	7	33609	45
26729	35	26942	48	28011	39	28157	22,46	30298	7	33612	45
26731	35	26943	48	28012	39	28158	22,46	30299	8	33614	45
26732	35	26944	48	28013	39	28159	22,46	30517	8	33620	45
26733	35	26945	48	28014	39	28160	22,46	30520	8	33622	45
26735	35	26946	48	28015	39	28161	22,46	30523	8	33653	45
26736	35	26947	48	28016	39	28162	22,46	30526	8	33659	45
26737	35	26948	48	28017	39	28163	22,46	30530	8	33623	45
26739	35	26949	48	28021	38	28164	22,46	30535	8	33665	45
26741	35	26950	48	28023	38	28168	22,46	30540	8	33671	45
26743	35	26951	39	28024	38	28169	22,46	30550	8	33674	45
26745	35	26952	39	28025	38	28170	22,46	30560	8	33677	45
26747	35	26953	39	28026	38	28171	22,46	30580	8	33690	45
26749	35	26954	39	28027	38	28172	22,46	30813	5	33691	45
26751	35	26955	39	28028	38	28173	22,46	30814	5	34120	42
26761	33	26956	39	28029	38	28174	22,46	30815	5	34121	42
26762	33	26957	39	28033	38	28175	22,46	30816	5	34122	42
26763	33	26958	39	28034	38	28176	22,46	30817	5	34123	42
26764	33	26959	39	28035	38	28177	22,46	30820	5	34124	42
26765	33	26960	39	28036	38	28189	22	30825	5	34125	42
26766	33	26961	39	28037	38	28191	21	30830	5	34126	42

Item No. Page	Item No. Page	Item No. Page	Item No. Page	Item No. Page	Item No. Page
34127 42	36201 10	36298 11	39896 9	45595 18	52020 23
34128 42	36202 9	36299 11	40010 27	45597 18	52025 23
34129 42	36203 9	36710 12	44590 40	45598 18	52035 23
34130 42	36205 25	36713 12	45040 16	46094 17	52040 23
34131 42	36207 9	36715 13	45050 16	46095 17	52050 23
34132 42	36210 25	36716 12	45052 16	46097 17	52090 23
34133 42	36211 11	36719 12	45054 16	46098 16	52097 23
34134 42	36212 25	36720 13	45055 16	46099 16	52098 23
34135 42	36215 25	36723 12	45056 16	46702 19	52099 23
34136 42	36220 25	36725 13	45057 16	46704 19	52105 23
34137 42	36223 11	36726 12	45058 16	46706 19	52110 23
34138 42	36225 25	36728 12	45060 16	46708 19	52115 23
34139 42	36228 11	36730 13	45061 16	46710 19	52120 23
34140 42	36229 11	36732 12	45062 16	46712 19	52125 23
34141 42	36230 25	36734 12	45064 16	46714 19	52650 24
34142 42	36233 11	36736 12	45065 16	46715 18	52711 25
34143 42	36234 9	36738 12	45067 16	46716 19	52713 25
34144 42	36235 25	36740 13	45069 16	46718 19	52716 25
34145 42	36238 11	36742 12	45135 16	46720 18	52719 25
34193 42	36239 11	36744 12	45137 16	46722 19	52722 25
34194 42	36240 25	36750 13	45140 16	46724 19	52726 25
34195 42	36243 11	36760 13	45142 16	46725 18	52729 25
34302 44	36244 9	36780 13	45144 16	46726 19	52732 25
34304 44	36245 25	36786 13	45147 16	46728 19	52790 25
34306 44	36248 11	36790 13	45150 16	46730 18	52791 25
34308 44	36249 9	36791 12	45152 16	46740 18	53010 4
34310 44	36250 25	36792 13	45205 17	46750 18	53015 4
34312 44	36253 11	36793 12	45207 17	46760 18	53020 4
34314 44	36254 9	36794 12	45215 17	46780 18	53025 4
34336 44	36255 11	37220 43	45220 17	46786 18	53027 4
34338 44	36256 9	37222 43	45225 17	46793 19	53035 4
34339 44	36257 9	37224 43	45230 17	46794 19	53040 4
34340 44	36258 9	37226 43	45235 17	46796 18	53075 5
34341 44	36259 11	37228 43	45504 17	46797 19	53090 4
34342 44	36264 10	37230 43	45505 26	46799 18	53096 5
34343 44	36266 10	37235 43	45506 26	46803 15	53097 4
34390 44	36267 10	37236 43	45507 17	46806 15	53099 5
34391 44	36268 10	37237 43	45508 17	46812 15	53110 4
34474 45	36269 11	37238 43	45509 17	46815 15	53115 4
34475 45	36270 10	37239 43	45510 17	46912 15	53120 4
34476 45	36271 11	37241 43	45511 26	46915 15	53310 24
34478 45	36272 10	37244 43	45515 17	46921 15	53315 24
34480 45	36273 11	37290 43	45516 26	46924 15	53320 24
34482 45	36274 10	37291 43	45520 17	46933 15	53325 24
34712 43	36275 11	37608 14	45521 26	46991 15	53330 24
34715 43	36276 10	37609 14	45522 26	48106 15	53390 24
34718 43	36277 11	37610 14	45525 17	48190 15	53398 24
34721 43	36278 10	37615 14	45526 26	48400 26	53405 24
34724 43	36279 11	37620 14	45527 17	48401 16	53410 24
34727 43	36280 10	37625 14	45530 17	51020 27	53425 24
34730 43	36281 11	37627 14	45531 26	51025 27	62990 37
34753 43	36282 10	37630 14	45536 26	51030 27	62993 37
34759 43	36283 11	37640 14	45540 17	51035 27	62994 37
34765 43	36284 10	37690 14	45541 26	51040 27	62995 37
34771 43	36285 11	38800 45	45545 17	51055 27	65090 37
34774 43	36286 10	39700 9	45546 26	51065 27	90000 27
34777 43	36287 11	39701 9	45550 17	51080 27	91118 30
34791 43	36288 10	39702 9	45551 26	51090 27	92190 33
34792 43	36290 9	39825 9	45556 26	51099 27	92191 32
35800 6	36291 10	39830 9	45561 26	51105 27	95190 37
35801 6	36292 25	39840 9	45589 26	51110 27	96800 37
35802 6	36293 25	39850 9	45591 26	51120 27	
35803 6	36294 10	39860 9	45592 26	52005 23	
35894 6	36296 11	39892 9	45593 17	52010 23	

(800) 494-6104
 fax: (800) 494-7456
 email: cservice@wihatools.com

**SEE OUR GREAT
 WEB SPECIALS!**



Wiha Quality Tools

1348 Dundas Circle
 Monticello, MN 55362
 tel: 763.295.6591
 fax: 763.295.6598

Wiha Tools Canada Ltd.

www.wihatools.ca
 Brampton, ONT L6T 4X4
 tel: 866.494.0096 or 763.295.6591
 fax: 763.295.6598

To:

Catalog Item No. 99002 .wo
 version - 5/15/14

Subject to change without notice

©2014 Willi Hahn Corporation

®Torx is a registered trademark of
 Acument Intellectual Properties LLC.



91330.wo - Tooling Catalog




99004.wo - Shop Tools Catalog



99914.wo - TORX Catalog



99951.wo - Bits Catalog



99919.wo - Insulated Catalog



99001.wo - TorqueControl Catalog



99934.wo - Hex Tools Catalog



99006.wo - Tech Tools Catalog



99945.wo - ESD Catalog



99977.wo - Pliers/Crimpers Catalog