

Open-end wrenches

► Standard series




44 series open end wrenches

THE "DOUBLE-ENDED" WRENCH

2 sizes per wrench




- Reduces the number and weight of tools.



Power and precision

- Tightening torque : ISO 1711, DIN 899, NF E 74.381.
- Tight tolerances on openings for a perfect fit on fasteners.



Slim profile and comfort

- Smaller shape and volume for better accessibility.
- Streamlined heads.
- 30° increments.

44 Metric and inch open-end wrenches

► ISO 10102, DIN 3110, NF ISO 3318, NF ISO 10102.

- Metric sizes from 3.2 to 42 mm.
- Inch sizes from 1/4" x 5/16" to 17/16" x 15/8".
- Satin chrome finish.

➤ A mm	➤ A"	B x B' mm	C mm	L mm	ΔΔ g
44.3,2X5,5		11 x 13,5	3,0	90	11
44.4X5		11 x 13,5	3,0	90	11
44.6X7	44.1/4X5/16	15 x 17,5	3,5	120	20
44.8X9		18,5 x 21	3,8	137	30
44.8X10	44.11/32X13/32	19 x 23	4,2	143	38
44.10X11	44.3/8X7/16	23 x 25	4,7	152	47
44.10X13		23 x 29	5,1	162	58
44.11X13		25,5 x 29	5,1	167	65
44.12X13		25,5 x 29	5,1	167	64
44.12X14	44.1/2X9/16	29 x 33,5	5,5	177	77
44.14X15		31 x 33	5,8	182	87
44.13X17		31 x 37	6,3	192	118
44.16X17		35,5 x 37	6,3	200	118
44.16X18	44.5/8X11/16	37 x 42	6,8	210	144
44.17X19	44.11/16X3/4	37 x 42	6,8	210	144
44.18X19		39 x 42	7,3	220	157
44.20X22	44.3/4X13/16	43 x 48,5	7,5	240	200
44.21X23		47 x 50,5	7,8	242	218
44.22X24	44.7/8X15/16	47,5 x 52	8,3	261	258
44.24X27		51 x 58	8,8	270	324
44.25X28		56 x 61,6	8,8	282	360
44.26X28	44.1"X1"1/16	56 x 61,6	8,8	282	360
44.27X29		59 x 64	9,5	301	450
44.27X30		59 x 64	9,5	301	450
44.27X32	44.1"1/8X1"1/4	63 x 70	9,8	318	513
44.30X32	44.1"3/16X1"5/16	63 x 70	9,8	318	513
44.33X35		71 x 75	11,5	342	720
44.34X36		71 x 75	11,5	342	720
44.36X41	44.1"3/8X1"1/2	78 x 87	12,0	381	945
44.38X42	44.1"7/16X1"5/8	78 x 87	12,0	381	945

