

Distributed by:

JAMECO[®]
ELECTRONICS


www.Jameco.com ♦ 1-800-831-4242

The content and copyrights of the attached
material are the property of its owner.


Jameco Part Number 69462

Dimensions in mm

MFA



MFA-PA




* PS:12A~25A 32V approvals
30A 32V approvals

Test Specification according to standard
UL 248-1,14


Electrical Characteristic

Rated Current	1.0In	1.35In	2.0In
In	Min.	Max.	Max.
100mA-30A	4 h	3600 s	120 s

MFA-P



MFA-PR



Rated Current	Breaking capacity	Rated Voltage	MFA-P/PR/PA		
100mA	⑤125V/AC 10KA ⑤250V/AC 35A	125V/250V			
125mA		125V/250V			
150mA		125V/250V			
200mA		125V/250V			
250mA		125V/250V			
300mA		125V/250V			
315mA		125V/250V			
400mA		125V/250V			
500mA		125V/250V			
600mA		125V/250V			
800mA		125V/250V			
1A		125V/250V			
1.25A		125V/250V			
1.5A		125V/250V			
1.8A		125V/250V			
2A	⑤125V/AC 10KA ⑤250V/AC 100A	125V/250V			
2.5A		125V/250V			
3A		125V/250V			
3.15A		125V/250V			
3.5A		125V/250V			
4A		125V/250V			
5A		125V/250V			
5A		125V/250V			
5.3A		125V/250V			
7A		125V/250V			
8A	⑤125V/AC 10KA ⑤250V/AC 200A	125V/250V			
10A		125V/250V			
* 12A		32V			
* 13A		32V			
* 15A		32V			
* 16A		32V			
* 20A		32V			
* 25A		32V			
* 30A		32V			
	⑤32V/AC 1000A	32V			
		32V			

UNLESS OTHERWISE SPECIFIED
DIMENSIONS ARE IN MM
TOLERANCE
DECIMALS ANGULAR
X ± 0.5 ± 2°
XX ± 0.35
DO NOT SCALE DRAWING



P/N MFA63ax.xxx
REV A

CUSTOMER NO.

DRAWN BY JANE

CHECKED BY

APPROVED BY 郭定和

DATE 2008.06.16

SCALE

TITLE

Miniature Cartridge Fuse 6.35x32mm

PART NO. MFA MFA- P/PA /PR

DRAWING NO. AA05062109