


[About Leviton](#)
[A Century of Success](#)
[Press](#)
[Join Our eMailing List](#)
[Trade Shows](#)
[RoHS](#)
[Career Opportunities](#)
[Contact Us](#)
[All Leviton Products](#)
[Electrical](#)
[Network Solutions](#)
[Lighting Controls](#)
[Entertainment](#)
[Home Automation](#)
[Connected Home](#)
[Energy Management](#)
[Power Quality](#)
[Library Home](#)
[Application Notes](#)
[Brochures / Catalogs](#)
[Case Studies](#)
[DDLs](#)
[Downloads](#)
[Drawings](#)
[Line Cards](#)
[Manuals / Instructions](#)
[Product Specifications / Datasheets](#)
[Software](#)
[Specs \(AIA / CSI\)](#)
[Take One](#)
[Tech Notes](#)
[Technical Articles](#)
[Videos](#)
[ez-Biz](#)
[ez-Find](#)
[ez-Learn](#)
[ez-Configurator](#)
[Distribution Home](#)
[Contractor Connection](#)
[ez-Learn](#)
[ez-Find](#)
[Sign In - B2B](#)
[OEM Home](#)
[How to Buy](#)
[Whats New](#)
[Press/News](#)
[Retail Home](#)
[Product Information](#)
[How To](#)
[Merchandising](#)
[Energy Smart Living](#)
[International Home](#)
[China \(English\)](#)
[China \(Chinese\)](#)
[Mexico \(English\)](#)
[Mexico \(Spanish\)](#)
[Middle East \(English\)](#)
[International Contact](#)
[Press](#)
[Products](#)
[Trade Shows](#)
[Made to Order](#)
[EZE-Rough](#)
[Acenti Devices](#)
[AC Switches](#)
[Appliance Switches](#)
[Architectural Controls](#)
[Camera Systems](#)
[Combination Devices](#)
[Connectors & Cables](#)
[Cord Sets](#)
[Corrosion Resistant Devices](#)
[Daylighting Controls](#)
[Decora Devices](#)
[Dimmers](#)
[Cam-Type Devices](#)
[Electrical Accessories](#)
[Entertainment Accessories](#)
[Entertainment Fixtures](#)
[Entertainment Lighting Controls](#)
[Entertainment Lighting Kits](#)



[Electrical](#)
[Network Solutions](#)
[Lighting Controls](#)
[Entertainment](#)
[Home Automation](#)
[Connected Home](#)
[Energy Management](#)
[Power Quality](#)


 [ZOOM](#)

Quantity:

Color: Ivory



NEMA: 5-15R



5015-I

Description

15 Amp, 125 Volt, NEMA 5-15R, 2P, 3W, Narrow Body Single Receptacle, Straight Blade, Commercial Grade, Grounding, , , Side Wired, Steel Strap, - Ivory

Additional Product Information

- [Dimensional Drawing](#)
- [Wiring Diagram](#)

Product Features

Grounding: Grounding
Amperage: 15 Amp
Voltage: 125 Volt
NEMA: 5-15R
Pole: 2
Wire: 3
Termination: Side
Face Material: Nylon
Body Material: Nylon
Strap Material: Steel
Color: Ivory
Standards and Certifications: UL/CSA
Warranty: 10 Year Limited

AC Horsepower Ratings
At Rated Voltage: 1/2 HP

Electrical Specifications
Dielectric Voltage: Withstands 2000V per UL498
Current Limiting: Full Rated Current

Environmental Specifications
Flammability: Rated V-2 per UL94
Operating Temperature: -40C to 60C

Material Specifications
Face Material: Nylon
Body Material: Nylon
Line Contacts: Brass Double Wipe .031 Thick
Terminal Screws: Brass 8-32
Grounding Screw: Brass 8-32
Yoke: Zinc-Plated Steel

Mechanical Specifications
Terminal ID: Brass-Hot, Green-Ground, White-Neutral
Terminal Accom.: 14-10 AWG
Product ID: Ratings are permanently marked on device

Standards and Certifications
NEMA: WD-2 WD-6
ANSI: C-73
UL498: File E13399
UL Fed Spec WC-596: File E13399
CSA C22.2 No. 42: File 152105
NOM: 057