



Representative

**Catalog Number:** 312  
**Product ID:** 7TAA106030R0006  
**UPC Number:** 78621000312  
**Status:** A

2 Inch. Tite-Bite Connector, Malleable Iron-Electro Zinc Plated, Insulator-Thermoplastic.

- For use with Armored Cable and Flexible Metal Conduit

#### North American Specifications (UNSPSC)

UNSPSC	39121419 Flex connectors
IGCC	4573 Flex connectors
Brand Name	T&B
Type	Armored Cable/Flexible Metal Conduit Fittings
Special Features	Easy to Install with Double Grip Saddle, Connectors are Completely Salvageable
Application	To Connect and Effectively Bond Metal-Clad Cables, Armored Cable, and Flexible Metal Conduit to a Box or Enclosure
Standard	UL E23018, CSA
Size	2 Inch
Conductor Range	2.312 to 2.500 Inch
Material	Malleable Iron
Finish	Electro Zinc Plated
Color	Metallic
Insulation	No

#### European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	2 inch
Model	Straight
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Other
Material housing	Other
Surface protection	Zinc coated
Thread length	58.73mm
Approved in combination with protective conduit CSA	Y
Approved in combination with protective conduit UL	Y

#### Packaging

Outer Quantity	5
Outer Dimensions (inches)	9.6x6.8x3.8
Weight Uom	163.5 lbs. per 100

#### Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
Technical Drawing / Data Sheet Canada	Available on Website

#### Header

3D Model	Available on Website
----------	----------------------

**For further technical assistance, please contact us...**

860 Ridge Lake Blvd.  
Memphis, TN 38120  
[www.tnb.com](http://www.tnb.com)

MS 3B-50  
860 Ridge Lake Blvd.  
Memphis, TN 38120

Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)