

PANEL MOUNT INDICATOR, NON-RELAMPABLE

NEON TECHNOLOGY

MOUNTING HOLE, Ø 0.500"

PART NO.	LENS COLOR	VOLTAGE	CURRENT [mA]	RATED LIFE HOURS
NEON 115VAC SERIES				
WL-1060QD1	RED	105-125VAC	1.5mA	25,000
WL-1060QD3	AMBER	105-125VAC	1.5mA	25,000
WL-1060QD4	WHITE	105-125VAC	1.5mA	25,000
WL-1060QD5	GREEN	105-125VAC	1.5mA	25,000
NEON 230VAC SERIES				
WL-1061QD1	RED	208-250VAC	1.5mA	25,000
WL-1061QD3	AMBER	208-250VAC	1.5mA	25,000
WL-1061QD4	WHITE	208-250VAC	1.5mA	25,000
WL-1061QD5	GREEN	208-250VAC	1.5mA	25,000

NOTES


1. Recommended panel thickness
0.030" to 0.090"
2. .187 terminals are standard
3. Storage temperature
 T_{STG} : -25°C - +80°C
4. Ambient temperature
 T_A : -20°C - +60°C
5. Voltage tolerance
 V_{OP} : ±10%
6. Body material
Polycarbonate, white
7. Lens material
Polycarbonate
8. Bezel material
Stainless steel
9. .250 terminals available upon request

CERTIFICATIONS

UL (E340667), RoHS



DIMENSIONAL CHARACTERISTICS



unless otherwise specified, all dimensions are in inches



OPTIONS

Additional options and lens styles available. Please contact Wamco for more information.

