

ローレットつまみ

KNURLED KNOB FASTENERS

A-1038
ステンレス製A-1038-TMP
ステンレス製AP-38
プラスチック製A-38
黄銅製

特徴 Feature

仕様

- 〔A-1038〕
 - ・材質: ステンレス鋼 (SUS304)
 - ・表面仕上: 鏡面バフ研磨
 - 〔A-1038-TMP〕
 - ・材質: ステンレス鋼 (SUS304)
 - ・表面仕上: 電解研磨 (TMP)
 - 〔AP-38〕
 - ・材質: 頭部 / ABS樹脂
ねじ部 / 快削黄銅棒 (3604BD)
 - ・表面仕上: ねじ部 / ニッケルめっき (MBNi)
 - 〔A-38〕
 - ・材質: 快削黄銅棒 (3602BD)
 - ・表面仕上: クロムめっき (MBCr)
 - ・付属品: S.W.・ナット
- 用途
- ・配分電盤・制御盤・小型ボックス
- 納期
- ・標準在庫品
- 備考
- ・他のカラーも製作致します。(AP-38)



A-1038



A-1038-TMP




AP-38-2-Ivory (特注色)
アイボリー (custom-made color)




AP-38-3-Black (標準色)
ブラック (standard color)

〔A-1038・A-1038-TMP・A-38〕



〔AP-38〕



Specifications

- 〔A-1038〕
 - ・Material: Stainless steel (SUS304)
 - ・Finish: Mirror surface buffering
 - 〔A-1038-TMP〕
 - ・Material: Stainless steel (SUS304)
 - ・Finish: Electrolytic polishing (TMP)
 - 〔AP-38〕
 - ・Material: Head: ABS resin
Screw: Free cutting brass bar (C3604BD)
 - ・Finish: Screw: Nickel plating (MBNi)
 - 〔A-38〕
 - ・Material: Free cutting brass bar (C3602BD)
 - ・Finish: Chrome plating (MBCr)
 - ・Accessories: S.W. and nut
- Specific use
- ・Distribution, control boards and small boxes.

商品番号 Product No.	RoHS 2D/3D	CAD 2D/3D	材質 Material	L ₁	L ₂	L ₃	ΦD ₁	ΦD ₂	M	製品質量(g) Mass	コード Code	単価 Price	量販価格 Quantity	Bulk Price 単価 Price
A-1038	●	●	SUS304							40	01558	¥500	20個～	¥480
A-1038-TMP	●	●	SUS304							40	04616	¥750	20個～	¥720
A-38	●	●	黄銅 Brass							40	00137	¥240	25個～	¥230
AP-38-1-Black	●	●	ABS樹脂	19	11	9	22	11	M6	9	01366	¥190	50個～	¥182
AP-38-2-Black	●	●	ABS樹脂	15	10	5	18	9	M5	5	01367	¥170	50個～	¥163
AP-38-3-Black	●	●	ABS樹脂	12	8	2	15	8	M4	3	01368	¥160	50個～	¥154

● : RoHS指令対応品 ▲ : RoHS指令に対応可能です。

※大量のご注文は更にお安くなります。



クレモン

ローラー
継り特装密閉
ハンドルフリーザー^{密閉}平面
スイング

ギア式

平面
ハンドルポップ
ハンドルリフト
ハンドル