


USB "A" Type Plug

154-UAW16-E, 154-UAC16-E

KOBICONN

USB "A" Type Plug



Dimensions: mm (In)

MATERIAL SPECIFICATIONS: HOOD

Hood Material:	ABS Resin
RoHS Compliant	

ELECTRICAL SPECIFICATIONS: PLUG

Voltage:	30 VAC
Current:	1.5A Max. per contact at 30°C Rise
Temp. Range:	Storage: 20°C to 60°C Operating: 0°C to 50°C
Contact Resistance:	30mΩ Max. Initial
Insulation Resistance:	6000MΩ Min. Initial
Dielectric Withstanding Voltage:	750 VAC at Sea Level
RoHS Compliant	

Date Last Revised: 7-19-07

MATERIAL SPECIFICATIONS: PLUG

Upper and Lower Shell:	Steel
Housing:	Thermoplastic, glass filled
Contact:	Copper Alloy
Recommended Cable	O.D. ø3.4mm to ø5.3mm
Application:	O.D. ø3.4mm to ø5.3mm

All Parts Packaged Unassembled

RoHS Compliant

154-UAW16-E, 154-UAC16-E

Available from Mouser Electronics
1-800-346-6873 / www.mouser.com

KC-301153



Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.

USB "A" Type Plug

154-UAW16-E, 154-UAC16-E

KOBICONN

USB "A" Type Plug



Date Last Revised: 7-17-07

Dimensions: mm (In)

Available from Mouser Electronics
1-800-346-6873 / www.mouser.com

KC-301153

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.

154-UAW16-E, 154-UAC16-E

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[154-UAW16-E](#) [154-UAC16-E](#)