




Headers

to **Type 217** and **Type 218**

Type 235 page 145

Type 236 page 149

Accessories

for **Type 217** and **Type 218**
Coding set
700025 page 206

Type 217

Screw type terminal block, pluggable, centerline 5.08 mm / 0.200 inches, wire entry on rippled side, perpendicular to plug direction, lift system, contact with integrated wire protection, with mounting flange

Technical Data

V / A / AWG 300 / 12 / 28 - 12

0.08 - 4 mm² 250 V / 4 kV / 12 A

Insulation co-ordination according to EN 60664-1

Clearance and creepage distances min. 3.2 mm

Insulating material class CTI 600

Overvoltage category III III II

Pollution degree 3 2 2

Rated voltage 250 630 630

Rated test voltage 2.5 6 4

Protection category according to IEC 529 IP20

Tightening torque UL 4.4 lb-in max.


Min. insul. strip length 8 mm

Pole size 2 - 24

Color black

Dimensions in mm

1 mm = 0.0394 in.



L = (pole size - 1) x centerline + 14.68 mm / 0.578 inches

Part numbers (P/N)

(information: page 56)

Complete the part number by adding the pole size.

Type 217

centerline 5.08 mm / 0.200 inches

P/N 312171

	02	03	04	05	06	07	08
09	10	11	12	13	14	15	16
17	18	19	20	21	22	23	24

Type 217

centerline 10.16 mm / 0.400 inches

P/N 312172

* approval pending

	02	03	04	05	06	07	08
09	10	11	12				

Standard pole sizes

Available on demand. Minimum order quantity 5000 pieces per item.

Type 218

Screw type terminal block, pluggable, centerline 5.08 mm / 0.200 inches, wire entry on straight side, perpendicular to plug direction, lift system, contact with integrated wire protection, with mounting flange

Technical Data

V / A / AWG 300 / 12 / 28 - 12

0.08 - 4 mm² 250 V / 4 kV / 12 A

Insulation co-ordination according to EN 60664-1

Clearance and creepage distances min. 3.2 mm

Insulating material class CTI 600

Overvoltage category III III II

Pollution degree 3 2 2

Rated voltage 250 630 630

Rated test voltage 2.5 6 4

Protection category according to IEC 529 IP20

Tightening torque UL 4.4 lb-in max.


Min. insul. strip length 8 mm

Pole size 2 - 24

Color black

Dimensions in mm

1 mm = 0.0394 in.



L = (pole size - 1) x centerline + 14.68 mm / 0.578 inches

Part numbers (P/N)

(information: page 56)

Complete the part number by adding the pole size.

Type 218

centerline 5.08 mm / 0.200 inches

P/N 312181

	02	03	04	05	06	07	08
09	10	11	12	13	14	15	16
17	18	19	20	21	22	23	24

Type 218

centerline 10.16 mm / 0.400 inches

P/N 312182

	02	03	04	05	06	07	08
09	10	11	12				

Standard pole sizes

Available on demand. Minimum order quantity 5000 pieces per item.