

Search Results

- Evaluate
 - FAQ's
- How to Buy
 - Bill of Material
 - Favorite Products List
 - Locate Distributor

Home > Product On-Line Catalog > Search Results >

Current refinements (click  to remove) Search Tips 

 Text Search: 'FZPE3-10M1'

Your search criteria matched only one product, shown below

FZPE3-10M1



- Patch cords are tested to support network transmission speeds up to 10 Gb/s for link lengths up to 550 meters with an 850nm source per IEEE 802.3ae 10 GbE standard
- Pass all TIA/EIA-568-B.3 performance requirements
- Insertion loss per connection: 0.10dB typical; 0.30dB maximum
- Backward compatible for use with all 50/125µm system requirements
- Factory terminated and 100% tested for insertion loss
- Insertion loss data recorded for every multimode patch cord
- Lifetime traceability of test data to a Q.C. number on each patch cord
- SC Duplex Patch Cords include SC Duplex Clips to maintain polarity
- Highest quality flame retardant fiber optic cable with tight-buffered coating on each optical fiber

¹Additional lengths and availability: Patch cords are available in 1 – 10 meter lengths in 1 meter increments, and 15, 20, 25 and 30 meter lengths. Pigtails are available in 1, 2, and 3 meter lengths. Ex: To order lengths other than 1 meter, replace the 1 after the M (FZPE10-10M1) with the desired length (FZPE10-10M2 for 2 meter length). The above lengths are stock items. For other lengths, contact Customer Service for actual lead times.

| | |
|--------------------------------|--|
| • Part Number | FZPE3-10M1 |
| • RoHS Compliance Status | RoHS directive is not applicable |
| • Note | Intended for use in fixed installations which are outside the scope of RoHS |
| • Part Description | SC to LC Patch Cord, Standard OM4, 0.25 dB IL Loss, Duplex, Plenum, 1.6mm jacketed cable, 1m |
| • Product Type | Hybrid Patch Cords |
| • Length (m) | 1 |
| • Fiber Compatibility | 10 GbE 50/125µ |
| • Fiber Cable Size | 1.6mm |
| • Fiber Cable Type | Jacketed Cable |
| • Fiber Type | Multimode |
| • Connector 1 Type | SC Connector |
| • Connector 2 Type | LC Connector |
| • End Configurations | SC to LC |
| • Fiber Count | 2 |
| • Flammability Rating | Plenum (OFNP) |
| • Pricing Description | SC to LC, OM4 STD, Duplex, Plenum, 1.6mm jacketed cable, 1M |
| • Min. Order UOM | PC |
| • Min. Order Qty. | 1 |
| • BOM Qty. (# of Pkgs.) | 0 |
| • Add to Favorite Product List | <input type="checkbox"/> |

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.