

10GBase CX4 Cable, 5M (16-ft.)

MODEL NUMBER: **N263-05M**



Description

Tripp Lite's high-speed 10Gbps CX4 Cables provide an ultra high-performance, cost-effective solution for Gigabit Copper applications. Featuring 28AWG Madison TurboTwin™ twinaxial cable, these cables utilize up to 3.125 gigabytes per second wire speed connections with four channels. Cables work with any manufacturers' 10Gbps Xenpak transceivers that utilize the Ejector style latch connector. Tripp Lite CX4 cables are available in 0.5 meter, 1 meter, 3 meter, and 5 Meter lengths.

Features

- 5 Meter CX4 Cable
- Flexible 28AWG Madison TurboTwin™ Cable
- Ejector style latch mechanism
- Connects the CX4 modules between two switches
- Fully 802.3ak compliant
- RoHS Compliant

Specifications

General Info	
Product Group	NETWORK CABLES
OVERVIEW	
Intended Application	Computer Networking
Cable Type	CAT6
Model Type	CX4
INPUT	

Highlights

- 5 Meter CX4 Cable
- Works with any manufacturers' 10Gb XenPak
- Made with Premium Madison TurboTwin™ cable
- Compliant with the IEEE Draft specification P802.3ak/D5.3

Applications

- Used to interconnect 10GBase switches with CX4 modules

System Requirements

- Ethernet switches with CX4 / Xenpak modules for 10Gbps linking

Package Includes

10 GBase CX4 Cable (5 Meter)

Cable Length (ft.)	16.4
Cable Length (m)	5
UPC ASSIGNMENT	
Unit Carton UPC#	037332149916
PHYSICAL	
Color	Black
Style	CX4
CONNECTIONS	
Connector A	CX4 [SFF-8470] (MALE)
Connector B	CX4 [SFF-8470] (MALE)
Number of Connectors	2
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2014 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.