





LOC E	DIST B	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			B	ECR-06-015596	27JUN06	JMS	FWK

NOTES:


- 1 SINGLE PACK IN ACCORDANCE WITH AMP SPEC 107-3275
- 2 100 TRAY PACK IN ACCORDANCE WITH AMP SPEC 107-3275
- 3 Au PLATING
- 4 Ni PLATING
- 5 THIS ITEM MUST BE WHITE
- 6 HAND TOOL : 9-1478240-0
- 7 DIE SET : 9-1478242-0
- 8 ELECTRICAL CHARACTERISTICS
FREQUENCY RANGE: DC - 4 GHz
NOMINAL IMPEDANCE: 50 Ohm
INSULATION RESISTANCE: 5000 MOhm
WORKING VOLTAGE: 500 Volts RMS at Sea Level
DIELECTRIC WITHSTAND VOLTAGE: 1500 Volts RMS Max
CONTACT RESISTANCE:
CENTRE CONTACT: 1.50 mOhm Max
OUTER CONTACT: 0.20 mOhm Max
VSWR @ 4GHz: 1.30:1 Max
INSERTION LOSS dB @ x 3 GHz: 0.20 Max
- 9 MECHANICAL CHARACTERISTICS
COUPLING NUT RETENTION FORCE: 445N Min
CABLE RETENTION FORCE: 170N Min
DURABILITY: 500 Cycles Min
- 10 ENVIRONMENTAL CHARACTERISTICS
OPERATING TEMPERATURE: -65 to +165 DegC
- 11 FOR TECHNICAL DATA REFER TO YOUR LOCAL
TYCO ELECTRONICS SALES OFFICE
- 12 ALL DIMENSIONS ARE NOMINAL FOR REFERENCE
ONLY UNLESS OTHERWISE STATED




RECOMMENDED
CENTRE CONTACT
A/F HEX



RECOMMENDED
CRIMP SLEEVE
A/F HEX



RECOMMENDED
CABLE STRIPPING DIM'S



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	J.SANDWELL	27JUN06	tyco Tyco Electronics Corporation Bideford EX39 4HE		
		CHK	S.PARLOW	27JUN06			
		APVD	F.WHEELER-KING	27JUN06	NAME		
		PRODUCT SPEC			BNC STRAIGHT PLUG CRIMP 50 OHM RG55B/U, 142B/U, 223/U, 400/U, URM301, KX23		
		APPLICATION SPEC			-		
		WEIGHT			SIZE	CAGE CODE	RESTRICTED TO
		-			A3	00779	-
		CUSTOMER DRAWING			SCALE		
					NTS		
					SHEET	1 OF 1	REV
					B		