







Dimensions: mm (In.)



Without locking ring.

With standard locking ring.

PANEL MOUNTING

SOLDER LUG

POS.1	POS.2
ON	(ON)
2-3	2-1

SWITCH FUNCTION

Mechanical Specifications:

- Operating Temperature: -30°C to +85°C

Electrical Specifications:

- Electrical Life: 40,000 make-and-break cycles at full load
- Contact Resistance: 10mΩ max. initial @ 2-4VDC 100mA
- Insulation Resistance: 1,000MΩ min.
- Rating: 2A/ 250VAC, 5A/ 120VAC or 28VDC
- Dielectric Strength: 1,000 V RMS@ sea level

Materials:

- Case: Diallyl phthalate (DAP)
- Acutuator: Brass, chrome plated
- Bushing: Brass, nickel plated
- Housing: Stainless steel
- Terminal/Contact: Silver or Gold plated

Toggle Switch
108-1MS2T6B11M1QE

Mountain
Switch

Available from Mouser Electronics

www.mouser.com 1-800-346-6873

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mountain Switch:](#)

[108-1MS2T6B11M1QE](#)