



+ RELAYS, CONTACTORS & SWITCHES
DC



✓ Active

TE CONNECTIVITY (TE)
FM200DAYYY=RELAY, 3PST-NC, 24VDC COIL
[Kilovac](#) | [FM200](#)

FM200DAYYY
TE Internal Number: 3-1618378-2

- Not EU RoHS Compliant
- Not EU ELV Compliant
- Contact Arrangement 3 Form B, 3PST-NC, 3 N/C
- Wire Size (AWG) 24 – 14
- Contact Current Rating (A) 200
- Coil Voltage (Max) (VDC) 24
- Coil Voltage Rating (VDC) 12, 24

DOCUMENTATION

No documentation available.

FEATURES

Please review product documents or [contact us](#) for the latest agency approval information.

Product Type Features

- Terminal Configuration Quick Connect
- Contact Type High Power
- Product Category Electromechanical Relays
- Model FLATMAN III
- Product Type Contactor
- Product Classification Relays - Contactors

Electrical Characteristics

Coil Voltage (Max) (VDC) 24
Coil Voltage Rating (VDC) 12, 24
Actuating System DC

Contact Features

Contact Arrangement 3 Form B, 3PST-NC, 3 N/C
Contact Current Rating (A) 200
Number of Poles 3

Termination Features

Coil Termination M8 x 13mm Screw

Dimensions

Wire Size (AWG) 24 – 14

Packaging Features

Packaging Method Individual

PRODUCT COMPLIANCE

+

Statement of Compliance

Statement of Compliance
PDF