

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0190700078](#)
Status: **Active**
Description: InsulKrimp™ Ring Tongue Terminal for 14-16 AWG Wire

Documents:
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-19902-009 \(PDF\)](#)


General
Product Family Ring and Spade Terminals
Series [19070](#)
Mil-Spec N/A
Product Name InsulKrimp™
Type Ring

Physical
Barrel Type Closed
Color - Resin Natural
Flammability 94V-2
Insulation PVC
Material - Plating Mating Tin
Packaging Type Bag
Plating min: Mating (µin) 100
Plating min: Mating (µm) 2.5
Plating min: Termination (µin) 100
Plating min: Termination (µm) 2.5
Stud Size 5/16" (M8)
Wire Insulation Diameter 4.40mm (.175") max.
Wire Size AWG 14, 16
Wire Size mm² 1.30 - 2.00

Electrical
CSA LR18689
UL E32244

Material Info
Old Part Number BB-225-56X

Reference - Drawing Numbers
Product Specification PS-19902-009
Sales Drawing SD-19070-004



Series
image - Reference only

EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Not Reviewed
Halogen-Free
Status
Not Reviewed

China RoHS



Need more information on product environmental compliance?
Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)
Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[19070Series](#)

Application Tooling | FAQ
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
Hand Crimp Tool	0640010100
Crimp Head for the AT-200™ Pneumatic Hand Tool	0640050100
Crimp Head for the AT-200™ Pneumatic Hand Tool	0640050300
Crimp Head for the AT-200™ Pneumatic Hand Tool	0640051400
Hand Crimp Tool	0640010300
Hand Crimp Tool	0640011400

This document was generated on 02/02/2010

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION