


3M™ Cubitron™ II Abrasives[Products](#) | [Technology](#) | [Resources](#) | [Testimonials](#) | [Videos](#)[United States](#) > [Products & Services](#) > [Manufacturing and Industry](#) > [Cubitron II](#) > [Products](#) > [Cable/Wire](#) > [3M™ Round Conductor Flat Cable, 3801 Series, 3801/14, 100 ft.](#)

3M™ Round Conductor Flat Cable, 3801 Series, 3801/14, 100 ft.

UPC# 00054007320838 3M Product Number 3801/14 3M ID 80610088496

[Print](#)[Share](#) .050" 26 AWG Stranded, PVC, 100 ft.

- 26 AWG wire allows for higher power levels
- Stranded wire provides flexibility and extended product life
- .050 inch centers permit mass termination to a broad line of IDC connectors
- Zippable for branching or discrete termination
- Available in gray and black
- RoHS compliant

Need Help?**Questions?** We can help
[Contact Us](#) Network Access Message: The page[Overview](#) [Support](#)**Specifications****Color** Gray Standard or Black (See Ordering Information)**Shape** Flat**People who viewed this item also viewed**

3M™ Round, Shielded/Jacketed, Flat Cable, Cable, 3365 Series, 3365/16, 3659 Series 3659/26, 100 ft.



3M™ Round Conductor Flat Cable, 3365 Series, 3365/16, 100 ft.



3M™ High Flex Life Cable, 3319 Series, 3319/16, 100 ft.



3M™ Round Conductor Flat Cable, 3365 Series, 3365/40, 100 ft.



No Photo Available

3M™ DIP Socket, 4800 Series, 4824-3000-CP

