

Electronic housing - UM108-PROFIL 100CM - 2907525

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)

Drawn section panel mounting base, with a constructional width of 108 mm and a fixed length of 100 cm



The illustration shows the variant
UM 45-Profil CM

Why buy this product

- ✓ Lateral elements with potential ground contact available from the PCB to the DIN rail (EMC)
- ✓ Wide range of options for external conductor connection
- ✓ Fast assembly on standard NS 35 or NS 32 DIN rails
- ✓ Inexpensive as a result of reducing the number of separate housing parts
- ✓ Flexible size and shape
- ✓ High degree of mechanical stability by screwing the lateral elements to the profile
- ✓ The modules can be marked with Phoenix Contact marking material using the marking grooves in the press-drawn section



Key commercial data

Packing unit	1
Minimum order quantity	1
Catalog page	Page 645 (CC-2011)
GTIN	 4 017918 336653
Custom tariff number	39162000
Country of origin	GERMANY

Technical data

General

Housing type	Panel mounting base
Housing material	PVC
Color	green

Dimensions/poles

Width	1000 mm
-------	---------

Technical data

Ambient temperature (operation)	-15 °C ... 50 °C
---------------------------------	------------------

Electronic housing - UM108-PROFIL 100CM - 2907525

Technical data

Technical data

Inflammability class according to UL 94	V0
---	----

Classifications

ETIM

ETIM 2.0	EC001031
ETIM 3.0	EC001031
ETIM 4.0	EC001031
ETIM 5.0	EC000721

UNSPSC

UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	31261501
UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501

eCl@ss

eCl@ss 4.0	27180401
eCl@ss 4.1	27180401
eCl@ss 5.0	27180506
eCl@ss 5.1	27180506
eCl@ss 6.0	27180802
eCl@ss 7.0	27182701

Accessories

Accessories

Assembly

Electronic housing - UM108-FE - 2959463

Foot element, 107.5 mm wide, for mounting on NS 32 or NS 35/7.5, below profile housing UM 108.



Mounting flange - UMK-BF - 2976077



Mounting flange, for mounting directly on the wall

Electronic housing - UM108-PROFIL 100CM - 2907525

Accessories

Electronic housing - UM108-SEPEF/L - 2906490



Side element, left, with foot, width: 5 mm, length: 108 mm, for mounting on NS 32 or NS 35/7.5, with PE contact to the DIN rail

Electronic housing - UM108-SE - 2959476



Side element, 5 mm wide, PCB width: 107.5 mm

Electronic housing - UM108-SEFE/R-A60 - 2959706



Side element, with foot, tall version, right-hand, for 60 mm wide U-shaped cover.

Electronic housing - UM108-SEFE/R-A73 - 2959719



Side element, with foot, tall version, right-hand, for 73 mm wide U-shaped cover.

Electronic housing - UM108-FE - 2959463



Foot element, 107.5 mm wide, for mounting on NS 32 or NS 35/7.5, below profile housing UM 108.

Electronic housing - UM108-PROFIL 100CM - 2907525

Accessories

Electronic housing - UM108 N-SEFE/R-A73 - 2709354



Side element, with foot, low-profile version, right-hand, for 73 mm wide U-shaped cover.

Electronic housing - UM108-SEFE/L-A60 - 2959722



Side element, with foot, tall version, left-hand, for 60 mm wide U-shaped cover.

Electronic housing - UM108-SEPEF/L-A60 - 2906500



Side element with foot, tall design, left-hand, for 60 mm wide U-shaped cover, with PE contact to the DIN rail.

Electronic housing - UM108-SEFE/L-A73 - 2959735



Side element, with foot, tall version, left-hand, for 73 mm wide U-shaped cover.

Electronic housing - UM108-SEPEF/L-A73 - 2906513



Side element with foot, tall design, left, for 73 mm wide U-shaped cover, with PE contact to the DIN rail.

Electronic housing - UM108 N-SEFE/L-A73 - 2709367



Side element, with foot, low-profile version, left-hand, for 73 mm wide U-shaped cover.

Electronic housing - UM108-PROFIL 100CM - 2907525

Accessories

Electronic housing - UM108 N-SEPEF/L-A73 - 2709370



Side element with foot, low-profile design, left, for 73 mm wide U-shaped cover, with PE contact to the DIN rail.

Electronic housing - UM108-SE-A60 - 2959748



Side element, without foot, tall version, for 60 mm wide U-shaped cover.

Side element - UM108-SE-A73 - 2959751



Side element, without foot, tall version, for 73 mm wide U-shaped cover.

Electronic housing - UM108 N-SE-A73 - 2709383



Side element, without foot, low-profile version, for 73 mm wide U-shaped cover.

Electronic housing - UM108-A/U CM - 2854898

Profile covers, tall version, widths of 60 mm (internal dimension 56 mm) and 73 mm (internal dimension 69 mm) are available. Please note the ordering example and the order key.

Electronic housing - UM108-LG 10 - 2959780



Profile housing and board base, 10 mm wide module, consisting of two side elements

Electronic housing - UM108-PROFIL 100CM - 2907525

Accessories

Mounting flange - UMK-BF - 2976077




Mounting flange, for mounting directly on the wall

Electronic housing - UM-A/U N 73 CM - 2706852

U-shaped cover, flat-profile version, transparent, PC, high-temperature resistant material, please indicate length in [cm] with order no.

Drawings

Dimensioned drawing



© Phoenix Contact 2012 - all rights reserved
<http://www.phoenixcontact.com>