



FEATURES:

- Rigid sheath provides protection and accurate placement through bulkheads.
- Compatible with all temperature measuring instruments that accept Type "K" Thermocouples and have a miniature connector input.

MATERIALS:

Thermocouple – "K" Type, Chromel/Alumel

Cable – Perfluoroalkyl, AWG #24

Probe Sheath – Stainless Steel, 304

Connector Plug – Yellow, Hytrel 4776

RATINGS:

Operating Temperature: -40 to 500°F. (-40 to 260°C.)

Accuracy: $\pm 4.0^{\circ}\text{F.}$ ($\pm 2.2^{\circ}\text{C.}$) or .75% whichever is greater.

ORDERING INFORMATION:

 Model 6367

All dimensions are in inches. Tolerances (except noted): .xx = $\pm .02$ " (.51 mm), .xxx = $\pm .005$ " (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA